



BCT3L9N125 | 3-PHASE MODULAR UPS BATTERY CABINET

Configure a new system or extend runtime capacity with an additional battery cabinet

The CyberPower BCT3L9N125 3-Phase Modular UPS Battery Cabinet can hold up to 6 battery modules (BM120V30ATY). These 3-layer units can be configured as stand-alone cabinets, rack mounted, or stacked with another component of our modular UPS system. Includes a One-Year Limited Warranty.



SPECIFICATIONS

BATTERY	
Battery Module Capacity Maximum	6
OUTPUT	
Nominal Output Voltage	240 VAC
PHYSICAL	
Color	Black
Form Factor	Modular
Material of Construction	Metal
Mounting Hardware	Yes
Rack Height	11U
POWER MODULE DIMENSIONS	
Battery Module	3U
Battery Cabinet - Rack Units	19U

PHYSICAL DIMENSIONS	
Physical Dimensions - WxHxD (cm)	48.51 x 60.71 x 77.47 cm
Physical Dimensions - WxHxD (in.)	19.1 x 23.9 x 30.5 in.
Weight (kg)	61.1 kg
Weight (lb)	134.7 lbs.
SHIPPING DIMENSIONS	
Shipping Dimensions - WxHxD (cm)	63.2 x 78.74 x 101.6 cm
Shipping Dimensions - WxHxD (in.)	24.88 x 31 x 40 in.
Weight (kg)	101.15 kg
Weight (lb)	223 lbs.

BCT3L9N125

3-PHASE MODULAR UPS BATTERY CABINET

SPECIFICATIONS CONT.

ENVIRONMENTAL	
Operating Elevation	0 - 10,000 ft (0 - 3,048 m)
Operating Elevation Note	At \leq 1,000m above sea level, de-rate power by 1% per 100m between 1,000m and 3,048m
Operating Relative Humidity	0 - 95 % (non-condensing)
Operating Temperature	32 - 104°F (0 - 40°C)
Operating Temperature Note	Battery life is halved for every 50°F (10°C) increase above 68°F (20°C)
Storage Battery Temperature Note	Optimum battery storage between 5 - 68°F (-15 - 20°C)
Storage Relative Humidity	0 - 95% (non-condensing)
Storage Temperature	5 - 104°F (-15 - 40°C)

CERTIFICATIONS	
Environmental	RoHS Compliant
Safety	cTUVus UL1778, CSA C22.2 No. 107.3-14 CFR 47 FCC Part 15, Subpart B, Class A

WARRANTY	
Product Warranty	One-Year Limited Warranty