

# ideapad 5 (14", 15")

## REFINED FOR LIFE.

The Lenovo™ **IdeaPad™** 5 brings you exceptional features for your digital life with the ideal blend of high performance, reliable connectivity, and immersive entertainment, all in a sleek design. Its Dolby Audio™ speakers with a user-facing setup elevate your audio experience. Plus, AMD Ryzen™ 5000 Series Mobile Processors with Radeon™ graphics deliver the lightning-fast responsiveness you need to get the job done and enjoy entertainment to its fullest.



### SUPREME PERFORMANCE. INFINITE POSSIBILITIES.

Run your most demanding apps all at once with the world's best mobile processors\*. Experience lightning-fast responsiveness and hyper-efficient battery life thanks to industry-leading technology that keeps you productive and entertained from anywhere.

\* 'Best Mobile Processors' is defined as having the highest multi-thread processing performance in each of four (4) classes of Ryzen 5000 series processors. Testing by AMD engineering using the the Cinebench R20 NT benchmark, measuring multithreaded performance of a Ryzen 9 5900HX processor engineering sample vs Core i9-10980HK, Ryzen 7 5800U processor engineering sample vs Core i7-1185G7 processor, the Ryzen 5 5600U processor engineering sample vs Core i5-1135G7 processor, and a Ryzen 3 5400U processor engineering sample vs Core i3-1115G4 processor. Performance may vary. C2M-1.




### WHY YOU SHOULD BUY THE LENOVO IDEAPAD 5 (14", 15")



#### Privacy at your fingertips

The last thing you want is a hacker peeking into your life through your webcam. With the physical privacy shutter, you can block the camera when you don't want to be seen. Using a Post-it note is an outdated trick you can leave behind. It's the simple things that make the **IdeaPad 5** the smart choice, like being able to power up and log in with just a single touch thanks to an optional fingerprint reader on the power button. Now you can set to wake up your laptop when it detects your biometric signature.



#### Maximize your view

Step into the world of your favorite movies and shows with up to an IPS display panel designed to maximize your viewing experience. By increasing the amount of screen compared to the size of the surrounding borders, the **IdeaPad 5** has an incredible 90% Active Area Ratio.



#### A touch of class

This isn't your typical laptop that you carry around—it's a fashion statement. The **IdeaPad 5** is built with a new level of attention to detail, making this machine soft and comfortable to the touch with a durable paint that creates a better user-experience and multiple color options, so you can find the one that best fits you.



#### Options galore

The **IdeaPad 5** comes with a host of options including a USB-C port with power delivery to charge your devices right from your laptop, and Rapid Charge Boost to get your battery charged as quickly as possible with speedy SSD drives, and bountiful memory options, this PC is more than just an everyday laptop, it's an accessory to your lifestyle.

Lenovo™



WWW.LENOVO.COM

# ideapad 5 (14", 15")

## SPECIFICATIONS

Lenovo IdeaPad 5-14ARE-05 | Lenovo IdeaPad 5-14ALC-05 |  
Lenovo IdeaPad 5-15ARE-05 | Lenovo IdeaPad 5-15ALC-05\*

## PERFORMANCE

### Processor

IdeaPad 5-14ALC | IdeaPad 5-15ALC

Up to AMD Ryzen™ 7 5700U Mobile Processor  
with Radeon™ Graphics

IdeaPad 5-14ARE | IdeaPad 5-15ARE

Up to AMD Ryzen™ 7 4800U Mobile Processor  
with Radeon™ Graphics

### Operating System

Windows 10 Home  
Windows 10 S

### Graphics

UMA : AMD Radeon™ Graphics (Integrated Graphics)

### Memory

DDR4 : 4GB / 8GB / 16GB

### Storage

IdeaPad 5 - 14"

SSD PCIe M.2 : Up to 1TB

IdeaPad 5 - 15"

SSD PCIe M.2 : 128GB / 256GB / 512GB / 1TB

Dual Storage : 128GB/256GB + 1TB SATA HDD

### Camera

1 MP HD 720p with Microphone (Array)

### Audio

2 x 2W Speakers with Dolby Audio™ (User-facing)

### Battery<sup>1</sup>

IdeaPad 5 - 14"

MobileMark® 2014 : 11.5 Hours @ 44.5Whr  
14 Hours @ 56.5Whr

1080p Video Playback: 11 Hours @ 44.5Whr  
13.5 Hours @ 56.5Whr

Rapid Charge Boost : 15 min. @ 2 Hours

IdeaPad 5 - 15"

MobileMark® 2014 : 11.5 Hours @ 45Whr  
14 Hours @ 57Whr  
17 Hours @ 70Whr

1080p Video Playback: 10.5 Hours @ 45Whr

13 Hours @ 57Whr  
15.5 Hours @ 70Whr

Rapid Charge Boost : 15 min. @ 2 Hours

## DESIGN

### Display

IdeaPad 5 - 14"

14" FHD (1920 x 1080) IPS, 16:9, 300 nits,  
100% sRGB (Metal only)

14" FHD (1920 x 1080) IPS, 16:9, 300 nits,  
45% NTSC

14" FHD (1920 x 1080) TN, 16:9, 250 nits,  
45% NTSC (Plastic only)

14" HD (1366 x 768) TN, 16:9, 250 nits<sup>2</sup>

IdeaPad 5 - 15"

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits,  
100% sRGB (Metal only)

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits,  
45% NTSC

15.6" FHD (1920 x 1080) IPS, 16:9, 300 nits,  
45% NTSC, On-Cell Touch

15.6" FHD (1920 x 1080) TN, 16:9, 250 nits,  
45% NTSC

### 4-Side Narrow Bezel (90% AAR)

IdeaPad 5 - 14"

Top : 7.6 mm

Left/Right : 2.8 mm

Bottom : 8.3 mm

IdeaPad 5 - 15"

Top : 7.4 mm

Left/Right : 2.9 mm

Bottom : 10.6 mm

### Dimensions (W x D x H)

IdeaPad 5 - 14" | Plastic

(mm) : 321.57 x 211.59 x 17.9

(inches) : 12.66" x 8.33" x 0.7"

IdeaPad 5 - 14" | Metal

(mm) : 321.57 x 211.59 x 16.9

(inches) : 12.66" x 8.33" x 0.67"

IdeaPad 5 - 15" | Plastic

(mm) : 356.67 x 233.13 x 17.9-19.9

(inches) : 14.04" x 9.17" x 0.7"-0.8"

IdeaPad 5 - 15" | Metal

(mm) : 356.67 x 233.13 x 16.9-19.1

(inches) : 14.04" x 9.17" x 0.66"-0.75"

### Weight

IdeaPad 5 - 14" | Plastic

Starting at 1.39-1.45 kg (3.1-3.2 lbs)

IdeaPad 5 - 14" | Metal

Starting at 1.38-1.48 kg (3.04-3.3 lbs)

IdeaPad 5 - 15"

Starting at 1.66-1.8 kg (3.7-3.9 lbs)

### Colors

IdeaPad 5-14ARE

Platinum Grey, Graphite Grey, Light Teal

IdeaPad 5-15ARE (Plastic)

Platinum Grey, Graphite Grey,  
Light Teal, Abyss Blue<sup>5</sup>

IdeaPad 5-15ARE (Metal)

Platinum Grey, Graphite Grey, Abyss Blue<sup>4</sup>

IdeaPad 5-14ALC | IdeaPad 5-15ALC

Platinum Grey, Graphite Grey, Abyss Blue

## WOW FEATURES

### Standard

Privacy Shutter, Windows Cortana  
Smart Login

### Optional

Backlit Keyboard (White)  
Fingerprint Reader (On power button)  
Touch Screen Display<sup>5</sup>  
One-handed Open<sup>6</sup>

## CONNECTIVITY

### WLAN

Up to WiFi 6 (2x2 802.11 ax/ac/a/b/g/n)

### Bluetooth\*

Bluetooth® 5.1

### I/O (Input/Output) Ports<sup>7</sup>

2 x USB 3.1 Gen 1<sup>8</sup>  
1 x Type-C™ USB 3.1 Gen 1<sup>8</sup> + PD 3.0 +  
DisplayPort™ 1.2<sup>9</sup>  
HDMI™ 1.4b, SD Card Reader,  
Audio Jack, DC-In (round)<sup>11</sup>

## PRELOADED SOFTWARE

- Windows 10 Home
- Windows 10 S
- McAfee LiveSafe™
- Microsoft Office
- Lenovo Utility
- Lenovo Vantage
- Alexa<sup>12</sup>
- Mirkat

## OPTIONS & ACCESSORIES



Lenovo 520  
Wireless Mouse



Lenovo USB-C  
3-in-1 Hub



Lenovo 100  
In-Ear Headphone

\* Example of Lenovo  
catalogue naming  
convention



### AMD platform codes

Bristol Ridge-L: ABL, Beema: ABM, Bristol Ridge: ABR, Carrizo-L: ACL, Carrizo: ACZ, Godavari: AGR,  
Kaveri: AKV, Stoney Ridge: ASR, Stoney Ridge: AST (NB), Summit Ridge: ASU, Raven Ridge: ARR,  
Picasso: API, Renoir: ARE, Lucienne: ALC.



WWW.LENOVO.COM

## LENOVO SERVICES

### Warranty Upgrades - On-site/ In-Home Service

Maximizes PC uptime and productivity  
by providing convenient, fast repair  
services in your own home.

### Accidental Damage Protection

Avoid the hassles of unexpected  
repair costs. Provides coverage for  
non-warranted damage incurred under  
normal operating conditions, such as

minor spills, drops or damage to the  
integrated screen.

### Warranty Extensions (1-to-3 Years Total Duration)

This fixed-term, fixed-cost service  
helps accurately budget for PC  
expenses, protect your valuable  
investment and potentially lower the  
cost of ownership over time.



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit [www.lenovo.com](http://www.lenovo.com). Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, ideacentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit [www.lenovo.com/lenovo/us/en/safecom/](http://www.lenovo.com/lenovo/us/en/safecom/) periodically for the latest information on safe and effective computing. ©2021 Lenovo. All rights reserved.