

HPE PROLIANT DL380 GEN10 PLUS 4314 2.4GHZ 16-CORE 1P 32GB-R P408I- A NC BCM57412 8SFF 800W PS SERVER (P43358- B21)

ProLiant DL300 Servers



OVERVIEW

WHAT'S NEW

Do your servers need increased performance in storage,

- Supports 3rd Generation Intel® Xeon® Scalable Processors.
- Support for PCIe Gen4, resulting in improved bandwidth and throughput.
- Support for industry-standard OCP 3.0 Network Adapters.
- Support for Trimodal (NVMe/SAS/SATA) HPE Smart Array controllers.

compute, or expansion?

The HPE ProLiant DL380 Gen10 Plus server is adaptable for diverse workloads and environments, providing you with the right balance of expandability and scalability. Designed for supreme versatility and resiliency, this 2U/2P platform is capable for deployment in multiple environments, built on 3rd Generation Intel® Xeon® Scalable Processors, and backed by a comprehensive warranty. Equipped with PCIe Gen4 capabilities, the HPE ProLiant DL380 Gen10 Plus server offers improved data transfer rates and higher networking speeds.

FEATURES

Built for Some of the Most Demanding Workloads

The HPE ProLiant DL380 Gen10 Plus server is built with foundational intelligence to transform IT with insights that enhance workload performance, placement, and efficiency, delivering better outcomes faster.

Provide real-time operational feedback on server performance and recommendations for fine-tuning BIOS settings to customize for changing business needs.

360-degree Holistic Security

The HPE ProLiant DL380 Gen10 Plus server provides an enhanced, holistic, 360-degree view to security that begins in the manufacturing supply chain and concludes with a safeguarded, end-of-life decommissioning.

HPE ProLiant security begins with the corruption-free manufacture of the server and auditing the integrity of every component – hardware and firmware – to provide verification that the server begins its lifecycle uncompromised through the supply chain.

HPE ProLiant servers provide rapid detection of a security-compromised server, even to the point of not allowing it to boot, verify containment of malicious code, and protect healthy servers.

HPE ProLiant servers provide automated recovery from a security event, including restoration of validated firmware, and facilitating recovery of operating system, application and data connections, providing the fastest path to bring a server back online and into normal operations.

When it's time to retire or repurpose an HPE ProLiant server, one button secure erase speeds and simplifies the complete removal of passwords, configuration settings and data, preventing inadvertent access to previously secured information.

Intelligent Management Automation

The HPE ProLiant DL380 Gen10 Plus server simplifies and automates management tasks, establishing a solid foundation for an open, hybrid cloud platform enabled by composableity.

Embedded in HPE servers, HPE Integrated Lights-Out (iLO) is an exclusive core intelligence that monitors server status, providing the means for reporting, ongoing management, service alerting, and local or remote management to quickly identify and resolve issues.

Automation and software defined control reduces time spent on provisioning and maintenance, as well as reduces deployment times from weeks to mere days.

HPE InfoSight for servers continually analyzes server infrastructure and applies real-world examples of hundreds of thousands of servers to predict and prevent problems before they can adversely affect business operations.

Available in an As-a-Service Experience

The HPE ProLiant DL380 Gen10 Plus server is supported by HPE GreenLake to simplify IT infrastructure management across your entire hybrid estate. With 24x7 monitoring and management, our experts do the heavy lifting to manage your environment with services built into consumption-based solutions.

Hewlett Packard Enterprise provides customers choice in how they acquire and consume IT beyond traditional financing and leasing, offering options that free trapped capital, accelerate infrastructure updates, and provide on-premises pay-per-use consumption with HPE GreenLake.



Technical specifications

HPE ProLiant DL380 Gen10 Plus 4314 2.4GHz 16-core 1P 32GB-R P408i-a NC BCM57412 8SFF 800W PS Server

Product Number (SKU)	P43358-B21
Processor Name	1 Intel® Xeon® Silver 4314 (16 Core, 2.4 GHz, 24MB, 135W)
Processor core available	16 cores
Processor cache	24MB L3
Processor speed	2.4GHz maximum
Power supply type	1 HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply
Expansion slots	8, for detailed descriptions refer to the QuickSpecs
Memory, standard	32 GB (1 x 32 GB) RDIMM
Memory type	HPE DDR4 SmartMemory
Included hard drives	None ship standard, 8 SFF drives supported
Optical drive type	Optional DVD-ROM Optional via Universal Media Bay External support only
System fan features	4 Hot-plug redundant fans, standard
Network controller	Broadcom BCM57412 Ethernet 10Gb 2-port SFP+ Adapter for HPE
Storage controller	HPE Smart Array P408i-a SR Controller and HPE 96W Smart Storage Lithium-ion Battery with 145mm Cable
Product Dimensions (metric)	8.75 x 44.54 x 71. cm
Weight	28.77 kg maximum
Infrastructure management	HPE iLO Standard with intelligent provisioning (embedded), HPE OneView Standard (requires download) (standard) HPE iLO Advanced, and HPE OneView Advanced (optional, requires licenses)
Warranty	3/3/3: Server Warranty includes three years of parts, three years of labor, and three years of onsite support coverage. Additional information regarding worldwide limited warranty and technical support is available at: http://h20564.www2.hpe.com/psc/wc/public/home . Additional HPE support and service coverage, to supplement the product warranty, is available. For more information, visit http://www.hpe.com/support
Drive supported	8 SAS/SATA/SSD 8, 16, or 24 SFF SAS/SATA/SSD, depending on configuration, 8 SFF mid-tray optional, 6 SFF rear drive optional or 4 LFF mid tray optional, 20 SFF NVMe optional, NVMe support via Express Bay will limit maximum drive capacity, depending on model



Most, if not all IT organizations are on a digital transformation journey — each at a different stage. With over 11,000 IT projects conducted and 1.4 million customer interactions each year, HPE Pointnext Services' 15,000+ experts and its vast ecosystem of solution partners and channel partners are uniquely able to help you at every stage of your digital transformation. We bring together technology and expertise to help you drive your business forward and prepare for whatever is next.

Advisory and Professional Services help you accelerate your digital transformation. Operational Services help you remove complexity and respond rapidly to business demands.

Operational Services from HPE Pointnext Services

HPE Pointnext Tech Care provides fast access to product-specific experts, an AI-driven digital experience, and general technical guidance to help enable constant innovation. We have reimagined IT support from the ground up to deliver faster answers and greater value. By continuously searching for better ways to do things—as opposed to just fixing things that break—HPE Pointnext Tech Care helps you focus on achieving your business goals.

- **HPE Datacenter Care** helps modernize and simplify IT operations. Partner with an assigned account team, access technical expertise, an enhanced call experience gives you priority access, choose hardware and software support, implement proactive monitoring to help stay ahead of issues, and access HPE IT best practices and IP.
- **HPE Proactive Care** offers an enhanced call experience and helps reduce problems with personalized proactive reports and advice. This also includes collaborative software support for Independent Software Vendors (ISVs), (Red Hat, VMWare, Microsoft, etc.). [Read more](#)
- **HPE Foundation Care** helps when there is a problem and has a choice of response levels. Collaborative software support is included and provides troubleshooting help for ISVs running on your server. [Read more](#).

Other related services

Defective Media Retention is optional and applies only to Disk or eligible SSD/Flash Drives replaced by HPE due to malfunction.

HPE Service Credits offers a menu of technical services, access additional resources, and specialist skills.

HPE Education Services delivers a comprehensive range of services to support your people as they expand their skills required for a digital transformation.

Consult your HPE Sales Representative or Authorized Channel Partner of choice for any additional questions and support options.



For additional technical information, available models and options, please reference the [QuickSpecs](#)

HPE GREENLAKE

HPE Greenlake is HPE's market-leading IT as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model. HPE GreenLake delivers public cloud services and infrastructure for workloads on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please [explore them here](#).

Make the right purchase decision.
Contact our presales specialists.



© Copyright 2021 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Intel, Intel Xeon, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. All third-party marks are property of their respective owners.

Image may differ from the actual product
[PSN1013486170USEN](#), July, 2021.

Hewlett Packard Enterprise