

PERFORMANCE

Processor

Intel® Xeon® W-2255 (10C / 20T, 3.7 / 4.5GHz, 19.25MB)

Processor Sockets

1x FCLGA2066

Discrete Graphics

NVIDIA® RTX A5000 24GB

Chipset

Intel C422

Memory

8x 32GB RDIMM DDR4-2933 ECC

Memory Slots

8 DDR4 DIMM slots, 4 channels capable

Max Memory

Up to 512GB (8x 64GB RDIMMs) DDR4-2933

M.2 SSD RAID Controller

RAID 0/1

M.2 SSD Drive

1x 1TB SSD M.2 PCIe® NVMe® Opal

HDD Controller

Onboard Intel RSTe SATA

SATA/SAS Drive

1x 2TB HDD 7200rpm 3.5" SATA6Gb/s

Storage Support

- Up to 6x 3.5" SATA HDD / 2.5" SATA HDD / 2.5" SATA SSD + 9x M.2 PCIe SSD + 1x PCIe AIC SSD
- 3.5" HDD up to 6TB each
- 2.5" SATA HDD up to 500GB each
- 2.5" SATA SSD up to 2TB each
- 2.5" SAS HDD up to 600GB each
- M.2 PCIe SSD up to 2TB each
- PCIe AIC SSD up to 480GB each

Audio Chip

High Definition (HD) Audio, Realtek® ALC662 codec

Power Supply

1000W Platinum Fixed

DESIGN

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse

Expansion Slots

- One PCI
- One PCIe 3.0 x8
- Two PCIe 3.0 x4
- Two PCIe 3.0 x16

M.2 Slots

Up to 9x M.2 SSD:

- 2 via onboard slots
- 4 via Quad M.2 to PCIe adapter
- 3 via Single M.2 to PCIe adapter

Bays

- 2x 3.5" disk bay (standard)
- 4x 3.5" disk bay (optional):
2 bays come with 3rd disk or Storage Bay Upgrade Kit
2 bays via flex bay

Flex Bays

2x flex bays, supports the following:

- 2x half-height optical drives
- 2x 5.25" 9.0mm optical drives
- 1x 5.25" 9.0mm optical drive + 2x 3.5"/2.5" SATA SSD/HDD
- 1x 3.5"/2.5" SATA SSD/HDD with Front Access Storage Enclosure
- 1x flex module for the following options:
Tray 1: 9.0mm optical
Tray 2: 15-in-1 USB 3.1 Gen 1 reader, 2x Thunderbolt™, or 4-digit diagnostic display
Port 1 and 2: Front USB 3.1 Gen 1 Type-C or eSATA

Dimensions (WxDxH)

165 x 460 x 440 mm (6.5 x 18.1 x 17.3 inches, with feet)

Weight

24 kg (52.91 lbs, maximum configuration)

CONNECTIVITY

Onboard Ethernet

Intel I219-LM, 1x GbE RJ-45

Card Reader

SD Card Reader

Front Ports

- 1x USB 3.1 Gen 1 (Always On and fast charge)
- 3x USB 3.1 Gen 1
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 2x USB 2.0
- 4x USB 3.1 Gen 1
- 2x PS/2 ports (keyboard / mouse)
- 1x Ethernet (RJ-45)
- 1x line-in (3.5mm)
- 1x line-out (3.5mm)
- 1x microphone (3.5mm)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

Physical Locks

Kensington® Security Slot, 3 x 7 mm

MANAGEABILITY

System Management

Intel® vPro with AMT 11

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

3Y Premier Support Upgrade from 3Y Onsite (5WSOU26649)

CERTIFICATIONS

Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0 (on model 30BE00B7US)
- GREENGUARD®
- RoHS compliant

ISV Certifications

Please visit www.thinkworkstations.com/isv-certifications/

SOFTWARE

Operating System

Ubuntu Linux

MODEL

TopSeller	: Yes	Announce Date	: 2021-09-07
EAN / UPC / JAN	: 196119161401	End of Support	: 2028-01-07

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Kensington MicroSaver 2.0 Cable Lock from Lenovo

4X60N86662

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

Recommended Services

BEST	5Y Lenovo Protect (Premier Support + ADP + KYD + International Upg) (5PS1D67032)
BETTER	5Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67028)
GOOD	4Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67027)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference