

Specifications

Parsec

5600 Pull-Up Table

HPFi



Base/Features

- 1.5" diameter, powder-coated tubular steel upright support
- .188" thick, powder-coated solid steel low-profile base
- Soft, non-marring skid pads on bottom of base
- The upright post is offset on the steel base with a gentle arc towards the center for maximum access while seated
- 1" thick vinyl clad top surface with soft, 1.5" waterfall radius edges on a 18"W x 12"D work surface
- Flat Iron (textured black) top and Silver base

Dimensions

- Overall: 18"W x 12"D x 25.5"H

Warranty

- Limited Lifetime
- Meets or exceeds ANSI/BIFMA 5.5-2014 Desk and Table Standard

Ships

- Fully Assembled by Truck
- Ship Weight: 35 lb
- Ship Cubes: 12
- Freight Class: 150

Environmental & Sustainability

Materials & Resources



Standard material use in products in accordance with the following criteria:

- LEED for Commercial Interiors EA Credit, 50% Construction Waste Diversion (1 point)
- LEED for Commercial Interiors EA Credit, 75% Construction Waste Diversion (1 point)
- ANSI/BIFMA e3-2014e (LEVEL®) Credit 5.10.2, 100% solid waste diversion
- LEED for Commercial Interiors EA Credit 3.3, Resource Reuse 30%, Furniture & Furnishings (1point) - HPFI Lifetime warranty and Second Life program applicable for reuse
- ANSI/BIFMA e3-2014e (LEVEL®) Credit 5.9.4, Extended Product Responsibility - HPFI Second Life program ensures reuse of usable product
- LEED for Commercial Interiors MR Credit, Regional Materials 20% (1 point) - HPFI products are manufactured in High Point, NC and may contribute this point based on project location.