

PERFORMANCE

Processor

Intel® Core™ i7-11850H (8C / 16T, 2.5 / 4.8GHz, 24MB)

Graphics

NVIDIA® GeForce® RTX™ 3070 8GB GDDR6

Chipset

Intel WM590

Memory

1x 16GB SO-DIMM DDR4-3200 Non-ECC

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Max Memory

Up to 64GB DDR4-3200

Storage

512GB SSD M.2 2280 PCIe 4.0x4 Performance NVMe Opal2

Storage Support

Model with RTX 3060/3070/3080 Graphics:
one drive, up to 2TB M.2 2280 SSD

RAID Preset

None

Card Reader

SD Card Reader

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

Speakers

Stereo speakers, 2W x2, Dolby® Atmos®

Camera

1080p + IR with Privacy Shutter

Microphone

2x, Array

Battery

Integrated 90Wh

Max Battery Life

MobileMark® 2018: 10.7 hr

JEITA 2.0: 12.8 hr

Power Adapter

230W Slim Tip

DESIGN

Display

16" WQUXGA (3840x2400) IPS 600nits Anti-glare, 100% Adobe®, HDR 400, Dolby Vision™

Touchscreen

None

Color Calibrator

Factory Color Calibration

Keyboard

Backlit, English

Case Color

Black, Weave

Case Material

CF Hybrid (Top), Aluminum Alloy (Bottom)

Pen

No Support

Dimensions (WxDxH)

359.5 x 253.8 x 17.7 mm (14.15 x 9.99 x 0.7 inches)

Weight

1.81 kg (3.99 lbs)

SOFTWARE

Operating System

Windows® 10 Pro 64, English

Bundled Software

None

CONNECTIVITY

Ethernet

100/1000M (Adapter Needed)

WLAN + Bluetooth®

Intel AX210 11ax, 2x2 + BT5.2

WWAN

None

SIM Card

None

NFC

None

Standard Ports

- 1x power connector
- 1x USB 3.2 Gen 1
- 1x SD card reader
- 1x headphone / microphone combo jack (3.5mm)
- 2x Thunderbolt™ 4 / USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x USB 3.2 Gen 1 (Always On)

Optional Ports

1x HDMI® 2.1 (model with discrete graphics)

Monitor Cable

None

SECURITY & PRIVACY

Smart Card Reader

None

Security Chip

Discrete TPM 2.0

Fingerprint Reader

Touch Style, Match-on-Chip

Physical Locks

Kensington® Nano Security Slot

Other Security

- IR camera for Windows® Hello
- Camera privacy shutter

MANAGEABILITY

System Management

Intel® vPro, DASH

SERVICE

Base Warranty

3-year, Depot

Included Upgrade

3Y Premier Support Upgrade from 3Y Courier/Carry-in
(5WSOT36160)

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- RoHS compliant
- TCO
- ENERGY STAR® 8.0
- EPEAT™ Gold

Mil-Spec Test

Work in progress

MODEL

TopSeller : Yes

EAN / UPC / JAN : 195891760277

Announce Date : 2021-07-20

End of Support : 2028-02-20

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



intel



intel

Recommended Services

BEST	4Y Lenovo Protect (Premier Support + ADP + KYD + 3Y SBTY + International Upg) (5PS1D67024)
BETTER	3Y Lenovo Protect (ADP + KYD + SBTY + International Upg) (5PS1D67023)
GOOD	3Y Lenovo Support (KYD + SBTY + International Upg) (5PS1D67026)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference