

SUPERIOR SERIES INL2158



INL2158 - 1080p - 4000 ☀ - 16:9 Aspect Ratio

The next generation of Laser Projection is here! With this multi-purpose, multi-use range of laser projectors, you get far more than an image on the wall. Content bursts to life, and viewing becomes an absolute pleasure and a next-level experience in any environment. Viewing presentations in the workplace offers much more crisp detail and readability. Engage more in the classroom and have peace of mind that you and your students or classmates are using the latest cutting-edge, environmentally friendly, energy-efficient display technology on the market.

Features

Environmentally-Friendly Laser Technology

The Superior Series, part of our Quantum Laser line of projectors, are deployed with solid-state laser light source technology. The complete Quantum Laser range is lamp, filter, mercury, and maintenance-free. The ultra-low energy usage for its class and long-standing durability and performance offers outstanding value and low cost of ownership.

4K Support

Simply stunning image quality with up to 1920 x 1200 native resolution and HDMI 2.0 (HDCP 2.2) 4K support. HDR compatible for like life texture details and improved image depth perception.

SuperSmartProject

Our SuperSmartProject suite of power-saving, power optimisation, and utilization features and functions combine ease of use and energy saving for your everyday use. Instant power on, signal power on, instant power off, auto power-off, 10 step illumination reduction, and Dynamic Black optimization all enhance your viewing experience while optimizing energy usage.

Flexible Installation

Flexibility for almost every surface with front, rear, and ceiling placement as well as floor to ceiling and ceiling to floor projection, full 360-degree placement across the horizontal axis and not forgetting both landscape and portrait modes ideal for retail display purposes, fixed installations, bars, clubs, and restaurants.

Image

Projection Technology	Texas Instruments DLP®
Panel Size	0.47"
Native Resolution	1080p
Pixels	1920 x 1080
Aspect Ratio	16:9
Contrast Ratio	300000:1
Brightness (Lumens)	4000
Light Source	Quantum Laser™
Light Source Life Maximum Hours	30000
Maximum Supported Resolution	4096 x 2160
Horizontal Sync. Range (KHz)	15 ~ 100

Vertical Sync. Range (Hz)	23 ~ 120
Uniformity (%)	85

Optical

Lens	1.3x
Lens Zoom Adjustment	Manual
Optional Lenses	-
Image Offset (%)	-
Focal Length (mm)	-
F-Stop	-
Vertical Lens shift (%)	-
Horizontal Lens shift (%)	-
Keystone Adjustment	Automatic/Manual
Vertical Keystone Correction	±30°
Horizontal Keystone Correction	±30°
Projection Factor	1.21 ~ 1.59:1
Projection Distance (Meters/Feet)	1.0 ~ 8.1 / 3.28 ~ 26.57
Optical Zoom	Manual
Digital Zoom Demagnification / Magnification	0.8x ~ 2.0x
Focus Adjustment	Manual

Connectivity

Analog Input	VGA, Composite Video
Analog Output	-
Digital Input	HDMI™ 2.0, HDMI™ 1.4
Digital Output	-
Audio Input	3.5mm
Audio Output	3.5mm
Control	RS232, RJ45, Micro USB
Service	Micro USB
Powered USB for Wireless Dongle	USB-A
3D Sync	-
Full 3D Support	Yes
3D Formats	All Major Formats Supported
Document Reader	Yes
Video Player	Yes
Photo Viewer	Yes
Music Player	Yes
PC Less Compatibility	-

Power

Power Supply	100 ~ 240 V AC; 50 - 60 Hz
Power Consumption Max (W)	211
Power Consumption Min. (W)	157
Power Consumption Network Standby (W)	<2
Power Consumption Standby (W)	<0.5

General

Dimensions (W x H x D) (mm / in)	337 x 265 x 119.3 / 13.27 x 10.4 x 4.7
Product Weight (Kilograms/Pounds)	4.6 / 10.14
Fan Noise (dB)	30
Audio	10
Operating Temperature (Celsius/Fahrenheit)	0 ~ 40 / 32 ~ 104
Operating Humidity (%)	0 ~ 85
Max Operating Altitude (meters / feet)	10000 / 32808
Storage Temperature (Celsius/Fahrenheit)	-10 ~ 60
Storage Humidity (%)	0 ~ 85
Security	Kensington Lock Port™, PIN & Timer Functions
In the Box	Projector, IR Remote Control (no Batteries), Power Cord, VGA Cable, Projector, Setup Guide.
Safety and Regulatory	CE, EAC, RoHS, cTUVus, CCC, FCC, FDA, NOM, PSB, BIS
Environmental	WEEE, RoHS