

PERFORMANCE**Processor**

Intel® Core™ i5-11400T (6C / 12T, 1.3 / 3.7GHz, 12MB)

Graphics

Integrated Intel UHD Graphics 730

Chipset

Intel B560 chipset

Memory

1x 8GB SO-DIMM DDR4-2666

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Max Memory

Up to 64GB DDR4-2933

Storage

128GB SSD M.2 2242 PCIe NVMe

Storage Support

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 SSD up to 2TB

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC233VB codec

Speakers

1.5Wx1

Power Supply

135W 89% Adapter

DESIGN**Keyboard**

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

Case Color

Black

Stand

Stand

Adapter Cage

None

Toolless Chassis Screw

None

Dust Filter

None

VESA Mount

None

Form Factor

Tiny (1L)

Dimensions (WxDxH)

179 x 182.9 x 36.5 mm with rubber feet (7.05 x 7.2 x 1.44 inches with rubber feet)

Weight

- With VESA mount & ODD box|1.74 kg (3.84 lbs)
- Tiny only|1.25 kg (2.76 lbs)

CONNECTIVITY**Ethernet**

Integrated 100/1000M

WLAN + Bluetooth®

Intel AX201 11ax, 2x2 + BT5.2

Front Ports

- 1x USB-C 3.2 Gen 1
- 1x headphone / microphone combo jack (3.5mm)
- 1x USB 3.2 Gen 2 (Always On and fast charge)

Rear Ports

- 1x DisplayPort™
- 2x USB 3.2 Gen 1
- 1x Ethernet (RJ-45)
- 2x USB 3.2 Gen 2
- 1x HDMI®

Optional Rear Ports

USB-C 3.2 Gen 1

Monitor Cable

None

SECURITY & PRIVACY**Security Chip**

Discrete TPM 2.0, TCG certified

Fingerprint Reader

No fingerprint reader

Physical Locks

No physical locks

Kensington® Cable Lock

None

Chassis Intrusion Switch

Chassis Intrusion Switch

MANAGEABILITY**System Management**

None

SERVICE**Base Warranty**

3-year, Onsite

Included Upgrade

None

CERTIFICATIONS**Green Certifications**

- RoHS compliant
- ENERGY STAR® 8.0
- EPEAT™ Gold

Mil-Spec Test

MIL-STD-810H military test passed

SOFTWARE**Operating System**

Windows® 10 Pro 64, English

Bundled Software

None

MODEL

TopSeller : Yes

Announce Date : 2021-08-30

EAN / UPC / JAN : 195890269931

End of Support : 2027-11-27



intel

Premier Support - A direct 24x7x365 line to our most elite technicians.






Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management



Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference