# GV-EBD8813 AI 8MP H.265 4.3x Zoom Super Low Lux WDR Pro IR Eyeball IP Dome



- Al Deep learning: Al Perimeter Protection & Classification (Human, Vehicle)
- 1/2.8" progressive scan super low lux CMOS sensor
- Triple streams from H.265, H.264 or MJPEG
- Wide Dynamic Range Pro (WDR Pro)
- Min. illumination at 0.003 lux
- Up to 20 fps at 3840 x 2160
- Intelligent IR
- Day and night function (with removable IR-cut filter)
- Motorized varifocal lens for remote focus / zoom adjustment
- 3-axis mechanism (pan / tilt / rotate)
- IR distance up to 40 m (130 ft)
- Vandal resistance (IK10 for metal casing)
- Ingress protection (IP67)
- Built-in micro SD card slot (SD / SDHC / SDXC / UHS-I) for local storage
- Built-in microphone
- DC 12V / PoE (IEEE 802.3af)
- ONVIF (Profile G, S, T) conformant

### Introduction

The Eyeball Dome IP Camera is an outdoor, network camera equipped with an automatic IR-cut filter and IR LEDs for day and night surveillance. The camera supports H.265 video codec to achieve better compression ratio while maintaining high quality pictures at reduced network bandwidths. GV-EBD8813 adheres to IK10 and IP67 standards, and can be powered through PoE.


Empowered by deep learning algorithms, AI technology distinguishes human and vehicles from other moving objects. Integrated with GeoVision Video Management Software (VMS), it supports AI perimeter protection, real time alert, events playback and more.

### **Deep Learning Function**

**Face Detection** 



AI Perimeter Protection (Intrusion, Crossing Line Entering Area, Leaving Area)




**People Counting** 



Note: The integration of AI events of the camera to GV-VMS is coming soon.

## Dimensions



# **Specifications**

Camera			
Image Sensor		1/2.8" progressive scan super low lux CMOS	
Picture Elements		3840 (H) x 2160 (V)	
Minimum	Color	0.003 Lux (F1.5, AGC ON)	
Illumination IR ON		0 Lux	
Shutter Speed		Auto / Manual (1 ~ 1/100000 sec)	
White Balance		Auto / Manual	
Gain Control		Auto / Manual	
S/N Ratio		56 dB	
WDR		WDR Pro	
Dynamic Range		120 dB	
Lens			
Megapixel		8 MP	
Day / Night		Yes (with removable IR-cut filter)	
Lens Type		Motorized varifocal lens	
Focal Length		2.8 ~ 12 mm	
Maximum Aperture		F/1.6	
Mount		Ø 12 mm	
Horizontal FOV		107° ~ 29°	
	Focus	Auto / Manual	
Operation	Zoom	4.3x Optical Zoom	
	Iris	Fixed	
IR LED Quantity		2 IR LEDs	
Max. IR Distance		40 m (130 ft)	
Operation			
Video Compression		H.265, H.264, MJPEG	
Video Streaming		Triple streams	
Frame Rate		20 fps at 3840 x 2160, 25 fps at 3072 x 1728 / 2560 x 1440, 30 fps at 1920 x 1080 (60 / 50 Hz) *The frame rate and performance may vary depending on the number of connections and data bitrates (different scenes).	
Video Analytics		Motion Detection, Tampering Alarm, Audio Detection *Tampering alarm and audio detection are only accessible through the camera's Web interface, which can be used to trigger alerts such as e-mail and FTP.	
Image Setting		Brightness, Contrast, Saturation, Sharpness, Flicker-less, Image Orientation (Flip, Mirror, 0°, 90°, 180°, 270°-including Corridor format)	
Audio Compressio	on	G.711	

Audio Support		One-way Audio	
Deep Learning Fur	nction		
AI Analytics		Intrusion, Crossing Line, Entering Area, Leaving Area (Human & Vehicle classification) Face Detection, People Flow Counting, Crowd Density Monitoring	
Video Resolution			
Main Stream		3840 x 2160 (Default), 2944 x 1656, 2592 x 1944, 2560 x 1440, 1920 x 1080	
Sub Stream		1920 x 1080, 1280 x 720, 720 x 576, 704 x 288, 640 x 360 (Default), 352 x 288	
Third Stream (Closed by Default)		720 x 576, 704 x 288, 640 x 360, 352 x 288	
Network			
Interface		10/100 Ethernet	
Protocol		ARP, DHCP, DDNS, DNS, DynDNS, FTP, HTTP, HTTPS, ICMP, IGMP, IPv4, NTP, PPPoE, RTCP, RTP, RTSP, SMTP, SNMP, TCP, UDP, UPnP, ONVIF (Profile G, S, T)	
Mechanical			
Camera Angle Adjustment	Pan	0° ~ 360°	
	Tilt	0° ~ 75°	
	Rotate	0° ~ 360°	
	Power	DC Jack (DC 12V, 1.25A), POE	
	Ethernet	RJ-45	
Connectors	Audio	1 In (built-in microphone)	
	Local Storage	Micro SD card slot (SD/SDHC/SDXC/UHS-I, Class 10) *UHS-II card types are not supported.	
General			
Environment Temperature	Start-up Operation	-30°C ~ 60°C (-22°F ~ 140°F)	
Humidity		0% ~ 95% (no condensation)	
Power Source		12V DC / PoE (IEEE802.3af)	
Max. Power Consumption		8.16W	
Dimensions		Ø 129 x 110 mm (Ø5.1" x 4.3")	
Weight		0.67 kg (1.48 lb)	
Ingress Protection	on	IP67	
Vandal Resistance		IK10 for metal casing	
Regulatory		CE, FCC, RoHS compliant	
Web Interface			
Installation Man	agement	Web-based configuration	
Maintenance		Firmware upgrade through Web Browser or GV-IP Device Utility	
Access from Web Browser		Live View, Video Recording, Change Video Quality, Bandwidth Control, Image Snapshot, Defog, Digital Zoom, Text Overlay, Image Masking	
Language		Czech, English, French, German, Hungarian, Italian, Japanese, Polish, Portuguese, Russian, Spanish, Traditional Chinese	
Web Interface			
Software Supported		GV-VMS (V17.4.1 / V18.2.1), GV-DVR / NVR (V8.9.1), GV-Control Center (V3.8.0), GV-Recording Server / Video Gateway (V2.0.0), GV-Edge Recording Manager Win version (V2.0.0), GV-Redundant / Failover Server (V1.2.0)	
Smart Device Access		GV-Eye for iOS and Android	
Live Viewing		Browser (IE, Edge, Chrome), Mobile App	

#### Note:

- 1. It is required to apply patch files to all or some of the supported software.
- 2. Do not use clothes or any ordinary material to clean the camera cover since they may result in scratches.
- 3. Specifications are subject to change without notice.

### **Packing List**

- 1. GV-EBD8813 IR Eyeball Dome
- Drill Template Paster
  Download Guide
- 2. Waterproof Rubber Set
- 3. Screw kit

GV-EBD8813

# 

Model No.	Name	Details
GV-Mount107 (must be used with GV-Mount212P)	Pendant Bracket	Dimensions: Ø 120 x 334 mm (Ø 4.72" x 13.15") Weight: 0.74 kg (1.63 lb)
GV-Mount211P	Wall Mount and Junction Box	Dimensions: Ø 233 x 125 x 125 mm (Ø 9.2" x 4.9" x 4.9" Weight: 1 kg (2.2 lb)
GV-Mount212P	Wall Box Mount	Dimensions: Ø 126 x 36 mm (Ø 5.0" x 1.4") Weight: 0.22 kg (0.48 lb)
GV-Mount300-2	Convex Corner Mount	Dimensions: 137 x 233 x 160 mm (5.4" x 9.17" x 6.3") Weight: 1.65 kg (3.64 lb)
GV-Mount310-2	Concave Corner Mount	Dimensions: 111.2 x 369.9 x 210 mm (2.6" x 11.4" x 6.6") Weight: 1.65 kg (3.64 lb)
GV-Mount420 (must be used with GV-Mount211P)	Pole Mount Bracket	Dimensions: Ø 120 x 120 x 53 mm (Ø 4.7" x 4.7" x 2.1") Weight: 0.45 kg (0.99 lb) Steel Strap Diameter: Ø 67 ~ 127 mm (Ø 2.6" ~ 5")
GV-Mount704 (must be used with GV-Mount107)	Extension Tube	Dimensions: Ø 3.5 x 10 or 20 or 30 or 50 cm (Ø 1.38 x 3.9 o 7.9 or 11.8 or 19.7") Weight: 225 g or 360 g or 500 g or 780 g (0.5 lb or 0.79 lb or 1.1 lb or 1.72 lb)
GV-PA191	Power over Ethernet (PoE) Adapter	The GV-PA191 is a Power over Ethernet (PoE) adapter designed to provide power to the IP device through a single Ethernet cable.
GV-POE Switch		The GV-POE Switch is designed to provide power along with network connection for IP devices. The GV-POE Switch is available in various models with different numbers and types of ports.
Power Adapter		Contact our sales representatives for the countries and areas supported