

VESA 75/100 HD AMPs Mount (26mm)


VESA compatible tablet connection featuring heavy-duty universal AMPs base for high vibration environments

SKU: MVU232
MSRP: \$99.99

The VESA 75/100 HD AMPs (26mm) Mount is a versatile solution to positioning a device in any vehicle that requires vibration dampening. The base features a drill down universal AMPs base that easily attaches to flat surfaces. Devices attach to the mount via VESA 75x75mm, 100x50mm and 100x100mm configurations it will accommodate most IPCs and a variety of other devices.

The body of the mount features cable management and a robust, corrosion-resistant mount arm that can be adjusted to reach the optimum viewing and operating angle. It features two rubber coated ball joints which provide vibration and shock reduction. To keep the device in place the robust arm and rubber coated ball joints provide an increased holding strength. The body of the mount has a slim profile to allow it to fit into tight spaces and features a lever which modifies the force put onto its joints. For public environments that require theft prevention, an optional security feature is available.

- Compatible with devices that utilize VESA 75x75mm, 100x50mm and 100x100mm patterns
- Drill down base has an AMPs 30x38mm pattern for universal compatibility
- Certified vibration and shock resistant MIL-STD-810G 514.7
- Built with two 26mm spherical rubber coated ball joints to provide maximum holding strength
- Made with corrosion-resistant material making it ideal for mixed element environments
- Features cable management, 360 degree rotation, shock and vibration resistance, and near infinite adjustability
- Mount features two 26mm ball joints for increased hold capacity
- Optional locking lever for usage in public spaces



BENEFITS

- Configurable
- Expand Usability
- Ease of Use
- High Quality
- Ergonomic
- Increase Productivity

FEATURES



360° Rotation



Built-In Security



Cable Management



Component Based



High Grade Material



Quick Positioning

The Joy Factory Inc.

16811 Hale Ave Bldg D, Irvine, CA 92606 | sales@thejoyfactory.com | T : 949.216.8869 | F : 949.216.8869 | www.thejoyfactory.com



Protect Secure Position



TECHNICAL SPECIFICATIONS



Material: Aluminum Alloy
 Weight: 1.41 lbs
 Arm Length: 5.25" x 1
 Ball Joint Size: 26mm (1")
 Total Length: 7.12"
 Mount Load Capacity: Up to 10 lbs
 Tablet Connection: Universal
 Base Specifications: Affixes via AMPs 30x38mm pattern

The information on this data sheet is subject to change at any time at the discretion of The Joy Factory

VESA 75/100 HD AMPs Mount
 (26mm)

SKU: MVU232
Product type: Mounts
MSRP: \$99.99

PRODUCT SPECIFICATIONS

Compatible with: Universal
 Product height: 7.12 in
 Product width: 4.76 in
 Product thickness: 4.76 in
 Product weight: 1.41 lb
 Package height: 3.5 in
 Package width: 8.5 in
 Package depth: 13.75 in
 Package weight: 3.9 lb
 UPC: 810041120441
 Warranty: 3 Year
 Certifications: MIL-STD-810G
 Rating: N/A
 Package content: