

### PERFORMANCE

#### Processor

AMD Ryzen™ 7 PRO 5850U (8C / 16T, 1.9 / 4.4GHz, 4MB L2 / 16MB L3)

#### Graphics

Integrated AMD Radeon™ Graphics

#### Chipset

AMD SoC Platform

#### Memory

1x 8GB SO-DIMM DDR4-3200

#### Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

#### Max Memory

Up to 64GB DDR4-3200

#### Storage

256GB SSD M.2 2280 PCIe x4 NVMe Opal2

#### Storage Support

One drive, up to 128GB M.2 2242 SSD or 1TB M.2 2280 SSD

#### Card Reader

MicroSD Reader

#### Optical

None

#### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

#### Speakers

Stereo speakers, 2W x2, Dolby® Audio™

#### Camera

720p with Privacy Shutter

#### Microphone

2x, Array

#### Battery

Integrated 45Wh

#### Max Battery Life

MobileMark® 2018: 11.8 hr  
JEITA 2.0: 12.3 hr

#### Power Adapter

65W USB-C (2-pin)

### DESIGN

#### Display

14" FHD (1920x1080) IPS 250nits Anti-glare

#### Touchscreen

None

#### Keyboard

Non-backlit, English

#### Case Color

Black

#### Case Material

PC + ABS (Top), PC + ABS (Bottom)

#### Dimensions (WxDxH)

331 x 235 x 20.4 mm (13.03 x 9.25 x 0.80 inches)

#### Weight

1.59 kg (3.49 lbs)

### SOFTWARE

#### Operating System

Windows® 10 Pro 64, English

#### Bundled Software

None

### CONNECTIVITY

#### Ethernet

100/1000M

#### WLAN + Bluetooth®

11ax, 2x2 + BT5.2

#### WWAN

None

#### SIM Card

None

#### NFC

None

#### Standard Ports

- 1x Ethernet (RJ-45)
- 1x HDMI® 2.0
- 1x Side docking connector
- 1x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 2.0 and DisplayPort™ 1.4)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 2.0 and DisplayPort 1.4)
- 1x USB 3.2 Gen 1 (Always On)
- 1x microSD card reader

#### Monitor Cable

None

### SECURITY & PRIVACY

#### Smart Card Reader

None

#### Security Chip

Discrete TPM 2.0

#### Fingerprint Reader

None

#### Physical Locks

Kensington® Security Slot

#### Other Security

Camera privacy shutter

### MANAGEABILITY

#### System Management

DASH

### SERVICE

#### Base Warranty

1-year, Depot

#### Included Upgrade

None

### ACCESSORIES

#### Bundled Accessories

None

### CERTIFICATIONS

#### Green Certifications

- TCO
- RoHS compliant
- ENERGY STAR® 8.0
- EPEAT™ Gold

#### Mil-Spec Test

MIL-STD-810H military test passed

### MODEL

TopSeller : Yes

Announce Date : 2021-08-13

EAN / UPC / JAN : 196118544779

End of Support : 2027-12-04



AMD

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences  
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



AMD



AMD



AMD

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference