



ZX70 FULLY RUGGED TABLET



- Qualcomm® Snapdragon™ 660, Octa-core Processor
- Verified as Android enterprise recommended
- 7" LumiBond® display with Getac sunlight readable technology and glove-enabled capacitive touchscreen
- 6ft drop, MIL-STD-810H and IP67 certified
- Optional barcode reader, RFID reader



Office dock



Vehicle dock



Specifications

Operating System

Android™ 10.0

Mobile Computing Platform

Qualcomm® Snapdragon™ 660, Octa-core 1.95GHz
Max. 2.2GHz

VGA Controller

Qualcomm® Adreno™ 512 GPU

Display

7" IPS TFT LCD HD (1280 x 720)
Protection film
LumiBond® display with Getac sunlight readable technology
Capacitive multi-touch screen

Storage & Memory

4GB LPDDR4
64GB eMMC

Keyboard

Power button
3 tablet programmable buttons

Pointing Device

Touchscreen
- Capacitive multi-touch screen

I/O Interface

8M pixels webcam x 1
12M pixels auto focus rear camera x 1
DC in Jack x 1
USB 2.0 (Host) x 1
MicroUSB 2.0 (Client) x 1
MicroSD x 1
Docking connector (Pogo / JAE) x 1
Optional: RF antenna pass-through for GPS and WWAN

Communication Interface

Wi-Fi 802.11ac
Bluetooth (v5.0)ⁱ
Dedicated GPS
Optional: 4G LTE mobile broadband

Security Feature

Optional: Contactless HF RFID / NFC combo readerⁱⁱⁱ
Optional: Barcode reader

Power

AC adapter (25W, 100-240VAC, 50/60Hz)
Li-ion battery (3.8V, typical 8480mAh; min. 8220mAh)

Dimension (W x D x H) & Weight

218 x 142 x 27mm (8.58" x 5.6" x 1.08")
762g (1.68lbs)^{iv}

Rugged Feature

MIL-STD-810H certified
IP67 certified
Vibration & 6ft (1.8m) drop resistant^v
Optional: ANS/UL 121201, CSA C22.2 NO. 213 (Class I, Division 2, Groups A, B, C, D)

Environmental Specification

Temperature^{vi}:
- Operating: -21°C to 60°C / -6°F to 140°F
- Storage: -40°C to 71°C / -40°F to 160°F
Humidity:
- 95% RH, non-condensing

Pre-installed Software

Getac File Browser
Getac Camera
Getac Input Method
DeployeXpress Client
Getac settings and Google applications (Search, Chrome, Gmail, Maps, YouTube, Play, Drive, Play music, Play movies, Duo and photos)

Accessories

AC adapter (25W; 12V/2A, 100-240VAC; 50/60Hz)
Capacitive stylus with tether
Pen holder
Wrist strap

Optional:

Carry bag
AC adapter (25W; 12V/2A, 100-240VAC; 50/60Hz)
Office dock AC adapter (60W, 110-240VAC)
DC-DC vehicle adapter (120W, 11-32VDC)
Capacitive stylus with tether
Protection film
Shoulder strap (2-point)
Wrist strap
Rotating hand strap with kickstand and stylus holder
USB to RS232 converter cable
Docking connector to HDMI converter cable
Vehicle dock
Office dock

Bumper-to-Bumper Warranty

Accidents can take your equipment out of service when you least expect it, especially in a rugged environment, which can cause costly equipment downtime.

That is why Getac has introduced accidental damage as standard under our Bumper-to-Bumper warranty, to help minimize your enterprise IT costs. Bumper-to-Bumper is your hassle-free guarantee. That means you can depend on us to have your unit back in service within days.

Standard

3 years Bumper-to-Bumper

- i Bluetooth performance and connectable distance may be subject to interference with the environments and performance on client devices, users may be able to reduce effects of interference by minimizing the number of active Bluetooth wireless devices that is operating in the area.
- ii 13.56MHz contactless HF RFID/NFC reader (ISO 15693, 14443 A/B, Mifare and FeliCa™ compliant).
- iii HF RFID/NFC combo reader applies to US & EU.
- iv Weight and dimensions vary from configurations and optional accessories.
- v Drop test results vary from configurations and optional accessories.
- vi Tested by an independent third-party test lab following MIL-STD-810H.
- vii Android enterprise recommended rugged devices deliver a consistent set of features verified by Google with an elevated device baseline, increased security standards and enterprise-focused features and behaviors to meet the needs of users. Google and Android are trademarks of Google LLC.

ZX70

Fully Rugged Tablet



Docking Solutions

	Getac-made Vehicle Dock (JAE)	Havis Vehicle Dock (Pogo, power only)	Havis Vehicle Dock (JAE)	Gamber-Johnson Charging Cradle (Pogo)	Havis Vehicle Dock (Pogo)	Office Dock (JAE)	Office Dock (Pogo)
Serial Port	1	--	1	--	1	--	--
Speaker	1	--	--	--	--	--	--
Audio Output	1	1	1	--	1	1	1
DC in Jack	1	1	1	1	1	1	1
USB	USB Host x 2	--	USB2.0 x 2	--	USB2.0 x 2	USB Host x 2 MicroUSB Client x 1	USB Host x 2
LAN	1	--	1	--	1	1	1
HDMI	1	--	1	--	--	1	--
RF Antenna Connector	(WWAN, GPS)	(WWAN, GPS)	(WWAN, GPS)	--	(WWAN, GPS)	--	--

Getac

GETAC TECHNOLOGY CORPORATION

5F, Building A, No. 209, Section 1, Nangang Rd.,
Nangang Dist., Taipei City, 11568, Taiwan, R.O.C.
Tel : +886 2 2785 7888
globalmarketing@getac.com | www.getac.com



Copyright © 2021 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.
Information provided herewith is for reference only,
available specification shall be subjected to quotation by request. V01M08Y21WWW