

### PERFORMANCE

#### Processor

Intel® Core™ i3-1115G4 (2C / 4T, 3.0 / 4.1GHz, 6MB)

#### Graphics

Integrated Intel UHD Graphics

#### Chipset

Intel SoC Platform

#### Memory

8GB Soldered DDR4-3200

#### Memory Slots

- Memory soldered to systemboard, no slots, dual-channel (8GB, 12GB, or 16GB model)
- Memory soldered to systemboard, no slots, dual-channel (8GB, 12GB, or 16GB model)

#### Max Memory

8GB soldered memory, not upgradable

#### Storage

256GB SSD M.2 2242 PCIe 3.0x4 NVMe

#### Storage Support

One drive, up to 512GB M.2 2242 SSD or 512GB M.2 2280 SSD

#### Card Reader

4-in-1 Card Reader

#### Optical

None

#### Audio Chip

High Definition (HD) Audio

#### Speakers

Stereo speakers, 2W x2, Dolby® Audio™

#### Camera

720p

#### Microphone

2x, Array

#### Battery

Integrated 52.5Wh

#### Max Battery Life

- Local video (1080p) playback: 11 hr
- MobileMark® 2014: 10 hr

#### Power Adapter

65W Round Tip (2-pin, Wall-mount)

### DESIGN

#### Display

14" FHD (1920x1080) IPS 250nits Glossy, 45% NTSC, Touch

#### Touchscreen

10-point Multi-touch

#### Keyboard

Non-backlit, English

#### Case Color

Abyss Blue

#### Surface Treatment

Metallic Painting

#### Case Material

PC + ABS (Top), PC + GF (Bottom)

#### Pen

None

#### Dimensions (WxDxH)

321.5 x 217.5 x 17.9-20.9 mm (12.65 x 8.56 x 0.70-0.82 inches)

#### Weight

1.5 kg (3.3 lbs)

### SOFTWARE

#### Operating System

Windows® 10 Home in S mode, English

#### Bundled Software

Office Trial

### CONNECTIVITY

#### Ethernet

None

#### WLAN + Bluetooth®

11ac, 2x2 + BT5.0

#### WWAN

None

#### SIM Card

None

#### NFC

None

#### Standard Ports

- 1x USB-C 3.2 Gen 1 (support data transfer and Power Delivery)
- 1x Power connector
- 1x Card reader
- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)

### SECURITY & PRIVACY

#### Security Chip

Firmware TPM 2.0

#### Fingerprint Reader

Touch Style

#### Other Security

Camera privacy shutter

### SERVICE

#### Base Warranty

1-year, Depot

#### Included Upgrade

None

### ACCESSORIES

#### Bundled Accessories

None

### CERTIFICATIONS

#### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

### MODEL

TopSeller : No

EAN / UPC / JAN : 195477707979

Announce Date : 2020-11-27

End of Support : 2026-11-30



## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.


## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo USB-C Mini Dock\_US

40AU0065US

Expand Your Potential with An Universal Mini Dock; Lenovo understands that modern business depends on a wide variety of PC's and even brands to meet their business needs. To make this easier Lenovo USB-C Mini dock is ...

## Recommended Services

BEST	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73723)
BETTER	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0K75721)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K75704)

For a full list of accessories and services, please visit: <https://smartfind.Lenovo.com>

Lenovo

**PSREF**  
Product Specifications  
Reference