

## PERFORMANCE

### Processor

Intel® Core™ i5-10400T (6C / 12T, 2.0 / 3.6GHz, 12MB)

### Graphics

Integrated Intel UHD Graphics 630

### Chipset

Intel B460

### Memory

2x 4GB SO-DIMM DDR4-2666

### Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

### Max Memory

Up to 16GB DDR4-2666

### Storage

256GB SSD M.2 2242 PCIe NVMe

### Optane™ Memory

None

### Storage Support

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 SSD up to 512GB
- Optional Intel Optane Memory, M.2

### Card Reader

3-in-1 Card Reader

### Optical

9.0mm DVD±RW

### Audio Chip

High Definition (HD) Audio

### Speakers

3Wx2

### Camera

720p

### Microphone

Mono

### Power Supply

90W Adapter Black

## DESIGN

### Display

21.5" FHD (1920x1080) IPS 250nits

### Touchscreen

10-point Multi-touch

### Keyboard

USB Calliope Keyboard, Black, English

### Mouse

USB Calliope Mouse, Black

### Expansion Slots

Two M.2 slots (one for WLAN, one for SSD)

### Case Color

Black

### Stand

AIO Stand

### Form Factor

AIO (21.5 inches)

### Dimensions (WxDxH)

490.5 x 185 x 417.68 mm (19.31 x 7.28 x 16.44 inches)

### Weight

5.5 kg (12.13 lbs)

## CONNECTIVITY

### Ethernet

Integrated 100/1000M

### WLAN + Bluetooth®

11ac, 2x2 + BT5.0

### Rear Ports

- 1x USB 3.2 Gen 1
- 1x power connector
- 1x Ethernet (RJ-45)
- 1x HDMI®-out 1.4
- 2x USB 2.0

### Left Ports

- 1x headphone / microphone combo jack (3.5mm)
- 1x card reader
- 1x USB 3.2 Gen 1

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications

- ErP Lot 3 and Lot 7
- RoHS compliant

## SOFTWARE

### Operating System

Windows® 10 Home 64, English

### Bundled Software

None

## MODEL

TopSeller : No

Announce Date : 2021-01-11

EAN / UPC / JAN : 195235133163

End of Support : 2026-05-15



## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

**Lenovo**

**PSREF**  
Product Specifications  
Reference