

## PERFORMANCE

### Processor

Intel® Core™ i7-11370H (4C / 8T, 3.3 / 4.8GHz, 12MB)

### Graphics

Integrated Intel Iris® Xe Graphics

### Chipset

Intel SoC Platform

### Memory

16GB Soldered LPDDR4x-4266

### Memory Slots

Memory soldered to systemboard, no slots, dual-channel

### Max Memory

16GB soldered memory, not upgradable

### Storage

512GB SSD M.2 2280 PCIe 3.0x4 NVMe

### Storage Support

One drive, up to 1TB M.2 2280 SSD

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

### Speakers

Stereo speakers, 2W x2, Dolby® Atmos®, Harman Speakers

### Camera

IR & 720p + ToF Sensor

### Microphone

2x, Array

### Battery

Integrated 61Wh

### Max Battery Life

MobileMark® 2014: 18 hr

MobileMark 2018: 13 hr

Local video (1080p) playback@150nits: 20.6 hr

### Power Adapter

65W USB-C Slim (3-pin)

## DESIGN

### Display

14" 2.8K (2880x1800) IPS 400nits Glossy, Touch, 90Hz, 100% sRGB, Dolby Vision™, Glass

### Touchscreen

10-point Multi-touch

### Keyboard

Backlit, English (US)

### Case Color

Slate Grey

### Surface Treatment

Anodizing Sandblasting

### Case Material

Aluminium (Top), Aluminium (Bottom)

### Dimensions (WxDxH)

312.4 x 221.4 x 14.6-16.9 mm (12.29 x 8.72 x 0.57-0.67 inches)

### Weight

1.38 kg (3.04 lbs)

## SOFTWARE

### Operating System

Windows® 11 Pro 64, English

### Bundled Software

Office Trial

## CONNECTIVITY

### Ethernet

None

### WLAN + Bluetooth®

11ax, 2x2 + BT5.1

### Standard Ports

- 1x Headphone / microphone combo jack (3.5mm)
- 1x USB 3.2 Gen 1 (Always On)
- 2x Thunderbolt™ 4 / USB4™ 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)

### Monitor Cable

None

## SECURITY & PRIVACY

### Security Chip

Firmware TPM 2.0 integrated in chipset

### Fingerprint Reader

None

## SERVICE

### Base Warranty

1-year, Depot

### Included Upgrade

1Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WSOT73712)

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

### Other Certifications

Intel® Evo™ Platform

## MODEL

TopSeller : No

Announce Date : 2021-10-05

EAN / UPC / JAN : 195891918937

End of Support : 2027-09-20



· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences  
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories

### Lenovo 500 FHD Webcam

4XCOV13599

A USB Video Class (UVC) compliant video camera designed for teleconferencing applications on desktop or laptop. It's a reliable digital video device to transfer video data with HD quality through a high-speed USB inte...

### Lenovo Adjustable Notebook Stand

4XFOH70605

Lifts your laptop to eye level. Bending over your laptop is a pain in the neck! The Lenovo Adjustable Height Laptop Stand lifts your laptop up to a comfortable and ergonomic viewing height. Also, use your laptop as th...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

PSREF  
Product Specifications  
Reference