



## SPECIFICATIONS

<b>Panel Size</b>	27" (69cm)
<b>Panel Resolution</b>	1920 x 1080 (FHD)
<b>Refresh Rate</b>	170Hz
<b>Response time</b>	1ms (MPRT)
<b>DYNAMIC REFRESH RATE TECHNOLOGY</b>	G-Sync Compatible
<b>ACTIVATED RANGE</b>	48 to 170Hz
<b>Panel Type</b>	IPS
<b>Brightness (nits)</b>	250
<b>Viewing Angle</b>	178° (H) / 178° (V)
<b>Aspect Ratio</b>	16:9
<b>Contrast Ratio</b>	1000:1
<b>DCR</b>	100000000:1
<b>Pixel Pitch (H x V)</b>	0.31125(H)x0.31125(V)
<b>Surface Treatment</b>	Anti-glare
<b>Display Colors</b>	16.7M
<b>Color Bit</b>	8
<b>Adobe RGB / DCI-P3 / sRGB</b>	85% / 92% / 135%
<b>Video ports</b>	2x HDMI (Supports FHD@165Hz as specified in HDMI 2.0) 1x DP (Supports FHD@170Hz as specified in DisplayPort 1.2a with DP overclocking)
<b>USB ports</b>	N/A
<b>Audio ports</b>	1x Earphone out
<b>Active Display Area (mm)</b>	597.6 (H) x 336.15 (V)
<b>Kensington Lock</b>	Yes
<b>VESA Mounting</b>	75 x 75 mm
<b>Control</b>	5-way OSD navigation joystick
<b>Power Type</b>	External Adaptor 12V 3A
<b>Power Input</b>	100~240V, 50/60Hz
<b>Signal Frequency</b>	96.4~186.7 KHz(H) / 48~170Hz(V)
<b>Adjustment (Tilt)</b>	-5° ~ 20°
<b>Adjustment (Swivel)</b>	-45° ~ 45°
<b>Adjustment (Height)</b>	0 ~ 130mm
<b>Curved</b>	Flat
<b>Carton Dimension (W X H X D)</b>	WW carton: 812 x 499 x 142 mm / Outer: 827 x 523 x 155 mm
<b>Weight (NW / GW)</b>	5.95kg / 8.05 kg without Stand: 3.95 kg

## FEATURES



### 1ms Fast Response Time

Eliminate screen tearing and choppy frame rates with 1ms response time.



### Night Vision

See every detail clearly in the dark, helping you find and attack enemies before they notice.

<b>Dimension (W x H x D)</b>	613.5 x 532 x 196.48 mm / 613.5 x 362.5 x 69.74 mm (without stand)
<b>Frameless Design</b>	Yes
<b>Note</b>	Display Port: 1920 x 1080 (Up to 170Hz) HDMI: 1920 x 1080 (Up to 165Hz) Adobe RGB, DCI-P3 and sRGB follow CIE1976 Standard
<b>PIP / PBP Function</b>	-

## CONNECTIONS



1. 5-way joystick navigator
2. 2x HDMI (2.0)
3. 1x Display Port (1.2a)
4. Earphone out
5. DC jack
6. Kensington lock