

2U Server Rack Shelf - Universal Vented Rack Mount Cantilever Tray for 19" Network Equipment Rack & Cabinet - Durable Design - Weight Capacity 200lb/91kg - 14" Deep Shelf, Black

Product ID: SHELF-2U-14-CENTER-V



The SHELF-2U-14-CENTER-V lets you add 2U 14 inches (35.6 cm) deep shelf to any 2-post EIA-310 compliant 19-inch rack or cabinet. The shelf is vented to improve airflow and help lower temperatures in your rack.

Quality construction

The centered rack shelf can hold up to 200 lbs (91 kg) of equipment and is constructed using 1/16 in (1.5 mm) thick SPCC commercial-grade cold-rolled steel for long-term durability and sturdiness. Accommodate your accessories or non-mountable devices for ease of access or connectivity to your equipment.

Hardware included

Conveniently includes M6 square cage nuts and M6 screws to set it up in no time.

The SHELF-2U-14-CENTER-V is backed by a StarTech.com lifetime warranty and free lifetime technical support

Certifications, Reports and Compatibility

Applications

Features

- **UNIVERSAL 19" FIT:** This 2U center-mounted vented server rack shelf is designed to fit 2-post EIA-310 compliant 19 in server racks and can accommodate an internal depth of 14in (35.6 cm) for your data, IT, networking, or other non-rack mountable equipment
- **CENTER MOUNT SHELF:** The center-mount design allows for easy access to the front and back of the equipment,

allowing for simple installation, maintenance and cable routing

- **DURABLE DESIGN:** Constructed with 1/16 in (1.5 mm) thick SPCC commercial cold-rolled steel, the sturdy rack shelf ensures long term durability and supports a total weight of 200 lbs (91 kg) making it the perfect rack shelf for any environment
- **MAXIMIZE VENTILATION:** The vented shelf plate on the cantilever rack shelf helps to improve airflow to effectively dissipate heat away from your equipment
- **STARTECH.COM ADVANTAGE:** IT professionals' choice for over 30 years, this 2U vented server rack shelf is backed for life by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Frame Type	Steel
U Height	2U
Cable Management	No
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	201.1 lb [91 kg]
------------------------------	------------------

Physical Characteristics

Color	Black
Material	Steel
Internal Width	19.0 in [48.3 cm]
Internal Depth	13.7 in [34.9 cm]
Product Length	14.0 in [35.6 cm]
Product Width	19.0 in [48.3 cm]
Product Height	3.4 in [87.3 mm]
Weight of Product	5.1 lb [2.3 kg]

Packaging Information

Package Length	21.7 in [55.0 cm]
----------------	-------------------



Package Width	16.1 in [41.0 cm]
Package Height	4.7 in [12.0 cm]
Shipping (Package) Weight	7.3 lb [3.3 kg]

What's in the Box

Included in Package	Shelf
	M6 Square Cage Nuts
	M6 Cage Screws
	Plastic Washers
	Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***

