

TR-MR32R-B

32-CH SMART Series Performance NVR with Turing Vision Bridge



Key Features

- Turing Vision cloud-ready with included Bridge Hardware
- ✓ Vision Core features People & Vehicle Attribute Search, LPR & More
- ✓ Cloud storage of event thumbnails and video clips
- ✓ Turing SMART Series IP cameras recommended
- Third-party IP cameras supported by NVR and Vision cloud
- ✓ Remote maintenance through Turing Vision Cloud
- ✓ Local full time recording on up to 4 SATA HDD
- √ Two RJ45; 384 Mbps inbound throughput








SPECIFICATIONS

Video/Audio Input	
IP Video Input	Up to 32 Channels
Two-Way Audio Input	1-Ch, RCA
Network	
Incoming Bandwidth	384 Mbps
Outgoing Bandwidth	384 Mbps
Remote Users	128
Protocols	P2P, UPnP, NTP, DHCP, PPPoE
VIDEO/AUDIO	
HDMI/VGA Output	VGA: 1920x1080p/60Hz, 1920x1080p/50Hz, 1600x1200/60Hz, 1280x1024/60Hz, 1280x720/60Hz, 1024x768/60Hz HDMI1/HDMI2(HDMI audio not supported): 4K (3840x2160)/30Hz, 1920x1080p/60Hz, 1920x1080p/50Hz 1600x1200/60Hz, 1280x1024/60Hz, 1280x720/60Hz, 1024x768/60Hz
Recording Resolution	12MP/8MP/6MP/5MP/4MP/3MP/1080p/960p/ 720p/D1/2CIF/CIF
Audio Output	1-ch, RCA
Synchronous Playback	16-ch
Image Rotation Mode Screen	3/4/5/7/9/10/12/16
Decoding	
Decoding Format	Ultra 265, H.265, H.264
Live View Playback	12MP/8MP/6MP/5MP/4MP/3MP/1080p/960p/ 720p/D1/2CIF/CIF
Decoding Capability	2 x 12MP@30, 4 x 4K@30, 8 x 4MP@30, 9 x 4MP@25, 16 x 1080p@30

Hard Disk		
SATA	4 SATA interfaces	
Capacity	Up to 10 TB for each disk	
eSATA	1 eSATA interface	
Disk Array		
USB Interface	RAID 1, 5	
External Interface		
Network Interface	2 RJ45 10M/100M/1000M self-adaptive Ethernet Interface	
USB Interface	Front panel: 2 x USB2.0 Rear panel: 1 x USB3.0	
Serial Interface	1 x RS485, 1 x RS232	
Alarm In	16-ch	
Alarm	4-ch	
GENERAL		
Power Supply	100 ~ 240 V AC Power Consumption: ≤25W(without HDD)	
Working Environment	-10°C~+ 55°C (+14°F∼+131°F), Humidity ≤ 90% RH (non-condensing)	
Dimensions	442mm ×426mm × 89mm (17.4" × 16.8" 3.5")	
Net Weight	≤5.7kg (12.57lb)	
COMPATIBILITY		
Recommended Turing Cameras	SMART Series	
ONVIF	Supported (S, G, T Profiles)	



DIMENSIONS



REAR PANEL

