

PERFORMANCE**Processor**

Intel® Core™ i5-1235U, 10C (2P + 8E) / 12T, P-core 1.3 / 4.4GHz, E-core 0.9 / 3.3GHz, 12MB

Graphics

Integrated Intel Iris® Xe Graphics

Chipset

Intel SoC Platform

Memory

8GB Soldered LPDDR5-4800

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

8GB soldered memory, not upgradable

Storage

256GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Support

One drive, up to 1TB M.2 2242 SSD or 1TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe 4.0 x4 slot

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3306 codec

Speakers

Stereo speakers, 2W x2, Dolby® Atmos®, sound by Harman / Kardon, Smart AMP

Camera

HD 720p + IR Hybrid with Privacy Shutter, ToF Sensor

Microphone

2x, Array

Battery

Integrated 56Wh

Max Battery Life

MobileMark® 2018: 11.4 hr

Power Adapter

65W USB-C® Slim (3-pin)

DESIGN**Display**

13.3" WQXGA (2560x1600) IPS 400nits Glossy, 100% sRGB, Eyesafe®, Glass

Touchscreen

None

Keyboard

Backlit, French / English

Case Color

Cloud Grey

Surface Treatment

CNC Unibody Anodized (Top), Stamping Anodized (Bottom)

Case Material

Aluminium (Top), Glass (Display Cover), Aluminium (Bottom)

Pen

Pen Upgradable (Purchase Separately)

Dimensions (WxDxH)

296 x 209 x 12.9 mm (11.7 x 8.2 x 0.5 inches)

Weight^[1]

Starting at 1.2 kg (2.65 lbs)

SOFTWARE**Operating System**

Windows® 11 Pro, French / English

Bundled Software

Office Trial

CONNECTIVITY**Ethernet**

No Onboard Ethernet

WLAN + Bluetooth®

Wi-Fi® 6E, 11ax 2x2 + BT5.1

Standard Ports

- 2x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x Headphone / microphone combo jack (3.5mm)

DockingVarious docking solutions supported via Thunderbolt. For more compatible docking solutions, please visit [Docking for ThinkBook 13x G2 IAP](#)**Monitor Cable**

1x ThinkBook USB-C Micro Hub

SECURITY & PRIVACY**Security Chip**

Discrete TPM 2.0

Fingerprint Reader

Touch Style, Integrated in Power Button

Other Security

- Camera privacy shutter
- IR camera for Windows® Hello

SERVICE**Base Warranty**

1-year, Courier or Carry-in

Included Upgrade

None

ACCESSORIES**Bundled Accessories**

None

CERTIFICATIONS**Green Certifications**

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- FSC certified carton
- TCO Certified
- RoHS compliant
- Low-VOC

Other Certifications

- Intel® Evo™ Platform
- Eyesafe® Certified
- TÜV Rheinland® Low Blue Light (Hardware Solution)

Mil-Spec Test

MIL-STD-810H military test passed

MODEL

TopSeller : Yes

Announce Date : 2022-04-28

EAN / UPC / JAN : 196379893630

End of Support : N/A

To see more note information, please link to

https://psref.lenovo.com/Detail/ThinkBook_13x_G2_IAP?M=21AT000WC

· Lenovo reserves the right to change specifications or other product information without notice.

· Product image on this page is a sample, it may not match the real color of this model

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management



Technical Account Managers for proactive relationship and escalation management



Priority on service delivery and repair parts



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Digital Pen

GX80U45010

The Lenovo Digital Pen with 4096 levels of pressure sensitivity, provides a natural pencil-like and paper experience when you sketch and jot down notes. Users will also enjoy easy access to short-cut functions through...

Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + International Upg) (5PS0N73132)
BETTER	3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + International Upg) (5PS0N73156)
GOOD	3Y Lenovo Support (Premier Support + Keep Your Drive + International Upg) (5PS0N73153)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference