

PERFORMANCE

Processor

Intel® Celeron® N4020 (2C / 2T, 1.1 / 2.8GHz, 4MB)

Graphics

Integrated Intel UHD Graphics 600

Chipset

Intel SoC Platform

Memory

4GB Soldered DDR4-2400

Memory Slots

Memory soldered to systemboard, no slots

Max Memory

4GB soldered memory, not upgradable

Storage

64GB eMMC 5.1

Storage Support

- 64GB eMMC 5.1 on systemboard
- MicroSD card, supports FAT32 file up to 128GB

Card Reader

MicroSD Card Reader

Optical

None

Audio Chip

High Definition (HD) Audio

Speakers

Stereo speakers, 1W x2, optimized with Dolby® Audio™

Camera

Front 2.0MP / Rear 5.0MP

Microphone

2x, Array

Battery

Integrated 30Wh

Max Battery Life

MobileMark® 2014: 9.3 hr

Local video (1080p) playback: 10.7 hr

Power Adapter

45W USB-C (3-pin)

DESIGN

Display

10.3" WUXGA (1920x1200) IPS 340nits Glossy, Touch

Touchscreen

10-point Multi-touch

Keyboard

Non-backlit, English

Case Color

Graphite Grey

Surface Treatment

Painting (Pad), Magnesium-Aluminium Painting (Kickstand)

Case Material

PC + ABS + Magnesium-Aluminium (Kickstand)

Pen

Pen Upgradable

Dimensions (WxDxH)

Pad: 253 x 166 x 9.9 mm (9.96 x 6.53 x 0.38 inches)

Folio case: 252 x 165 x 6.0 mm (9.92 x 6.49 x 0.23 inches)

Weight

Pad: around 597 g (1.32 lbs)

Folio: 269 g (0.59 lbs)

Others

- Buttons: power key with LED, volume key
- Kick-stand hinge: free stop

SOFTWARE

Operating System

Windows® 11 Home in S mode, English

Bundled Software

Microsoft® 365 Personal

CONNECTIVITY

Ethernet

None

WLAN + Bluetooth®

Wi-Fi® 5 11ac, 2x2 + BT5.0

WWAN

None

NFC

None

Standard Ports

- 1x USB-C 3.2 Gen 1 (support data transfer and DisplayPort™ 1.2)
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0, and DisplayPort 1.2)
- 1x microSD card slot
- 1x Headphone / microphone combo jack (3.5mm)

Docking

Lenovo® IdeaPad® Duet 3 Folio

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0

Fingerprint Reader

None

SERVICE

Base Warranty

1-year, Depot

Included Upgrade

None

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

MODEL

TopSeller : No

Announce Date : 2021-10-05

EAN / UPC / JAN : 196118136202

End of Support : 2026-06-25



Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.


Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo Digital Pen

GX80U45010

The Lenovo Digital Pen with 4096 levels of pressure sensitivity, provides a natural pencil-like and paper experience when you sketch and jot down notes. Users will also enjoy easy access to short-cut functions through...

Recommended Services

GOOD

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K78452)

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference