

ideapad S145 (14" & 15")

BUILT TO LAST.


Engineered for long-lasting performance, the Lenovo™ **IdeaPad™** S145 delivers powerful performance in an entry-level laptop—it's perfect for your everyday tasks with a durable build that you can depend on.

WHY YOU SHOULD BUY THE LENOVO IDEAPAD S145 (14" & 15")



Expect more from your entertainment

Dolby Audio™ delivers crystal-clear sound whether you're watching a video, streaming music, or video-chatting, you're sure to love what you hear on the **IdeaPad** S145.



See more, do more

A narrow bezel on 2 sides makes for a clean design and larger display giving you more viewing area and less clutter.



Unleash your inner traveler

With a starting weight of 1.85 kg / 4.1 lbs on the 15" and 1.6 kg / 3.5 lbs on the 14" the **IdeaPad** S145 is a great choice for when you're on-the-go.



Hybrid storage options

Keep your data secure and safe with a range of reliable storage options, including hybrid solid state and hard drives with speedy response times.



GO BOLDLY

With up to an 8th Generation Intel® Core™ processor, the **IdeaPad** S145 delivers unprecedented power and responsiveness that's vital in today's fast-paced digital world.

Lenovo™



WWW.LENOVO.COM



ideapad S145 (14" & 15")

SPECIFICATIONS

IdeaPad S145-14IWL*, IdeaPad S145-14IGM*, IdeaPad S145-14IKB*, IdeaPad S145-14IIL*
IdeaPad S145-15IWL*, IdeaPad S145-15IGM*, IdeaPad S145-15IKB*, IdeaPad S145-15IIL*

PERFORMANCE

Processor

Up to 10th Generation Intel® Core™ i7-1065G7 Processor

Operating System

Windows 10 Home

Graphics

NVIDIA® GeForce® MX230¹

NVIDIA® GeForce® MX110

Intel® Integrated Graphics

Memory

4 GB / 8 GB / 12 GB

Storage

SATA : 500 GB / 1 TB / 2 TB; 5400 rpm

PCIe SSD M.2 : 128 GB / 256 GB / 512 GB

Dual Storage : 16 GB Optane™ + 1 TB HDD /
PCIe SSD + 1 TB SATA 2.5 HDD

Intel® Teton Glacier²: 16 GB + 256 GB PCIe

Single Storage : SATA 2.5 HDD /
SATA 2.5 SSD / PCIe SSD²

Audio

2 x 1.5W Speakers with Dolby Audio™

Battery³

Up to 5.5 Hours with Polymer 30 WHr

Up to 6 Hours with Polymer 35 WHr

DESIGN

Display

S145-14IWL, S145-14IGM, S145-14IKB,
S145-14IIL

14" FHD (1920 x 1080) TN, Anti-Glare,
220 nits, 45% NTSC

14" HD (1366 x 768), TN, Anti-Glare,
220 nits, 45% NTSC

S145-15IWL, S145-15IGM, S145-15IKB,
S145-15IIL

15.6" FHD (1920 x 1080) TN, Anti-Glare,
220 nits, 45% NTSC

15.6" HD (1366 x 768), TN, Anti-Glare,
220 nits, 45% NTSC

Dimensions (W x D x H)

S145-14IWL, S145-14IGM, S145-14IKB,
S145-14IIL

(mm) : 327.1 x 241 x 19.93⁴

(inches): 12.88" x 9.49" x 0.78"

S145-15IWL, S145-15IGM, S145-15IKB,
S145-15IIL

(mm) : 362.2 x 251.5 x 19.93⁴

(inches): 14.26" x 9.9" x 0.78"

Weight

S145-14IWL, S145-14IGM, S145-14IKB,
S145-14IIL

Starting at 3.5 lbs (1.6 kg)

S145-15IWL, S145-15IGM, S145-15IKB,
S145-15IIL

Starting at 4.1 lbs (1.85 kg)

Colors

Granite Black Glossy

Granite Black Texture

Platinum Grey Glossy



CONNECTIVITY

WLAN

1 x 1 WiFi 802.11 ac

Bluetooth®

Bluetooth® 4.2

or 5.0 (on S145-14IIL, S145-15IIL)

Input/Output (I/O) Ports

2 x USB 3.1 Gen 1⁵

1 x USB 2.0

HDMI™ 1.4b

SD Card Reader

PRELOADED SOFTWARE

- Lenovo Antivirus Plus⁶
- Lenovo PC Manager⁶
- Lenovo Utility⁷
- Lenovo Vantage⁸
- LinkedIn⁷
- McAfee LiveSafe™⁸
- Microsoft Office

¹ Only for 15" (with PRC).

² Available only for 15".

³ All battery life claims are approximate and based on test results using the MobileMark® 2014 ver 1.5 battery life benchmark test. Actual results will vary, and depend on numerous factors including product configuration and usage, software, operating conditions, wireless functionality, power management settings, screen brightness and other factors. The maximum capacity of the battery will naturally decrease with time and usage. See <https://bapccom/products/mobilemark-2014/> for additional details.

⁴ As thin as in the reference.

⁵ The actual transfer speed of the USB 3.1 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 5 Gbit/s.

⁶ PRC only.

⁷ Worldwide (WW).

⁸ ROW only.

LENOVO SERVICES

Warranty Upgrades - On-site / In-Home Service

Maximizes PC uptime and productivity by providing convenient, fast repair services in your own home.

Accidental Damage Protection

Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

Warranty Extensions (1-to-3 Years Total Duration)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment and potentially lower the cost of ownership over time.

* Example of Lenovo IdeaPad catalogue naming convention



Intel® platform codes

Apollo Lake: IAP, Broadwell: IBD, Braswell: IBR, Broadwell: IBW, Baytrail: IBY, Cannonlake: ICN, Haswell: IHH, Kabylake: IKB, Skylake H: ISH, Skylake: ISK, Skylake U: ISU, Skylake Y: ISY, Skylake Z: ISZ, Gemini Lake: IGM, Whiskey Lake: IWL, Comet Lake: CML-IML-ICL-IIL



WWW.LENOVO.COM

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, IdeaCentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Logo, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. ©2019 Lenovo. All rights reserved.



Lenovo™