

## Key Features

ALL-IN-ONE SOLUTION | VIEWBOARD INTERACTIVE FLAT PANEL | FASTER  
WI-FI | FIXED WALL MOUNT

## Product Description

Ideal for education environments, this all-in-one ViewBoard Bundle includes a 86" ViewBoard IFP8652-1C 4K interactive flat panel, a wireless AC adapter, and a WMK-047-2 wall mount.



**Contact Sales**

- call: 888.881.8781
- email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)
- visit: [viewsonic.com](http://viewsonic.com)

**Display:**

Display Type:	LCD
Display Size (in.):	86
Viewable Area (in.):	85.6
Light Source:	LED
Resolution:	3840 x 2160
Refresh Rate (Hz):	60
Aspect Ratio:	16:9
Static Contrast Ratio:	1,200:1
Dynamic Contrast Ratio:	4,000:1
Backlight Life (Hours):	50,000
Brightness:	350 cd/m2
Response Time (Typical GTG):	8ms
Viewing Angles:	178° horizontal, 178° vertical
Panel Surface:	Anti-glare 7H tempered glass 3.2mm

**Networking:**

Ethernet LAN:	10/100/1000MB GigaLAN (PC); 10/100 (Android)
Wifi:	Optional VB-WIFI-001 adapter, 802.11AX + Bluetooth 5.2

**Embedded Player:**

OS:	ViewBoard OS based on Android 9.0
GPU:	ARM Mali-G52
CPU:	ARM Quad Core A73
CPU Processor Speed:	1.8GHz
Memory:	4GB LPDDR4
Storage:	32GB eMMC

**Audio:**

Microphone:	Beamforming array x 8, noise cancellation
Internal Speakers:	15W (x2)
Subwoofer:	15W (x1)

**Connector:**

HDMI 2.0 In(3), VGA(1), SPDIF(1), USB 3.0(2), USB 2.0(3), USB 2.0 Type B(2), USB 3.1 Type C(1), OPS PC Slot(1), RS232(1), Ethernet LAN (RJ45)(1)

**Power:**

Voltage:	100-240 VAC
Consumption (typical):	170W
Stand-by:	<0.5

**Operating Conditions:**

Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	10-90%

**Touch:**

Touch Technology:	Slim IR
Touch Points:	Windows: 33-Point Touch, Android: 20-Point Touch
Tip Detection:	Dual tips, 2mm and 8mm
Other:	Palm recognition, object awareness
Latency:	4ms

**Weight (imperial):**

Net (lbs):	121.8
Gross (lbs):	170.8

**Weight (metric):**

Net (kg):	55.2
Gross (kg):	77.4

**Dimensions (imperial) (WxHxD):**

Packaging (in.):	72.8 x 46.8 x 10.6
Physical (in.):	67.3 x 42.2 x 4.7

**Dimensions (metric) (WxHxD):**

Packaging (mm):	1848 x 1190 x 270.0
Physical (mm):	1709.0 x 1071.0 x 120.0

**Mount:**

VESA Compatible:	800 x 400 mm
Screw Size:	M8

**General:**

Warranty: 3-year limited warranty on parts, labor and backlight, onsite warranty

Recycle/Disposal: Please dispose of in accordance with local, state or federal laws.

PACKAGE CONTENTS: IFP6552-1C display, stylus pen x 2, power cable, HDMI cable, USB cable, AV cable, remote control with batteries, Camera plate, M8 screw x 8, Quick Start Guide. Bundle package includes VB-WIFI-001 and WMK-047

Regulations: cTUVus, FCC, ENERGY STAR, EPEAT Silver, Mexico Energy, CE, CB, RoHS, ErP, WEEE

**Accessories:**

NMP760, VB-BLF-003, VB-BLM-003, VB-BLW-003, VB-BOW-001, VB-CAM-001, VB-CAM-002, VB-EBM-001, VB-EBT-001, VB-EBW-001, VB-STND-001, VB-STND-002, VB-STND-003, VB-STND-004, VB-WIFI-001, VB-WKB-001, VPC12-WPO-6, VPC25-W53-O1-1B, VPC25-W53-O2-1B, VPC27-W55-O2-1B, VPC2C-W33-O1-1B, WMK-047-2