

# TN-NRP042T

4CH 1HDD NVR with 4CH PoE



## Key Features

- ✓ Up to 4ch IP cameras access
- ✓ Max. 8MP resolution recording
- ✓ 1 SATA hard disk up to 8TB
- ✓ 1 RJ45 10M/100M network interface
- ✓ Smart search and playback
- ✓ Support cloud upgrade



## SPECIFICATIONS

Network	
Incoming Bandwidth	28 Mbps
Outgoing Bandwidth	28 Mbps
Remote Users	8
Protocols	HTTP, HTTPS, TCP/IP, IPv4, UPnP, UDP, RTSP, SMTP, NTP, DNS, DHCP, P2P, IP Filter, DDNS, 802.1X, SNMP, 3G/4G, PPPoE

VIDEO/AUDIO	
IP Video Input	4-ch
Two-way Audio Input	1-ch, RCA
HDMI/VGA Output	HDMI: 3840×2160,1920×1080, 1440×900, 1280×1024 VGA: 1920×1080, 1440×900, 1280×1024
Recording Resolution	8MP, 6MP, 5MP, 4MP, 3MP, 1080P, 720P, D1 etc.
Audio Output	1-ch
Synchronous Playback	4/1

Decoding	
Decoding Format	Ultra 265, H.265, H.264
Live View Playback	4K/5MP/4MP/3MP/1080p/960p/720p/D1/2CIF/CIF
Capability	2 x 4k@30, 3 x 5MP@30, 4 x 4MP@30

Hard Disk	
SATA	1 SATA interface
Capacity	6 TB for HDD and 1-2 TB internally

External Interface	
NETWORK INTERFACE	1 RJ45 10M/100M self-adaptive Ethernet Interface
USB Interface	3 x USB2.0


PoE	
Interface	1 RJ-45 port (10/100 Mbps)
Max Power	32W total
Supported Standard	IEEE 802.3af/at

GENERAL	
Power Supply	48V DC, 1.25A Power Consumption:<5 W (without HDD)
Working Environment	-10°C~+ 50°C (+14°F~+122°F), Humidity < 90% RH
DIMENSIONS	255 × 237 × 47.5 mm (10.04 × 9.33 × 1.87 inch)
NET WEIGHT	0.9 kg (1.98 lb) without HDD

COMPATIBILITY	
ONVIF	Supported
Recommended Turing Cameras	ADVANTAGE Series Only



DIMENSIONS (mm)



REAR PANEL

