

## PE0316S

0U Basic PDU with Surge Protection

PE0316SA



ATEN's Basic PDU family is extended with 0U members containing 16 outlets and available in IEC or NEMA socket configurations. The compact aluminum housing gives a sleek, yet robust look while minimizing installation space for work space efficiency. Thanks to the built-in surge protection module, the IT devices connected to the PDU are well-protected from sudden surges in electricity; plus, the equipment downtime is reduced as a result of the overcurrent protection design. The Basic PDUs are tailored made for individuals who are in need of industrial-grade, easy-to-deploy power distribution unit in data centers, server rooms, and network wiring closets.


### Features

- Space saving – 0U rack mount design
- IEC or NEMA outlet models
- Overcurrent protection
- Surge protection
- Aluminum material
- Works with data centers, server rooms, and telecom equipment

**Specifications**

Function	PE0316SA	PE0316SG
<b>Electrical</b>		
Nominal Input Voltage	100-120 VAC	100-240 VAC
Maximum Input Current	30A Max (UL de-rated 24A Max)	32A Max
Input Frequency	50-60 Hz	50-60 Hz
Input Connection	NEMA L5-30P	IEC 60309 32A
Input Power	3600VA(Max); 2880VA(UL de-rated)	7680VA(Max)
Outlet Type	(16) NEMA 5-20R	(16) IEC 320 C13
Maximum Output Current (Outlet)	20 Max (UL de-rated 16A Max)	10A Max
Maximum Output Current (Bank)	20A Max (UL de-rated 16A Max)	16A Max
Maximum Output Current (Total)	30A Max (UL de-rated 24A Max)	32A Max
OPD(Overcurrent Protection Device)	Yes	Yes
<b>Physical Properties</b>		
Dimensions (L x W x H)	96.68 x 4.44 x 6.00 cm (38.06 x 1.75 x 2.36 in.)	96.68 x 4.44 x 6.00 cm (38.06 x 1.75 x 2.36 in.)
Weight	2.10 kg ( 4.63 lb )	2.10 kg ( 4.63 lb )
Power Cord Length	10ft(10#)	10ft(3×4mm <sup>2</sup> )
<b>Environmental</b>		
Temperature (Operating / Storage)	0 - 40°C / -20 - 60°C	0 - 40°C / -20 - 60°C
Elevation (Operating / Storage)	3000m	3000m
<b>Compliance</b>		
EMC Verification	FCC Class A	CE Class A
Safety Verification	By Request	CE,LVD
Note	For some of rack mount products, please note that the standard physical dimensions of WxDxH are expressed using a LxWxH format.	

Diagram



Note: (1) As there are many Basic PDUs, PE0324S (top) and PE0118S (bottom) are the respective 0U and 1U examples used here.

**ATEN International Co., Ltd.**

3F., No.125, Sec. 2, Datong Rd., Sijhih District., New Taipei City 221, Taiwan  
Phone: 886-2-8692-6789 Fax: 886-2-8692-6767  
www.aten.com E-mail: marketing@aten.com



© Copyright 2015 ATEN® International Co., Ltd.  
ATEN and the ATEN logo are trademarks of ATEN International Co., Ltd.  
All rights reserved. All other trademarks are the property of their respective owners.