



# DO THE IMPOSSIBLE. OM IS (RE)BORN.



## OM-1

Everything you'd want from a flagship camera, introducing the new OM SYSTEM OM-1. This model is a perfect all-in-one professional camera containing all the features and functions in a weathersealed, lightweight and compact body. The OM-1 contains in-body image stabilization combined with high res to ensure crisp, detailed 80MP images. The AF performance and high-speed burst made possible by the new TruePic™ X processor allow photographers to capture high quality images and deliver spectacular resolution, vivid color and razor sharpness. Compact, lightweight, weatherproof and packed with advanced features to advance your creativity. The OM SYSTEM OM-1.



## FEATURES

**Unexpected Image Quality** with the best image quality we've ever delivered

**Absolute Reliability** that no-one else can deliver

**Computational Photography** to cleverly expand the possibilities to create

**Unparalleled Speed** that makes you ready for every opportunity

**Full Video Capabilities** that meet every demand of the modern creator

# SPECIFICATIONS

# OM-1

<b>SENSOR EFFECTIVE RESOLUTION / TYPE</b>	20.4 Megapixel 4/3 Stacked BSI Live MOS
<b>DUST REDUCTION</b>	Super Sonic Wave Filter
<b>PROCESSOR</b>	TruePic™ X Dual Quad Core Processor
<b>IMAGE STABILIZATION SYSTEM</b>	5-Axis Image Stabilization with up to 8 Shutter Speed Steps Compensation*
<b>VIEWFINDER</b>	Eye-level OLED electronic viewfinder, approx. 5.76M dots
<b>REAR MONITOR</b>	3.0-inch vari-angle monitor (electrostatic capacitance touch panel), Approx.1.62M dots (3:2)
<b>WEATHERPROOFING</b>	Dust, Splash and Freezeproof (IP53 Rated)
<b>FOCUSING SYSTEM</b>	High-speed imager AF: Imager phase detection AF and imager contrast AF used in combination
<b>FOCUSING POINTS</b>	Cross-type phase detection AF (1,053 points) Contrast AF (1,053 points) / All target Single target (1 point), Small target (9 points), Cross target (39 points) Middle target (63 points), Large target (165 points) Custom target* (AF area and its increment steps selectable)
<b>AI DETECTION AF</b>	Formula Cars, Rally Cars, Motorcycles / Aircrafts, Helicopters / Bullet Trains, Standard Trains, Steam Locomotives / Birds / Dogs, Cats
<b>SEQUENTIAL SHOOTING</b>	[Sequential shooting] approx 10 fps with selectable 1-10 fps [Silent sequential shooting] approx 20 fps with selectable 5, 10, 15, 20 fps without blackout [Silent sequential shooting SH1] approx 120 fps with selectable 60, 100, 120 fps without blackout *Slower shutter speeds and flash can not be used. [Silent sequential shooting SH2] approx 50 fps with selectable 25, 50, fps without blackout *Slower shutter speeds and flash can not be used. *Compatible lenses are limited. [Pro Capture] approx 20 fps with selectable 5, 10, 15, 20 fps *When in Pro Capture mode, slower shutter speeds and flash can not be used [Pro Capture SH1] approx 120 fps with selectable 60, 100, 120 fps *When in Pro Capture mode, slower shutter speeds and flash can not be used [Pro Capture SH2] approx 50 fps with selectable 25, 50 fps *Slower shutter speeds and flash can not be used. *Compatible lenses are limited.
<b>ADDITIONAL FEATURES</b>	Focus Stacking Art Filters Live Composite Exposure Bracketing Live ND 4K Video Recording Wireless Shooting & GPS Info via Smartphone C4K/4K 60p 10 bit C4K/4K RAW 12bit 4:4:4 (HDMI)
<b>WEIGHT</b>	Approx. 511g (body only)
<b>DIMENSIONS</b>	Approx. 134.8mm(W) x 91.6mm(H) x 72.7mm(D) *Based on CIPA standards: excludes protrusions
<b>BOX CONTENTS</b>	Body, CB-USB13 USB cable, CC-1 Cable clip, CP-2 Cable protector, Shoulder strap, Instructionmanual, Warranty card, BLX-1 Li-ion battery, F-7AC AC adapter, FL-LM3 Flash

\*with the 150-400mm lens and measured within the CIPA standard

To learn more about Olympus & OM SYSTEM products, please visit [getolympus.com](http://getolympus.com).

\*Specifications and appearances are subject to change without any notice or obligation on the part of the manufacturer. \*The colors of products printed herein may differ from those of the actual products. \*All other company and product names are registered trademarks and/or trademarks of their respective owners. \*The date herein is as of February 2022. © 2022 OM Digital Solutions

