



[DOWNLOAD SPECS](#)

## RF100mm F2.8 L MACRO IS USM

### Lens

<b>Focal Length</b>	100mm
<b>Maximum and Minimum Aperture</b>	F2.8-32
<b>Lens Mount Type</b>	RF Mount Canon RF mount; Exclusively for Canon EOS R-series cameras
<b>Minimum Focusing Distance</b>	0.86 ft. (10.2 in.) /0.26 m.
<b>Maximum Magnification</b>	1.4x (Fills frame with subject 1.0 x 0.67 inches / 25 x 17mm in size)
<b>Angle of View</b>	Diagonal: 24°00'
<b>Lens Construction</b>	17 elements in 13 groups

<b>SA (Spherical Aberration) Control</b>	Provided
<b>Special Elements</b>	N/A
<b>Lens Coating</b>	Super Spectra Coating; Fluorine coating on front elemen
<b>Filter Size Diameter</b>	Ø67 mm
<b>Aperture Blades</b>	9
<b>Dust/Water Resistance</b>	Supported (Rubber Ring on lens mount, Focus Ring, Con Ring, SA Control Ring, switch panel and switches)
<b>IS Mode Selection</b>	None; Automatic detection and correction for panning
<b>Image Stabilization</b>	CIPA standard: 5 stops (Using an EOS R)
<b>Shake Correction with coordinated Optical Image Stabilizer and In-Body Image Stabilization.</b>	Supported. 8 Stops (Using an EOS R5); Hybrid IS during close-focus operation
<b>Maximum Outer Diameter x Length</b>	Approx. 3.21 in x 5.83 in. / 81.5mm x 148mm
<b>Weight</b>	Approx. 1.6 lbs. (25.8 oz) / 730g

## Accessories

<b>Lens hood</b>	ET-73C (Bundled)
<b>Lens Cap</b>	E-67II (bundled)
<b>Dust Cap</b>	Lens Dust Cap RF (Bundled)
<b>Lens Case</b>	Lens Pouch LP1222 (Bundled)
<b>Tripod Mount</b>	Tripod Mount Ring E(B) with adapter (Optional accessory, sold separately)

