

# HPE ProLiant DL360 Gen10 Plus server

---

## What's new

- Supports 3rd Generation Intel® Xeon® Scalable Processors for enhanced compute performance.
- 64 PCIe Gen4 lanes, resulting in more devices, improved bandwidth and augmented balanced I/O capabilities.
- Support for industry-standard OCP 3.0 Network Adapters, enhancing customer choice.
- Enhanced storage capabilities with Tri-mode controllers supporting NVMe/SAS/SATA drives, allowing customers to select the ideal media type and mix for their exact application.
- Choice of storage backplanes and cages, offering diverse bay counts, protocols, and bandwidth that enable customers to design their server storage for their precise needs.
- Slot-less HW RAID protected M.2 boot solution, providing peace-of-mind O/S deployment while saving invaluable slots and storage bays.

## Overview

Do you need to efficiently expand or refresh your IT infrastructure to propel the business?

Adaptable for diverse workloads and environments, the compact 1U HPE ProLiant DL360 Gen10 Plus server delivers enhanced performance with the right balance of expandability and density. Designed for supreme versatility and resiliency while backed by a comprehensive warranty, the HPE ProLiant DL360 Gen10 Plus server is ideal for IT infrastructure, either physical, virtual, or containerized.

Powered by 3rd Generation Intel® Xeon® Scalable Processors, delivering up to 40 cores, 3200 MT/s memory, and introducing PCIe Gen4 and Intel Software Guard Extension (SGX) support to the dual-socket segment, the HPE ProLiant DL360 Gen10 Plus server delivers premium compute, memory, I/O, and security capabilities for customers focused on performance at any cost.

## Features

### Built for Some of the Most Demanding Workloads

The HPE ProLiant DL360 Gen10 Plus server is powered by 3rd Generation Intel® Xeon® processors and built with foundational intelligence to transform IT with insights that enhance workload performance, placement, and efficiency, delivering better outcomes faster.

HPE ProLiant servers provide real-time operational feedback on server performance plus recommendations for fine-tuning BIOS settings to adjust to better serve changing business needs.

### 360-degree Holistic Security

The HPE ProLiant DL360 Gen10 Plus server provides an enhanced holistic, 360-degree view to security that begins in the manufacturing supply chain and concludes with a safeguarded, end-of-life decommissioning.

HPE ProLiant security begins with the corruption-free manufacture of the server and auditing the integrity of every component – hardware and firmware – to provide verification that the server begins its lifecycle uncompromised through the supply chain.

HPE ProLiant servers provide rapid detection of a security-compromised server, even to the point of not allowing it to boot, identify and contain malicious code, and protect healthy servers.

HPE ProLiant servers provide automated recovery from a security event, including restoration of validated firmware, and facilitating recovery of operating system, application, and data connections, providing a fast path to bring a server back online and into normal operations.

When it's time to retire or repurpose an HPE ProLiant server, one button secure erase speeds and simplifies the complete removal of passwords, configuration settings, and data, preventing inadvertent access to previously secured information.

### **Intelligent Management Automation**

The HPE ProLiant DL360 Gen10 Plus server simplifies and automates management tasks, establishing a solid foundation for a standards-based, hybrid cloud platform enabled by automation.

Embedded in Hewlett Packard Enterprise servers, HPE Integrated Lights-Out(iLO) is an exclusive core intelligence that monitors server status, providing the means for reporting, ongoing management, service alerting, and local or remote management to quickly identify and resolve issues.

Automation and software-defined control reduces time spent on provisioning and maintenance, and reduces deployment times.

HPE InfoSight for Servers continually analyzes server infrastructure and applies real-world examples of hundreds of thousands of servers to predict and prevent problems before they can adversely affect business operations.

### **Delivered As-a-Service**

The HPE ProLiant DL360 Gen10 Plus server is supported by HPE GreenLake to simplify IT. With 24x7 monitoring and management, our experts do the heavy lifting to manage your environment with services built into consumption-based solutions.

Hewlett Packard Enterprise provides customers choice in how they acquire and consume IT. Beyond traditional financing and leasing, HPE offers options that free trapped capital, accelerate infrastructure updates and provide for on-premises pay-per-use consumption with HPE GreenLake.

Rapidly deploy a broad portfolio of cloud services such as, containers, compute, virtual machines (VMs), accelerated storage, data protection, and more. Workload-optimized, preconfigured solutions can be quickly on-boarded, accelerating your agility



## Technical specifications

## HPE ProLiant DL360 Gen10 Plus server

<b>Processor type</b>	Intel®
<b>Processor name</b>	3rd Generation Intel® Xeon® Scalable Processor Family
<b>Processor family</b>	Intel® Xeon® Scalable 8300 series Intel® Xeon® Scalable 6300 series
<b>Processor number</b>	1 or 2
<b>Processor core available</b>	8 to 40 core, depending on processor
<b>Processor cache</b>	12 - 60 MB L3, depending on processor
<b>Processor speed</b>	3.6 GHz, maximum depending on processor
<b>Expansion slots</b>	Maximum 3 PCIe Gen4, for detail descriptions please see QuickSpecs
<b>Maximum memory</b>	6.0 TB per socket, when populated with 256 GB DDR4 and 512 GB Persistent Memory
<b>Memory, standard</b>	4 TB (16x 256 GB) RDIMM per socket 6 TB (8x 256 GB RDIMM and 8x 512 GB Persistent Memory) per socket, depending on processor model
<b>Memory slots</b>	16 DIMM slots per socket
<b>Persistent memory type</b>	Optional: Intel® Optane™ Persistent Memory for HPE
<b>Persistent memory media capacity</b>	Optional: 128 to 256 GB
<b>Memory type</b>	HPE DDR4 SmartMemory
<b>Memory protection features</b>	HPE Fast Fault Tolerant Memory Advanced ECC Memory Online Spare Memory Mirrored Memory
<b>Network controller</b>	Wide range of speeds, cabling, chipsets and form factors. Please see QuickSpecs for network card choices
<b>Storage controller</b>	Included - Embedded SATA controller (AHCI or SR100i modes) Optional - Variety of protocols -including NVMe-, port count, array utilities, and form factors. Please see QuickSpecs for storage controllers selection
<b>Product dimensions</b>	SFF: 4.29 x 43.46 x 76.96 cm LFF: 4.29 x 43.46 x 80.01 cm
<b>Weight</b>	SFF: 13.04 kg to 16.27 kg LFF: 13.77 kg to 16.78 kg
<b>Infrastructure management</b>	Included - HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download) Optional - HPE iLO Advanced, and HPE OneView Advanced
<b>Warranty</b>	3/3/3: Server Warranty includes three years of parts, three years of labor, and three years of onsite support coverage. Additional information regarding worldwide limited warranty and technical support is available at: <a href="http://h20564.www2.hpe.com/hpsc/wc/public/home">http://h20564.www2.hpe.com/hpsc/wc/public/home</a> . Additional HPE support and service coverage, to supplement the product warranty, is available. For more information, visit <a href="http://www.hpe.com/support">http://www.hpe.com/support</a>
<b>Drive supported</b>	Up to 4 LFF SAS/SATA HDDs or SSDs Up to 10 SFF SAS/SATA HDDs or SATA/SAS/NVMe U.2 or U.3 SDDs, depending on model



[For additional technical information, available models and options, please reference the QuickSpecs](#)

## HPE Services

No matter where you are in your transformation journey, you can count on HPE Services to deliver the expertise you need when, where and how you need it. From strategy and planning to deployment, ongoing operations and beyond, our experts can help you realize your digital ambitions.

### Consulting services

Experts can help you map out your path to hybrid cloud and optimize your operations.

### Managed services

HPE runs your IT operations, giving you unified control, so can focus on innovation.

### Operational services

Optimize your entire IT environment and drive innovation. Manage day-to-day IT operational tasks while freeing up valuable time and resources.

- HPE Complete Care Service: a modular service designed to help optimize your entire IT environment and achieve agreed upon IT outcomes and business goals. All delivered by an assigned team of HPE experts.
- HPE Tech Care Service: the operational service experience for HPE products. The service provides access to product specific experts, an AI driven digital experience, and general technical guidance to help reduce risk and search for ways to do things better.

### Lifecycle Services

Address your specific IT deployment project needs with tailored project management and deployment services.

### HPE Education Services

Training and certification designed for IT and business professionals across all industries. Create learning paths to expand proficiency in a specific subject. Schedule training in a way that works best for your business with flexible continuous learning options.

[The Defective Media Retention \(DMR\)](#) service feature option applies only to Disk or eligible SSD/Flash Drives replaced by Hewlett Packard Enterprise due to malfunction. [Comprehensive Defective Material Retention \(CDMR\)](#) allows you to keep all data retentive components.

## HPE GreenLake

[HPE GreenLake edge-to-cloud platform](#) is HPE's market-leading as-a-Service offering that brings the cloud experience to apps and data everywhere – data centers, multi-clouds, and edges – with one unified operating model, on premises, fully managed in a pay per use model.

If you are looking for more services, like **IT financing solutions**, please explore them [here](#).

**Make the right purchase decision.  
Contact our presales specialists.**

[Find a partner](#)



Explore **HPE GreenLake**



**Hewlett Packard  
Enterprise**

© Copyright 2023 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Parts and Materials: HPE will provide HPE-supported replacement parts and materials required to maintain the covered hardware.

Parts and components that have reached their maximum supported lifetime and/or the maximum usage limitations as set forth in the manufacturer's operating manual, product quick-specs, or the technical product data sheet will not be provided, repaired, or replaced as part of these services.

Intel, Intel Xeon, and Intel Optane are trademarks of Intel Corporation or its subsidiaries in the U.S. and/or other countries. All third-party marks are property of their respective owners.

Image may differ from the actual product  
[PSN1013291294WWEN](#), September, 2023.