

C7120/C7125/C7130

Xerox® VersaLink® Color Multifunction Printer

The Workplace Assistant that can do it all. Even print.



ConnectKey®
Technology

xerox™

Xerox® VersaLink® C7120/C7125/C7130

Color Multifunction Printer

What will you need tomorrow? It's tough to predict the future, but with VersaLink, it's easy to be prepared. In fact, print just scratches the surface of what's possible. Along with built-in, comprehensive security features, these Workplace Assistants deliver the everyday, must-have capabilities you need now with plenty of room to add new features as your work evolves.

ADAPTABLE TECHNOLOGY THAT FLEXES WITH YOU

Your work is always evolving, so you need technology that's always a step ahead. Xerox® ConnectKey® Technology-enabled VersaLink provides the adaptability needed to support advancements in technology and work processes. With regular firmware updates and an ever-growing collection of productivity tools delivered with the App Gallery, VersaLink helps you stay ahead of the change.

BREEZE THROUGH TASKS EFFORTLESSLY

Getting up to speed is easy with a tablet-like touch screen that balances simplicity and time-saving efficiency. The familiar, intuitive user interface (UI) guides you through tasks, eliminating extra steps. And the ability to personalize the UI empowers you to work the way you want.

Mobility features, like Wi-Fi Direct, take the hassle out of printing directly from your favorite mobile devices. Near Field Communication (NFC) lets you authenticate with a smartphone to connect in seconds, and the Xerox® Quick Link app enables you to quickly connect and print without IT support, reducing the burden on IT teams.

And with VersaLink Devices, more capabilities means added convenience, not more complexity. Leading-edge scanning functionality and automation of physical and digital workflows allow you to scan, digitize and route information without missing a beat, reducing errors and saving time. Furthermore, industry-specific apps for education, healthcare, legal and more help you stay plugged in and productive.

HELLO, DIGITAL RESILIENCE

Translator. Proofreader. Form checker. Do-it-all digitizer. VersaLink makes it easy to tackle the hardest challenges. Stay ready with access to an expanding portfolio of cloud-hosted apps and the ability to tailor solutions for your specific needs through the Xerox Partners program.

And with access to Xerox® Workflow Central Platform, a cloud-based solution that takes the guesswork out of converting physical and digital files into usable formats right from the VersaLink user interface, even complicated work processes are easy. It helps you get the most out of your Workplace Assistant, so you can stay productive and secure from the office or on the move.

PROACTIVE SECURITY YOU CAN COUNT ON

VersaLink's multi-layered protection safeguards all system components. A comprehensive range of proactive security features stop even the most sophisticated security threats where they start, preventing malicious attacks, proliferation of malware, unauthorized access or changes and breaches that lead to downtime.

To simplify security event reporting and management, VersaLink Devices can integrate with Security Information and Event Management (SIEM¹) Tools. Trellix[#] whitelisting/allowlisting constantly monitors, detects and blocks threats in real time. And automated security responses provide invaluable time savings and peace of mind.

SUPERIOR IMAGE QUALITY

Color is the difference between communications that fall flat and those with real impact. With high-resolution output of 1200 x 2400 dpi, the VersaLink takes your documents to the next level with sharp image quality.

SUSTAINABILITY WITHOUT COMPROMISE

All VersaLink Devices meet or exceed the strictest globally recognized standards for sustainability, including EPEAT and ENERGY STAR®, providing environmental benefits without ever having to compromise on performance or quality.

XEROX CONNECTKEY TECHNOLOGY

Intuitive User Experience

Tap into a tablet-like experience with gesture-based touch screen controls. Easy personalization, plus simple workflows and functions.

Mobile and Cloud Ready

Enjoy mobile flexibility with cloud-hosted services. Instantly connect to cloud and mobile devices right from the user interface.

Comprehensive Security

Prevent unauthorized access, detect threats and protect data and documents with built-in proactive security features.

Enables Managed Print Services

Boost workplace efficiency, productivity and security with seamless integration with Xerox® Managed Print Services.

Gateway to New Possibilities

Do your best work with the apps from the Xerox App Gallery. Don't see an app for your specific need? Our partners can develop a custom solution for you.

Learn more about expanding and customizing your capabilities at [ConnectKey.com](https://www.connectkey.com).

[#]Trellix formerly known as McAfee. Device firmware will reflect Trellix brand change in future software release.

Xerox® VersaLink® C7120/C7125/C7130 Color Multifunction Printer Configuration

130-sheet² Single-Pass Duplex Automatic Document Feeder (DADF)

saves time by simultaneously scanning both sides of two-sided documents with up to 80 impressions per minute (ipm). High paper capacity drives productivity, especially for tasks that require large batches of scanned or copied documents.

The 100-sheet Bypass Tray

handles media sizes from 3.5 x 3.87 in to 11.69 x 17 in/88.9 x 98.4 mm to 297 x 431.8 mm.



User interface is an intuitive, tablet-like, 7-inch tiltable touch screen that allows you to complete tasks in just a few effortless taps and lets you personalize your experience. Gain access to 100+ productivity apps through the **Xerox App Gallery**. Try it out at xerox.com/VersaLink7100UI.

The standard 520-sheet² Tray 1

handles media sizes from 5.5 x 7.17 in to 11.69 x 17 in/139.7 x 182 mm to 297 x 431.8 mm.



Card Reader Bay with embedded USB port.³

MAXIMIZE PAPER CAPACITY WITH ONE OF THESE FEEDING OPTIONS²

The Single Tray Module

(optional with desktop model) increases total paper capacity to 1,140 sheets (includes Bypass Tray).



The Stand Module

offers total paper capacity of 1,140 sheets (includes Bypass Tray) and provides storage for toner cartridges and other supplies



The Three Tray Module

(optional with desktop model) increases total paper capacity to 2,180 sheets (includes Bypass Tray).



The Tandem Tray Module

allows for total paper capacity of up to 3,140 sheets (includes Bypass Tray).



The High-Capacity Feeder

holds 2,000 sheets of Letter/A4 paper, increasing the maximum paper capacity to 5,140 sheets.



The Envelope Tray

can replace Tray 1 to provide feeding of up to 60 envelopes.



INCREASE VERSATILITY WITH FINISHING OPTIONS²



The Office Finisher

provides advanced finishing functions, 2,000 sheet stacker, 3 position stapling and optional hole punch.



The Office Finisher with Booklet Maker

simplifies booklet making, including score and saddle-stitch. Use it to create 64-page saddle-stitched booklets (2 to 16 sheets).



The Work Surface and Convenience Stapler

staples up to 50 sheets and provides plenty of elbow room to sort documents.



The Dual Off-set Catch Trays⁴

stack up to 250 sheets each.




The Integrated Office Finisher

provides 500-sheet stacking and 50-sheet, dual position stapling.

Xerox® VersaLink® C7120/C7125/C7130

Color Multifunction Printer



DEVICE SPECIFICATIONS		VersaLink C7120	VersaLink C7125	VersaLink C7130
Speed ⁵		Up to 20 ppm	Up to 25 ppm	Up to 30 ppm
Monthly Duty Cycle ⁶		Up to 87,000 pages	Up to 107,000 pages	Up to 129,000 pages
Hard Drive/Processor/Memory		320 GB HDD ⁴ /1.05 GHz Dual core/4 GB Memory		
Connectivity		Ethernet 10/100/1000 Base-T, High-speed USB 3.0, Wi-Fi® and Wi-Fi Direct® with optional Wi-Fi Kit, NFC Tap-to-Pair		
Controller Features		Unified Address Book, Configuration Cloning, Scan Preview, Xerox Extensible Interface Platform®, Xerox® App Gallery App, Xerox® Standard Accounting Tool, Role Based Permissions, Convenience Authentication Enabled, Online Support		
Copy and Print	Resolution	Copy: Up to 600 x 600 dpi; Print: Up to 1200 x 2400 dpi		
First-copy-out Time (as fast as)		As fast as 8.1 seconds color/ As fast as 5.7 seconds black-and-white	As fast as 8.1 seconds color/ As fast as 5.7 seconds black-and-white	As fast as 6.7 seconds color/ As fast as 4.4 seconds black-and-white
First-print-out Time (as fast as)		As fast as 8.8 seconds color/ As fast as 6.9 seconds black-and-white	As fast as 8.8 seconds color/ As fast as 6.7 seconds black-and-white	As fast as 7.0 seconds color/ As fast as 5.4 seconds black-and-white
Page Description Languages		PCL® 5e/PCL 6/PDF/XPS/TIFF/JPEG/HP-GL/optional Adobe® PostScript® 3™		
Paper Input²	Standard	Single-Pass Duplex Automatic Document Feeder (DADF): 130 sheets; Speed: up to 80 ipm; Custom sizes: 1.93 x 3.35 in to 11.69 x 17 in/49 x 85 mm to 297 x 431.8 mm		
		Bypass Tray: 100 sheets; Custom sizes: 3.5 x 3.87 in to 11.69 x 17 in/88.9 x 98.4 mm to 297 x 431.8 mm		
		Tray 1: 520 sheets; Custom sizes: 5.5 x 7.17 in to 11.69 x 17 in/139.7 x 182 mm to 297 x 431.8 mm		
	Choose One	Single Tray Module: 520 sheets; Custom sizes: 5.5 x 7.17 in to 11.69 x 17 in/139.7 x 182 mm to 297 x 431.8 mm Single Tray with Stand Module: 520 sheets; Custom sizes: 5.5 x 7.17 in to 11.69 x 17 in/139.7 x 182 mm to 297 x 431.8 mm Three Tray Module (1,560 sheets): 520 sheets each; Custom sizes: 5.5 x 7.17 in to 11.69 x 17 in/139.7 x 182 mm to 297 x 431.8 mm Tandem Tray Module (2,520 sheets): Tray 2: 520 sheets; Custom sizes: 5.5 x 7.17 in to 11.69 x 17 in/139.7 x 182 mm to 297 x 431.8 mm; Tray 3: 870 sheets; Standard sizes: 8.5 x 11 in and 7.25 x 10.5 in/A4 or B5; Tray 4: 1,130 sheets; Standard sizes: 8.5 x 11 in and 7.25 x 10.5 in/A4 or B5		
	Optional	Envelope Tray: Up to 60 envelopes: #10 commercial, Monarch, DL, C5; Custom sizes: 3.9 x 5.8 in to 6.4 x 9.5 in/98 x 148 mm to 162 x 241 mm High-Capacity Feeder (HCF): 2,000 sheets; Standard sizes: 8.5 x 11 in and 7.25 x 10.5 in/A4 or B5		
Paper Output/Finishing²	Standard	500-sheet Center Tray		
	Optional	Dual Off-set Catch Trays⁵: 250 sheets each; Lower tray offsets Integrated Office Finisher: 500-sheet stacker, 50 sheets stapled, dual position stapling Office Finisher: 2,000-sheet stacker, 50 sheets stapled, 3-position stapling, optional hole-punch, optional booklet maker (score, saddle stitch) Convenience Stapler and Work Surface: Staples 50 sheets		

INTUITIVE USER EXPERIENCE

Customize	Customize user interface, show/hide functions, personalize user experience with authentication, create 1-Touch Apps
Print Drivers	Job Identification, Bi-directional Status, Job Monitoring, Xerox® Global Print Driver®, Application Defaults, Xerox® Pull Print Driver
Xerox® Embedded Web Server	PC or Mobile — Status Information, Settings, Device Management, Cloning, Remote Control Panel
Print Features	Print from USB, Sample Set, Saved Job, Booklet Creation, Store and Recall Driver Settings, Scaling, Job Monitoring, Application Control, Two-sided Printing, Draft Mode; Optional: Print From Cloud Repositories (Dropbox, OneDrive, and Google Drive) via optional apps
Scan and Fax	Scan Preview, Scan to USB/Email/Network (FTP/SFTP/SMB), Scan File Formats: PDF, PDF/A, JPG, TIFF; Convenience Features: Scan to Home, Searchable PDF, Single/Multi-page PDF/TIFF, Password-protected PDF; Fax Features: Walk-up Fax (one-line or three-line options available, includes LAN Fax, Direct Fax, Fax Forward to Email), Fax dialing, Unified Address Book, Optical Character Recognition (OCR), Server Fax, TWAIN driver (scan); Optional: Scan To Cloud Repositories (Dropbox, OneDrive, and Google Drive)

MOBILE AND CLOUD READY

Mobile Connectivity	Near Field Communication (NFC); Optional: Wi-Fi Direct, Wi-Fi (802.11 b/g/n/ac); AirPrint™ (iOS) including iBeacon (Bluetooth)
Mobile Printing	Mopria® Print Service, Apple AirPrint™, Xerox® Print Service (Android), Xerox® @PrintByXerox App; Optional: Xerox® Workplace Mobile App (iOS/Android)
Mobile Scanning	Mopria® Scan, Apple AirPrint™; Optional: Xerox® Workplace Mobile App (iOS/Android)
Cloud Ready	Remote services enabled; Optional: direct connection to cloud hosted services via optional apps (accessed via Xerox App Gallery app or visit xerox.com/AppGallery)

COMPREHENSIVE SECURITY

Network Security	802.1x, IPsec, HTTPS, SFTP and Encrypted Email, Trellix® Enterprise Security Manager ¹ , LogRhythm SIEM ¹ , Splunk SIEM ¹ , Network Authentication, SNMPv3, SHA-256 Hash Message Authentication, TLS 1.1/1.2/1.3, Security Certificates utilizing ECDSA, Automatic Self-signed Certificate, Cisco® Identity Services Engine (ISE) integration, Local Authentication (Internal Database), FIPS 140-2
Device Access	User Access and Internal Firewall, Port/IP/Domain Filtering, Audit Log, Access Controls, User Permissions, TPM; Optional: Smart Card Enablement Kit (CAC/PIV/.NET/SIPRNet) ⁷ , Xerox® Integrated RFID Card Reader, NFC standard (authentication via optional Xerox® Workplace Cloud/Suite Print Management and Content Security; learn more at xerox.com/WorkplaceSolutions)
Data Protection	Trellix® Embedded Control and Integrity Control Whitelisting/Allowlisting, Firmware Verification, Job Level Encryption via HTTPS and Drivers, Encrypted and Signed Email; Encrypted Hard Disk (AES 256-bit, FIPS 140-2) with Image Overwrite; Optional: Xerox Workplace Cloud/Suite Content Security
Document Security	Under evaluation Common Criteria Certification (ISO 15408) full system against the HCD PP, Encrypted Secure Print, FIPS 140-2 Encrypted Data with Print Drivers

ENABLES MANAGED PRINT SERVICES

Print Management	Xerox® Standard Accounting; Optional: Xerox Workplace Suite/Cloud, Xerox® Virtual Print Management Service, more at xerox.com/PrintManagement
Fleet/Device Management	Xerox® CentreWare® Web, Xerox® Support Assistant, Automated Meter Read, Xerox® Cloud Fleet Management Solution, Configuration Cloning; Xerox® Easy Assist App; Optional: Managed Print Services Suite, Cloud-based remote management with Xerox Workplace Cloud ⁷
Security	Secure Device Management: Xerox® Printer Security Audit Service (auto-configuration of security settings, monitoring, and auto-remediation), Digital Certificate Management, SIEM Reporting, Interactive Dashboard Reports

GATEWAY TO NEW POSSIBILITIES

Xerox and Partner Apps	Automate everyday processes with apps that translate, redact, convert text to audio or handwritten notes to text files, and paper documents to Microsoft applications, all from a single cloud-based platform. Or visit xerox.com/WorkplaceApps to find apps by industry or workflow
Software and Solutions	Xerox DocuShare (xerox.com/ecm), XMPie (xerox.com/XMPie), Xerox Workplace Solutions (xerox.com/WorkplaceSolutions), Xerox WorkFlow Central Platform

¹ SIEM support with Xerox® Device Manager. ² Paper capacities are based on 20 lb/75 gsm stock; capacities will vary with different weight stocks. ³ USB ports can be disabled. ⁴ HDD and Dual Off-set Catch Trays are optional on Desktop model. ⁵ Declared print speed in accordance with ISO/IEC 24734. ⁶ Maximum volume capacity expected in any one month. Not expected to be sustained on a regular basis. ⁷ Not available in all markets. ⁸ Trellix formerly known as McAfee. Device firmware will reflect Trellix brand change in future software release. Certifications: xerox.com/OfficeCertifications

More information is available at xerox.com/VersaLink.

