

PERFORMANCE

Processor^[1]

Intel® Core™ i7-11700 (8C / 16T, 2.5 / 4.9GHz, 16MB)

Graphics

NVIDIA® GeForce GTX 1660 SUPER 6GB GDDR6

Chipset

Intel® B560 Chipset

Memory

2x 8GB UDIMM DDR4-3200

Memory Slots

Four DDR4 UDIMM slots, dual-channel capable

Max Memory^[2]

Up to 128GB DDR4-3200

Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe® + 1TB HDD 7200rpm
3.5"

Optane™ Memory

None

Storage Support^{[3][4]}

Up to five drives, 2x 3.5" HDD + 2x M.2 SSD + 1x open 2.5 HDD Bay

- 3.5" HDD up to 2TB each
- M.2 SSD up to 1TB each

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC887 codec

Speakers

No speakers

Power Supply

650W 90%

DESIGN

Keyboard

USB Calliope Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Optional Bay

2.5" HDD bay

Expansion Slots

- One PCIe® 4.0 x16
- One PCIe® 3.0 x4
- Three M.2 slots (one for WLAN, two for SSD)

Case Color

Black

System Lighting

Legion OY Iconic LED + Internal Ambient Lighting

Chassis

Transparent Cover

Cooler

150W Airflow with RGB Light + M.2 SSD DECO Mylar®
Heatsink

System Fan

2x Front for Airflow with ARGB + 1x Rear for Airflow with ARGB

Carry Handle

Carry Handle

Form Factor

Tower (26L)

Dimensions (WxDxH)^[5]

205 x 396 x 411 mm (8.1 x 15.6 x 16.2 inches)

Weight^[6]

14 kg (30.86 lbs)

CONNECTIVITY

Ethernet

Integrated 100/1000M

WLAN + Bluetooth^[7]

Wi-Fi® 6, 11ax 2x2 + BT5.1

Top Ports

- 2x USB 3.2 Gen 1
- 1x headphone (3.5mm)
- 1x microphone (3.5mm)

Rear Ports

- 1x USB-C® 3.2 Gen 2 (support data transfer and 5V@3A charging)
- 2x USB 2.0
- 2x USB 3.2 Gen 1
- 1x Ethernet (RJ-45)
- 1x power connector
- 3x audio out (5.1 channel)

Optional Rear Ports (configured)

1x DVI, 1x HDMI® 2.0b, 1x DP 1.4 on NVIDIA® GeForce GTX 1660 SUPER

SERVICE

Base Warranty

1-year, Mail-in

Included Upgrade

3Y Legion Ultimate Support with Onsite

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0 (only available for MT 90RS)
- ErP Lot 3
- RoHS compliant

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

None

MODEL

TopSeller : Yes

Announce Date : 2022-04-05

EAN / UPC / JAN : 196801058163

End of Support : 2027-04-22



intel

Product image is a sample, it may not match the real color of this model

Note:

[1] Intel UHD Graphics in processor is disabled.

Intel Max Turbo frequency will vary depending on application workload and the hardware and software configurations, see <http://www.intel.com/technology/turboboost/> for more information.

[2] The max memory is based on the test results with current Lenovo memory offerings.

[3] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[4] 2.5" HDD bay is for customer self upgrade purpose and the hard drive is sold separately.

[5] The system dimensions may vary depending on configurations.

[6] The system weight is approximate and based on results in.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/1617?M=90RS0026US>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.



ThinkPad USB3.0 to Ethernet Adapter

4X90S91830

The ThinkPad USB3.0 to Ethernet Adapter is quick and easy way to connect your notebook and desktop to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference