

## PERFORMANCE

### Processor

Intel® Celeron® N4000 (2C / 2T, 1.1 / 2.6GHz, 4MB)

### Graphics

Integrated Intel UHD Graphics 600

### Chipset

Intel SoC Platform

### Memory

4GB Soldered LPDDR4-2400

### Memory Slots

Memory soldered to systemboard, no slots, single-channel (4GB models)

### Max Memory

4GB soldered memory, not upgradable

### Storage

64GB eMMC 5.1

### Storage Support

64GB eMMC 5.1 on systemboard

### Card Reader

MicroSD Card Reader

### Optical

None

### Audio Chip

High Definition (HD) Audio, Maxim MAX98357A Dialog DA7219 codec

### Speakers

Stereo speakers, 2W x2

### Camera

HD 720p

### Microphone

Mono

### Battery

Integrated 42Wh

### Max Battery Life

Google power load test: 10 hr

### Power Adapter

45W USB-C® (3-pin)

## DESIGN

### Display

11.6" HD (1366x768) IPS 250nits Glossy, Touch

### Touchscreen

10-point Multi-touch

### Keyboard

Non-backlit, French / English

### Case Color

Abyss Blue

### Surface Treatment

Aluminum Stamping (Anodized)

### Case Material

Aluminium (Top), PC + ABS (Bottom)

### Pen

None

### Dimensions (WxDxH)

290 x 207.8 x 17.8 mm (11.41 x 8.18 x 0.70 inches)

### Weight

Around 1.2 kg (2.65 lbs)

## SOFTWARE

### Operating System

Chrome OS

### Bundled Software

None

## CONNECTIVITY

### Ethernet

None

### WLAN + Bluetooth®

Wi-Fi® 5 11ac, 2x2 + BT4.2

### NFC

None

### Standard Ports

- 2x USB 3.2 Gen 1
- 2x USB-C 3.2 Gen 1 (support data transfer, Power Delivery, and DisplayPort™ 1.1a)
- 1x Card reader
- 1x Headphone / microphone combo jack (3.5mm)

## SECURITY & PRIVACY

### Security Chip

Google Security Chip H1

### Fingerprint Reader

None

### Physical Locks

Kensington® Security Slot™, 3 x 7 mm

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

None

## ACCESSORIES

### Bundled Accessories

None

## CERTIFICATIONS

### Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

## MODEL

TopSeller : No

Announce Date : 2022-02-14

EAN / UPC / JAN : 196380607998

End of Support : 2026-04-03



· Lenovo reserves the right to change specifications or other product information without notice.

· Product image on this page is a sample, it may not match the real color of this model

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.


## Recommended Accessories



### Lenovo 65W USB-C DC Travel Adapter

40AK0065WW

Power up and stay productive on the road with this DC Travel adapter. Lenovo 65W USB-C DC Travel Adapter is the universal DC adapter, providing 65W power via USB-C for outdoor use.



### ThinkPad Professional 15.6-inch Backpack

4X40Q26383

The Lenovo ThinkPad Professional Backpack is a streamlined yet versatile backpack for the on-the-go professional. This clean, modern design carries, protects, and organizes your mobile office, while premium, lightweight...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

PSREF  
Product Specifications  
Reference