


2-Post 21U Heavy-Duty Wall Mount Network Rack, 19" Open Frame Server Rack with Adjustable Depth, Wall Mount Data Rack for IT / AV / Patch Panel / Computer Equipment - Cage Nuts and Screws Included

**Product ID:** RACK-21U-20-WALL-OA



The RACK-21U-20-WALL-OA 21U Open Frame Wall Mount Equipment Rack with Adjustable Depth is a high-quality, sturdy relay rack solution that is easy to assemble and install into any environment.

The open rack features an adjustable depth ranging from 12-20 inches to accommodate larger data, network, and telecommunications devices. With a maximum depth of 20 inches, this rack allows for mounting of shelves and other accessories with enough clearance at the back for cable management. The open-frame design help to keep your equipment cool and easily accessible from different angles. The wall mounting holes are positioned 12 and 16 inches apart (center to center) providing a convenient and effecting anchoring, making it suitable for mounting on virtually any wall surface or construction framework.

This 21U rack includes M6 square cage nuts and M6 screws to save you the hassle of sourcing separate mounting hardware for your equipment. This rack can be mounted to the wall in a server room, data closet, or office expanding your valuable floor space.

## Certifications, Reports and Compatibility

## Applications

## Features

- **ADJUSTABLE DEPTH:** This 2-post 21U 19 inch open frame network rack is EIA/ECA-310 compliant and has an adjustable depth (12-20in / 30.5-50.8cm); Data rack is ideal for AV / Audio / IT / computer equipment, servers, switches, patch panels, and PDUs

- **HEAVY DUTY:** Durable rack features a vertical rail made of 2.0mm SPCC cold-rolled steel and a weight capacity of up to 200lbs/90kg; Its design supports unobstructed airflow to help keep your equipment cool and easy to install with access to all sides
- **EFFICIENT FLAT PACK SHIPPING:** The IT rack ships flat packed with ISTA-6 certified packaging (assembly required) to ensure hassle-free installations with complete and undamaged delivery; Comprehensive assembly instructions included
- **HARDWARE INCLUDED:** The open post wall mount server rack includes a complete set of M6 square cage nuts, M6 screws and plastic washers to securely mount all of your equipment in the rack
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 21U wall mounted network rack is backed for 5-years, including free lifetime 24/5 multi-lingual technical assistance

#### Hardware

Warranty	5 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	21U
Special Features	Easy Assembly Wall-Mountable
Mounting Rail Profile	G-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

#### Performance

Weight Capacity	198.4 lb [90 kg]
-----------------	------------------

#### Physical Characteristics

Color	Black
Construction Material	Steel
Product Length	20.0 in [50.8 cm]
Product Width	19.8 in [50.4 cm]

Product Height	3.4 ft [1.0 m]
Weight of Product	36.2 lb [16.4 kg]
Maximum Mounting Depth	20.0 in [50.8 cm]

---

#### Packaging Information

Package Quantity	1
Package Length	16.5 in [42.0 cm]
Package Width	3.8 ft [1.2 m]
Package Height	6.3 in [16.0 cm]
Shipping (Package) Weight	44.5 lb [20.2 kg]

---

#### What's in the Box

Included in Package	2 - Front Horizontal Brackets
	2 - Rear Horizontal Brackets
	2 - Vertical Brackets
	84 - M6 Cage Nuts
	84 - M6 Cage Screws
	84 - Plastic Washers
	16 - M5x12mm Assembly Screws
	24 - M8x16mm Bolts
	24 - #8 Flat Washers
	1 - Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***