

**PERFORMANCE****Processor**

Intel® Xeon® W-2225 (4C / 8T, 4.1 / 4.6GHz, 8.25MB)

**Processor Sockets**

1x FCLGA2066

**Discrete Graphics**

NVIDIA® RTX A4500 20GB

**Chipset**

Intel C422

**Memory**

1x 32GB RDIMM DDR4-2933 ECC

**Memory Slots**

4 DDR4 DIMM slots, 4 channels capable

**Max Memory**

Up to 256GB (4x 64GB RDIMMs) DDR4-2933

**M.2 SSD RAID Controller**

RAID 0/1

**M.2 SSD Drive**

1x 1TB SSD M.2 PCIe® NVMe® Opal

**HDD Controller**

Onboard Intel RSTe SATA

**Storage Support**

Up to 4x 3.5" SATA HDD / 2.5" SATA HDD / 2.5" SATA SSD + 5x M.2 PCIe SSD

- 3.5" HDD up to 6TB each
- 2.5" SATA HDD up to 500GB each
- 2.5" SATA SSD up to 2TB each
- 2.5" SAS HDD up to 600GB each
- M.2 SSD up to 2TB each

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC662 codec

**Power Supply**

625W Platinum Fixed

**DESIGN****Keyboard**

USB Traditional Keyboard, Black, English

**Mouse**

USB Calliope Mouse

**Expansion Slots**

- One PCIe 3.0 x4
- One PCIe 3.0 x8
- Two PCIe 3.0 x16

**M.2 Slots**

Up to 5x M.2 SSD:

- 2 via onboard slots
- 3 via Single M.2 to PCIe adapter

**Bays**

- 2x 3.5" disk bay (standard)
- 2x 3.5" disk bay (optional, via flex bay)

**Flex Bays**

2x flex bays, supports the following:

- 2x half-height optical drives
- 2x 5.25" 9.0mm optical drives
- 1x 5.25" 9.0mm optical drive + 2x 3.5"/2.5" SATA SSD/HDD
- 1x 3.5"/2.5" SATA SSD/HDD with Front Access Storage Enclosure
- 1x flex module for the following options:

Tray 1: 9.0mm optical

Tray 2: 15-in-1 USB 3.1 Gen 1 reader, 2x Thunderbolt™, or 4-digit diagnostic display

Port 1 and 2: Front USB 3.1 Gen 1 Type-C or eSATA

**Dimensions (WxDxH)**

175 x 426 x 376 mm (6.89 x 16.77 x 14.8 inches, with feet)

**Weight**

14.5 kg (31.96 lbs, maximum configuration)

**CONNECTIVITY****Onboard Ethernet**

Intel I219-LM, 1x GbE RJ-45

**Card Reader**

SD Card Reader

**Front Ports**

- 2x USB 3.1 Gen 1
- 1x headphone (3.5mm)
- 1x microphone (3.5mm)

**Rear Ports**

- 2x USB 2.0
- 4x USB 3.1 Gen 1
- 2x PS/2 ports (keyboard / mouse)
- 1x Ethernet (RJ-45)
- 1x line-in (3.5mm)
- 1x line-out (3.5mm)
- 1x microphone (3.5mm)

**SECURITY & PRIVACY****Security Chip**

Discrete TPM 2.0, TCG certified

**Physical Locks**

Kensington® Security Slot, 3 x 7 mm

**MANAGEABILITY****System Management**

Intel® vPro with AMT 11

**SERVICE****Base Warranty**

3-year, Onsite

**Included Upgrade**

3Y Premier Support Upgrade from 3Y Onsite (5WSOU26649)

**CERTIFICATIONS****Green Certifications**

- EPEAT™ Silver
- ENERGY STAR® 8.0 (on model 30BX0095US)
- GREENGUARD®
- RoHS compliant

**ISV Certifications**Please visit [www.thinkworkstations.com/isv-certifications/](http://www.thinkworkstations.com/isv-certifications/)**SOFTWARE****Operating System**

Windows® 11 Pro 64 for Workstations, English

**MODEL**

TopSeller : Yes

Announce Date : 2022-04-21

EAN / UPC / JAN : 196379906439

End of Support : 2025-12-21



## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

## Recommended Services

BEST	5Y Lenovo Protect (Premier Support + ADP + KYD + International Upg) (5PS1D67032)
BETTER	5Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67028)
GOOD	4Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67027)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference