

NEW A Series

10000nit High Brightness Energy-saving LED Display



P4 | P6 | P8 | P10



High Brightness
& Energy Saving



Extremely Real
Display Performance



High Stability
& Reliability



Very Low Operating Cost
Throughout Product's Life Cycle

► **Meet various medium and high-end outdoor advertising scenarios needs**



Billboard



Spectacular



Street Furniture



Transit Center



Sports

► Extremely Real Display Performance

Dazzling and Vivid Images, to make you see the most natural and real world



Up to 10000nit
High Brightness



3840+ Hz
High Refresh Rate



16bit
High Gray Scale



10000+: 1
High Contrast Ratio



150% BT.709
Wide color gamut



PWM
High level driving IC

► High Stability & Reliability

Multi-layered water resistant design involving modules/panels/power boxes to ensure safety.



Professional heat dissipation structure design.
Free of Fan Design



► Very Low Operating Cost Throughout Product's Life Cycle



Savings in electricity costs



Light weight panel, saving steel structure cost



Thin panel, convenient transport, save transport cost



Convenient maintenance-front and rear access

Parameters	A0421	A0621	A0821	A1021	Unit
Pixel pitch	4.44	6.66	8	10	mm
LED	SMD	SMD	SMD	SMD	—
Brightness	7500	10000	10000	10000	nit
Refresh rate	>3840	>6000	>15000	>15000	hz
Grayscale	16	16	16	16	bit
Power consumption (max./avg.)	570/190	660/ 220	675/ 225	675/ 225	w/sq.m
Viewing angle (H/V)	160/85	160/75	160/75	160/80	deg
Contrast	14000:1	12000:1	19000:1	22000:1	—
Panel dimensions(W*H*D)	1280x960x70	1280x960x72	1280x960x72	1280x960x72	mm
Panel weight	31		32		kg
Panel material	Aluminum Profile				—
Ingress protection	IP65/IP54				—
Certification	ETL/FCC/CE/CCC				—

7120 Lake Ellenor Dr, Orlando, FL 32809

Contact us 407.203.8870; info@usabsen.com; www.usabsen.com

East Service Center 7307
Presidents Drive, Orlando