

**Full size Z tower power at half the size**

Get all the power of a full size tower at a fraction of the size. Re-engineered to fit full-height, full-length graphics while leaving room for upgrades and expansion, the Z2 SFF delivers high performance for your intensive workflow—from 3D design to real time ray tracing—now and in the future.



HP recommends Windows 11 Pro for business

Full height, full length performance

Design, simulate and—for the first time—real time ray trace on a Z2 SFF. Now fitting full height, full length professional graphics and Intel® processors, this PC delivers tower-sized performance that defies space constraints.

Configurable for today. Expandable for tomorrow.

Accelerate your current workflow with a multitude of options across processor, graphics, memory, storage, and I/O ports. And with plenty of room to upgrade and expand, this PC is ready to grow with you as your workflow evolves.

Industry leading security. Reliability you can trust.

Get peace of mind with a PC that's built to endure. The Z2 SFF undergoes 360K hours of rigorous testing, military-standard testing[1] and is certified for pro apps. And with HP Wolf Security for Business[2], it's protected below, in and above the OS.

Featuring**Intel® Core™ i7 processor**

Run several CPU-heavy programs simultaneously without sacrificing performance with an Intel® Core™ i7 processor. [3]

Security is your top priority

The HP Wolf Pro Security Edition provides preconfigured enterprise-level PC protection for small and medium sized businesses.

Specifications

Operating system	Windows 11 Pro
Processor family	12th Generation Intel® Core™ i7 processor
Processor	Intel® Core™ i7-12700 (up to 4.9 GHz with Intel® Turbo Boost Technology, 25 MB L3 cache, 12 cores, 20 threads) ^[6,7]
Memory	16 GB DDR5-4800 MHz RAM (1 x 16 GB)
Internal Storage	512 GB HP Z Turbo Drive PCIe® NVMe™ TLC M.2 SSD
Internal drive bays	One 2.5" HDD; One 3.5" HDD; Three M.2 NVME 2280 SSD
External drive bays	One 3.5" HDD; One slim ODD
Optical drive	Not included
Graphics	Discrete
Graphics (discrete)	NVIDIA® T1000 (4 GB GDDR6 dedicated)
Graphics	Integrated
Graphics (integrated)	Intel® UHD Graphics 770
Compatible displays	All HP Z Displays and HP DreamColor Displays are supported. For more information see www.hp.com/go/zdisplays (<i>Supports 8 displays, driving 8 displays requires the use of integrated and discrete graphics ports. Each source can drive a total of 4 displays. At least one of the integrated graphics ports need to drive two displays in a daisy chain configuration.</i>)
Audio	Realtek ALC3205-VA2-CG, 2.0W internal mono speaker
Minimum dimensions (W x D x H)	38.4 x 30.8 x 10 cm (Standard desktop orientation.)
Minimum dimensions (W x D x H)	15.1 x 12.1 x 3.95 in (Standard desktop orientation.)
Weight	Starting at 5.9 kg (Exact weights depend upon configuration (System weight only))
Weight	Starting at 13.1 lb (Exact weights depend upon configuration (System weight only))
Keyboard	HP USB 320K Keyboard
Pointing device	HP Wired 320M Mouse
Ports	4 SuperSpeed USB Type-A 10Gbps signaling rate (1 charging); 1 universal audio jack
Expansion slots	1 PCIe 3 x4 (x16 connector); 1 PCIe 3 x4 (x4 connector); 1 PCIe 3 x1 (x4 connector); 1 PCIe 4 x16 (x16 connector); 3 M.2 2280 PCIe 4 X4 for NVMe; 1 M.2 2230 PCIe 3 X1 for WLAN (1 M.2 2230 slot for WLAN and 3 M.2 2280 slots for storage)
Ports	1 audio-in; 1 audio-out; 1 RJ-45; 2 DisplayPort™ 1.4; 2 SuperSpeed USB Type-A 10Gbps signaling rate; 1 SuperSpeed USB Type-A 5Gbps signaling rate; 3 USB Type-A 480Mbps signaling rate
Package dimensions (W x D x H)	10 x 38.4 x 30.8 cm
Package weight	Starting at 5.0 kg
Ecolabels	EPEAT® registered
Energy star certified	ENERGY STAR® certified
Management features	HP Driver Packs; HP Management Integration Kit for Microsoft System Center Configuration Management Gen4; HP System Software Manager (download); HP BIOS Configuration Utility (download) ^[18]
Sustainable impact specifications	Ocean-bound plastic in speaker enclosure; 45% post-consumer recycled plastic; 25% ITE-derived closed loop plastic; Bulk packaging available; 80 Plus® Gold power supplies available; Molded paper pulp cushion inside box is 100% sustainably sourced and recyclable; Ocean-bound plastic in speaker enclosure and system fan; Contains recycled metal
Security management	HP Secure Erase; HP Sure Click; HP BIOSphere Gen6; HP Sure Admin; Hood Sensor Optional Kit; HP Client Security Manager Gen6; HP Sure Start Gen7; HP Sure Recover Gen4; HP Sure Sense Gen2; HP Sure Run Gen5 ^[19,20,21,22,23,24,25,26,31]
Software included	HP PC Hardware Diagnostics UEFI; HP Support Assistant; HP PC Hardware Diagnostics Windows; ZCentral Remote Boost; HP Image Assistant; HP Manageability Integration Kit; Performance Advisor 3.0 ^[15,16,17]
UPC number	(ABA) 196548995790; (ABC) 196548995813

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] HP Wolf Security for Business requires Windows 10 or higher, includes various HP security features and is available on HP Pro, Elite, RPOS and Workstation products. See product details for included security features and OS requirement.

[2] MIL STD testing is not intended to demonstrate fitness for U.S. Department of Defense contract requirements or for military use. Test results are not a guarantee of future performance under these test conditions. Accidental Damage or damage under these test conditions requires an optional HP Accidental Damage Protection Care Pack.

[3] Multicore is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

Technical Specifications Footnotes

[6] Multi-core is designed to improve performance of certain software products. Not all customers or software applications will necessarily benefit from use of this technology. Performance and clock frequency will vary depending on application workload and your hardware and software configurations. Intel's numbering, branding and/or naming is not a measurement of higher performance.

[7] Intel® Turbo Boost performance varies depending on hardware, software and overall system configuration. See <http://www.intel.com/technology/turboboost/> for more information.

[15] HP ZCentral Remote Boost does not come preinstalled on Z Workstations but can be downloaded and run on all Z desktop and laptops without license purchase. With non-Z sender devices, purchase of perpetual individual license or perpetual floating license per simultaneously executing versions and purchase of ZCentral Remote Boost Software Support is required. RGS requires Windows, RHEL (7 or 8), UBUNTU 18.04 LTS, or HP ThinPro 7 operating systems. MacOS (10.13 or newer) operating system is only supported on the receiver side. Requires network access. The software is available for download at hp.com/ZCentralRemoteBoost.

[16] HP Performance Advisor Software - HP Performance Advisor is ready and waiting to help you get the most out of your HP Workstation from day one—and every day after. Learn more or download at: <https://www8.hp.com/us/en/workstations/performance-advisor.html>

[17] HP Support Assistant requires Windows and Internet access.

[18] HP Manageability Integration Kit can be downloaded from <http://www8.hp.com/us/en/ads/clientmanagement/overview.html>

[19] HP Client Security Manager Gen7 requires Windows and is available on the select HP PCs.

[20] HP BIOSphere Gen6 features may vary depending on the platform and configurations.

[21] HP Sure Click requires Windows 10 Pro or higher or Enterprise. See https://bit.ly/2PrLT6A_SureClick for complete details.

[22] HP Sure Start Gen7 is available on select HP PCs and workstations. See product specifications for availability.

[23] HP Sure Run Gen5 is available on select HP PCs and requires Windows 10 and higher.

[24] HP Sure Recover Gen4 is available on select HP PCs and requires an open network connection. You must back up important files, data, photos, videos, etc. before using HP Sure Recover to avoid loss of data.

[25] HP Secure Erase for the methods outlined in the National Institute of Standards and Technology Special Publication 800-88 "Clear" sanitation method. HP Secure Erase does not support platforms with Intel® Optane™.

[26] HP Sure Sense requires Windows 11 Pro or Enterprise and supports Microsoft Internet Explorer, Google Chrome™, and Chromium™. Supported attachments include Microsoft Office (Word, Excel, PowerPoint) and PDF files in read only mode, when Microsoft Office or Adobe Acrobat are installed.

[31] HP Sure Admin requires Windows 10 or higher, HP BIOS, HP Manageability Integration Kit from <http://www.hp.com/go/clientmanagement> and HP Sure Admin Local Access Authenticator smartphone app from the Android or Apple store.

© Copyright 2022 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Intel, Pentium, the Intel logo, Intel Core, Thunderbolt, vPro, Optane, and Core Inside are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries. Bluetooth is a trademark of its proprietor, used by HP Inc. under license. USB Type-C® and USB-C® are registered trademarks of USB Implementers Forum. Adobe PDF is a trademark of Adobe Systems Incorporated. ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. NVIDIA, the NVIDIA logo, Quadro, and GeForce are trademarks and/or registered trademarks of NVIDIA Corporation in the U.S. and other countries. Bluetooth is a trademark of its proprietor and used by HP Inc. under license. AMD and Radeon are trademarks of Advanced Micro Devices, Inc. All other trademarks are the property of their respective owners.

