

PERFORMANCE

Processor

Intel® Core™ i5-11300H (4C / 8T, 3.1 / 4.4GHz, 8MB)

Graphics

NVIDIA® GeForce RTX™ 3050 4GB GDDR6, Boost Clock 1500 / 1740MHz, TGP 90W

Chipset

Intel SoC Platform

Memory

1x 8GB SO-DIMM DDR4-3200

Memory Slots

Two DDR4 SO-DIMM slots, dual-channel capable

Max Memory

Up to 16GB DDR4-3200 offering

Storage

256GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

Storage Support

Up to two drives, 1x 2.5" HDD + 1x M.2 2242 SSD or 1x M.2 2242/2280 SSD + 1x M.2 2242 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 1TB

Storage Slot

One 2.5" drive slot + two M.2 slots

- One 2.5" drive slot, supports 2.5" HDD
 - One M.2 2242 PCIe Gen 3x4 slot, supports M.2 2242 SSD
 - One M.2 2280 PCIe Gen 3x2 slot, supports M.2 2242/2280 SSD
- 2.5" drive slot and M.2 2280 slot are used exclusively

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Nahimic Audio

Camera

HD 720p with Camera Shutter

Microphone

2x, Array

Battery

Integrated 45Wh

Max Battery Life

MobileMark® 2014: 8 hr

Power Adapter

135W Slim Tip (3-pin)

DESIGN

Display

15.6" FHD (1920x1080) IPS 250nits Anti-glare, 120Hz, 45% NTSC, DC dimmer

Touchscreen

None

Keyboard

White Backlit, English (US)

Case Color

Shadow Black

Surface Treatment

IMR (In-Mold Decoration by Roller)

Case Material

PC + ABS (Top), PC + ABS (Bottom)

Dimensions (WxDxH)

359.6 x 251.9 x 24.2 mm (14.16 x 9.92 x 0.95 inches)

Weight

Around 2.25 kg (4.96 lbs)

SOFTWARE

Operating System

Windows® 11 Home 64, English

Bundled Software

Office Trial

CONNECTIVITY

Ethernet

100/1000M

WLAN + Bluetooth®

Wi-Fi® 6 11ax, 2x2 + BT5.0

Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C® 3.2 Gen 1 (support data transfer only)
- 1x HDMI® 2.0
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0

Fingerprint Reader

None

Other Security

Camera privacy shutter

SERVICE

Base Warranty

1-year, Depot

Included Upgrade

None

ACCESSORIES

Bundled Accessories

None

CERTIFICATIONS

Green Certifications

- ErP Lot 3
- RoHS compliant

MODEL

TopSeller : No

EAN / UPC / JAN : 196118027043

Announce Date : 2021-10-05

End of Support : 2027-05-29



intel

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

The ThinkPad Hybrid USB-C with USB-A Dock expands the capabilities of most any laptop, new or old, making it perfect for enterprise customers with mixed-PC or shared-desk environments. Featuring enterprise-class manag...

Recommended Services

BEST	3Y Premium Care with Onsite upgrade from 1Y Courier/Carry-in (5WS0T73714)
BETTER	3Y Onsite upgrade from 1Y Mail-in delivery (5WS0K75674)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K75663)

For a full list of accessories and services, please visit: <https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference