

PERFORMANCE

Processor

Intel® Core™ i5-1135G7 (4C / 8T, 2.4 / 4.2GHz, 8MB)

Graphics

Integrated Intel Iris® Xe Graphics

Chipset

Intel SoC Platform

Memory

4GB Soldered DDR4-3200 + 4GB SO-DIMM DDR4-3200

Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

Max Memory

Up to 12GB (4GB soldered + 8GB SO-DIMM) DDR4-3200 offering

Storage

256GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

Storage Support

Model with 38Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB

Storage Slot

Model with 38Wh battery: one 2.5" drive slot + one M.2 slot

- One 2.5" drive slot, supports 2.5" SATA HDD
- One M.2 2280 PCIe Gen 3x4 slot, supports M.2 2242/2280 SSD

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 1.5W x2, Dolby® Audio™

Camera

HD 720p with Privacy Shutter

Microphone

2x, Array

Battery

Integrated 38Wh

Max Battery Life

MobileMark® 2018: 5.5 hr (38Wh)

Power Adapter

65W Round Tip (2-pin, Wall-mount)

DESIGN

Display

15.6" FHD (1920x1080) TN 250nits Anti-glare, 45% NTSC

Touchscreen

None

Keyboard

Non-backlit, English (EU)

Case Color

Black

Surface Treatment

Texture

Case Material

PC + ABS (Top), PC + ABS (Bottom)

Dimensions (WxDxH)

359.2 x 235.8 x 19.9 mm (14.14 x 9.28 x 0.78 inches)

Weight

Starting at 1.7 kg (3.75 lbs)

SOFTWARE

Operating System

Windows® 10 Home 64, Benelux (EN/FR/DE/NL)

Bundled Software

Office Trial

CONNECTIVITY

Ethernet

100/1000M

WLAN + Bluetooth®

11ac, 2x2 + BT5.0

Standard Ports

- 1x USB 2.0
- 1x USB 3.2 Gen 1
- 1x USB-C® 3.2 Gen 1 (support data transfer only)
- 1x HDMI® 1.4b
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0

Fingerprint Reader

None

Physical Locks

Kensington® Nano Security Slot

Other Security

Camera privacy shutter

SERVICE

Base Warranty

1-year, Depot

Included Upgrade

2Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WSOQ81880)

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

Other Certifications

TÜV Rheinland® Low Blue Light

MODEL

TopSeller : Yes

Announce Date : 2021-04-09

EAN / UPC / JAN : 195477519305

End of Support : 2027-08-28



intel

- Lenovo reserves the right to change specifications or other product information without notice.
- Product image on this page is a sample, it may not match the real color of this model
- Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkPad Hybrid USB-C with USB-A Dock (American Standard Plug Type B)

40AF0135US

The ThinkPad Hybrid USB-C with USB-A Dock expands the capabilities of most any laptop, new or old, making it perfect for enterprise customers with mixed-PC or shared-desk environments. Featuring enterprise-class manag...



ThinkPad 15.6-inch Essential Topload Case

4X40E77328

Specifically designed for the budget-conscious customer who values a functional and lightweight case, the Essential Toploader offers uncompromising quality. Made of durable, lightweight nylon, this backpack boasts a p...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference