



[DOWNLOAD SPECS](#)

MAXIFY GX5020

Printer

Print Speed (up to) Black: ESAT Approx. 24.0 ipm⁸
Colour: ESAT Approx. 15.5 ipm⁸

Number of Nozzles Colour (C/M/Y): 1,024x3 / Pigment Black: 1,280 / Total: 4,352

Print Resolution (Up to) Up to 600 x 1200 dpi⁹

Ink Compatibility INK TYPE

GI-26 Pigment-Based Ink Bottles (Cyan, Magenta, Yellow, Black)

INK TANK & FILL VOLUME

GI-26 Black Ink Bottles: 167.0 ml

GI-26 C, M, Y Ink Bottles: 132.0 ml (each)

Paper Sizes 4" x 6", 5" x 5" (Square), 5" x 7", 7" x 10", 8" x 10", Letter (8.5" x 11"), Legal (8.5" x 14"), Executive, U.S. #10
Custom Size: Width: 3.5" - 8.5" / Length: 5" - 47"

Paper Compatibility Plain: Plain Paper, Canon High Resolution Paper;
Glossy: Photo Paper Plus Glossy II, Photo Paper Glossy;

Semi-Gloss: Photo Paper Plus Semi-Gloss, Photo Paper Pro Luster;
Matte: Matte Photo Paper, Double-sided Matte Paper;
Other (Canon): Magnetic Photo Paper, Restickable Photo Paper, Light Fabric Iron-on Transfers;
Other (non-Canon): Greeting Card, Envelopes, Recycled paper and Chlorine-free paper can be used

Rear Tray Supported Media Weight
Plain Paper: 64 - 105 gsm
Canon Paper: Max. approx. 265gsm (Canon PP-301) OR
Thicker Paper: approx. 115-250gsm

Bottom Cassette Supported Media Weight
Plain Paper: 64-105gsm

Printer Features Document Printing, Photo Printing, Wireless Printing⁷, Mobile Device Printing, Business Card Printing, Greeting Card Printing, Label Printing, Square Media Printing Support, Double-sided Matte Paper Support, Auto Duplex Printing

HIGH PAGE YIELD: Up to 6,000 (Black & White) / 14,000 (Colour)⁶

Paper Handling PAPER HANDLING
INPUT Bottom Cassette: 250 Sheets Plain Paper (Letter or Legal)
Rear Paper Tray: 100 Sheets of Plain Paper OR 20 Sheets (4 x 6)

AUTO DOCUMENT FEEDER
50 Sheets Plain Paper

Output Tray Capacity INPUT PAPER CAPACITY
Cassette: 250 Sheets Plain Paper (Letter)
Rear Paper Tray: 100 Sheets of Plain Paper (Letter) OR 20 Sheets (4 x 6)

Noise Level (Approx.) Approx. 49.0 dB(A) (Plain Paper)
Quiet Mode: Available

General

Other Features Auto Power On/Off, Print, Quiet Mode, Wireless Direct Connection¹, Wireless Connect¹, Auto Paper Width Detection, User Replaceable Print Head, User Replaceable Maintenance Cartridge

Display: 2-Line Mono LCD

Smart assistant & automation support: Amazon Alexa™¹⁴, Google Assistant™¹⁴

OS Compatibility Windows:¹⁰ Windows® 11 (64-bit), Windows 10, Windows 8.1, Windows 7 SP1, Windows Server 2008 R2 SP1, Server 2012 R2, Server 2016, and Server 2019
Mac:¹¹ macOS v10.13.6 - 12
Chromebook Compatible¹³
Mobile Operating Systems:¹² iOS®, iPadOS®, Android™

Standard Interface Hi-Speed USB
Wi-Fi® (Wireless LAN, 2.4/5 GHz, IEEE 802.11b/g/a/n)⁷
Wired LAN (100BASE-TX / 10BASE-T)

Wireless Information⁷
Standard: IEEE 802.11 b/g/a/n
Security: WPA-PSK (TKIP / AES), WPA2-PSK (TKIP / AES), WPA-EAP(AES)^, WPA2-EAP(AES)^
^IEEE802.1X (EAP-TLS/EAP-TTLS/PEAP) available

Wireless LAN Frequency Band(s): 2.4 GHz / 5 GHz
Wireless Direct Connection Capable/ Wireless Connect1 Capable: Yes

Software Included Included or available for download/installation:

SOFTWARE (WINDOWS¹⁵/MAC¹⁶) MAXIFY GX5020 Driver, Easy-PhotoPrint Editor Software¹⁵, PosterArtist Lite Software¹⁸, PosterArtist online version¹⁹

MOBILE APPS & PRINTING AirPrint®³, Mopria®⁴, Canon PRINT app², Easy PhotoPrint Editor App¹⁵, Canon Print Service¹⁶ (Android), PIXMA Cloud Link², Creative Park App¹⁷

Power Consumption (approx.) Energy Efficiency: Energy Star® Certified²²
Auto Power On / Off Capable: Yes
Input Voltage: AC 100 - 240 V, 50 / 60 Hz
Power Consumption: 20W (0.8W Standby / 0.2W Off)
TEC (Typical Electricity Consumption): 0.12 kWh

Dimension (W x D x H) Closed: 15.8" (L) x 16.4" (W) x 9.4" (H)
Trays Extended: 15.8" (L) x 25.2" (W) x 13.1" (H)

Weight Weight: 19.8 lbs.