

**PERFORMANCE****Processor**

Intel® Core™ i3-1215U, 6C (2P + 4E) / 8T, P-core 1.2 / 4.4GHz, E-core 0.9 / 3.3GHz, 10MB

**Graphics**

Integrated Intel UHD Graphics

**Chipset**

Intel SoC Platform

**Memory**

4GB Soldered DDR4-3200 + 4GB SO-DIMM DDR4-3200

**Memory Slots**

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

**Max Memory**

Up to 12GB (4GB soldered + 8GB SO-DIMM) DDR4-3200 offering

**Storage**

256GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

**Storage Support**

Models with 38Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB

- M.2 2242 SSD up to 512GB

**Storage Slot**

Models with 38Wh battery: one 2.5" drive slot + one M.2 slot

- One 2.5" SATA HDD slot
- One M.2 2280 PCIe 4.0 x4 slot

**Card Reader**

None

**Optical**

None

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC3287 codec

**Speakers**

Stereo speakers, 1.5W x2, Dolby® Audio™

**Camera**

HD 720p with Privacy Shutter

**Microphone**

2x, Array

**Battery**

Integrated 38Wh

**Max Battery Life**

Models with 38Wh battery:

MobileMark® 2018: up to 5.3 hr

Local video (1080p) playback@150nits: up to 6.85 hr

**Power Adapter**

65W Round Tip (3-pin)

**DESIGN****Display**

15.6" FHD (1920x1080) TN 250nits Anti-glare

**Touchscreen**

None

**Keyboard**

Non-backlit, English (UK)

**Case Color**

Business Black

**Surface Treatment**

Texture

**Case Material**

PC-ABS (Top), PC-ABS (Bottom)

**Dimensions (WxDxH)**

359 x 236 x 19.9 mm (14.13 x 9.29 x 0.78 inches)

**Weight**

Starting at 1.7 kg (3.74 lbs)

**SOFTWARE****Operating System**

Windows® 11 Home, English

**Bundled Software**

Office Trial

**CONNECTIVITY****Ethernet**

100/1000M (RJ-45)

**WLAN + Bluetooth®**

11ac 2x2 + BT5.0

**Standard Ports**

- 1x USB 2.0
- 1x USB 3.2 Gen 1
- 1x USB-C® 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.2)
- 1x HDMI®, up to 2.5K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

**SECURITY & PRIVACY****Security Chip**

Firmware TPM 2.0

**Fingerprint Reader**

None

**Physical Locks**

Kensington® Nano Security Slot™, 2.5 x 6 mm

**Other Security**

Camera privacy shutter

**SERVICE****Base Warranty**

1-year, Courier or Carry-in

**Included Upgrade**

None

**ACCESSORIES****Bundled Accessories**

None

**CERTIFICATIONS****Green Certifications**

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

**Other Certifications**

TÜV Rheinland® Low Blue Light (Software Solution)

**MODEL**

**TopSeller** : Yes

**Announce Date** : 2022-04-29

**EAN / UPC / JAN** : 196379808139

**End of Support** : 2028-10-22



intel

· Lenovo reserves the right to change specifications or other product information without notice.

· Product image on this page is a sample, it may not match the real color of this model

· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 65W Standard AC Adapter (USB Type-C)- US/Can/Mex

4X20M26268

This Lenovo 65W Standard AC Adapter (USB Type-C) Power Adapter offers fast, efficient charging at home, in the office, or on the go. This power adapter is compatible with ThinkPad USB-C enabled Notebook and Tablet.



### Lenovo USB-C 65W AC Adapter (UL)

GX20P92530

Lenovo AC Adapter offers fast and efficient charging. Keep one in the office, one at home, and another in your case for convenient access to power. Just plug it into an available outlet to deliver AC power to the comp...

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference