


SmartRack 1U Cantilever Fixed Rack Shelf - Steel, Vented, 7 in. (17.8 cm) Deep, Holds up to 40 lb. (18 kg)

MODEL NUMBER: SRSHELF2P1USHRT



Vented shelf is 7 in. deep to house a wireless access point or other non-rack device and save space in your server room or network closet.

Features

1U Vented Cantilever Rack Shelf Secures Non-Rack Equipment in Your Data Center

This SmartRack® fixed shelf supports monitors, wireless access points, tower units and other IT equipment not typically stored in a rack. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the SRSHELF2P1USHRT has a maximum load capacity of 40 pounds (18 kilograms). It mounts easily into 1U of space in an EIA-standard 19-inch 2-post or 4-post enclosure or open frame rack using the included hardware.

Maximizes Rack Space and Saves Desk or Floor Space in a Busy Office

The steel shelf is seven inches (17.8 centimeters) deep for organizing network and other non-rack equipment in your small office or server room. The vented surface allows generous airflow to keep your equipment cool and functioning at its peak. You may mount two SRSHELF2P1USHRT shelves back-to-back in your rack to create a deeper shelf in the same 1U rack space.

Highlights

- Cantilever 1U rack shelf secures non-rack equipment like WAPs and monitors
- Heavy-duty cold-rolled steel construction with maximum load capacity of 40 lbs (18 kgs)
- Vented design maximizes airflow to protect equipment against excessive heat
- 2 units can be installed back-to-back to create a deeper shelf in same 1U rack space

Package Includes

- SRSHELF2P1USHRT 1U Fixed Shelf, 7 in. Deep (17.8 cm)
- (4) 12-24 screws
- (4) Cup washers
- Instruction sheet

Specifications

OVERVIEW	
UPC Code	037332263155
Product Type	Accessories / Shelf
Accessory Type	Rack Shelves
Accessory Class	Rack Accessories
PHYSICAL	
Rack Height	1U



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Maximum Weight Capacity (lbs.)	40
Maximum Weight Capacity (kg)	18
Unit Dimensions (hwd / in.)	1.75 x 19 x 7.31
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 18.56
Unit Weight (lbs.)	2.5
Unit Weight (kg)	1.13
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>