

This Thunderbolt 3 docking station must be connected to a Thunderbolt 3-enabled laptop or computer using a Thunderbolt 3 cable to achieve maximum data transfer and video transmission specifications.

Thunderbolt 3 Dock with USB-C Compatibility, Dual Display - 8K DisplayPort, USB 3.2 Gen 2 10G, USB-A/USB-C Hub, GbE, International Plug Adapters

MODEL NUMBER: MTB3-DOCK-03INT



Turns your MacBook Pro or Windows laptop into a 10-port workstation capable of transmitting 8K video.

Features

Thunderbolt 3 Dock Turns Your MacBook Pro into a 10-Port 8K Workstation

This Thunderbolt 3 docking station dramatically expands the potential of your MacBook Pro or Windows laptop by adding 10 ports to its Thunderbolt 3 or USB-C MFD port. Not only does the MTB3-DOCK-03INT allow you to transmit 8K video to one display or 4K video to two displays, you can also add USB peripherals, record a podcast, connect to a Gigabit Ethernet network, charge your laptop and more, all at the same time.

Supports DisplayPort Alternate Mode for Transmitting Audio/Video Signals

By connecting the included Thunderbolt 3 cable to a source device that supports DisplayPort Alt Mode, you can output 4K video and digital audio to a compatible monitor, television or projector without installing special software drivers.

Thunderbolt 3 Supports Blisteringly Fast 40 Gbps Data Transfer Speeds

The included Thunderbolt 3 cable supports bidirectional speeds up to 40 Gbps, which is eight times faster than USB 3.2 Gen 1, four times faster than Thunderbolt 1 and twice as fast as Thunderbolt 2. With dual 20 Gbps channels moving data both directions at the same time, the MTB3-DOCK-03INT is perfectly suited for 4K video streaming and editing on two monitors, as well as transferring large RAW video or CAD files. When connected to a host computer's USB-C MFD port, the cable supports 26.2 Gbps speeds.

DisplayPort Multi-Stream Transport (MST) Allows Connection of Multiple Displays

By connecting the included Thunderbolt 3 cable to a source that supports DisplayPort MST Mode, you may connect two displays simultaneously at resolutions of 8K (30 Hz) plus 4K (30 Hz) or both displays at 4K (60 Hz). This allows you to display the same image on both monitors, extend your host desktop across both with different windows open on each, or combine both into one large display as a video wall.

Transmits Crystal-Clear 8K and 4K Video for Professional Editing and Digital Signage

Both the DisplayPort and Thunderbolt 3 video ports can achieve resolutions up to 8K (7680 x 4320) at 30

Highlights

- Connects 2 displays at the same time for multitasking and increasing productivity
- Transmits 8K video (7680 x 4320) @ 30 Hz to a single display for professional users
- Can operate with Thunderbolt 3 or USB-C Multi-Function DisplayPort (MFD) host
- Supports Thunderbolt 3 speeds up to 40 Gbps between compatible devices
- USB 3.2 Gen 2 data ports allow connection of flash drives and other peripherals

System Requirements

- Source device with Thunderbolt 3 port that supports DisplayPort MST Mode or USB-C port that supports Multi-Function DisplayPort
- Display device with Thunderbolt 3 or DisplayPort input

Package Includes

- MTB3-DOCK-03INT Thunderbolt 3 Dock, Dual Display
- Thunderbolt 3 cable (M/M), 1.6 ft. (0.5 m)
- External power supply (Input: 100–240V, 50/60 Hz, 3.0A; Output: 20V 6A)
- (4) International plug adapters (North America, U.K., Australia, Europe)
- Owner's manual



Hz, when used with a Thunderbolt 3-enabled source computer and Thunderbolt 3 cable. When used with an MFDP-enabled source computer, the DisplayPort connector's maximum resolution is 4K (3840 x 2160) at 60 Hz. The Thunderbolt 3 port also allows daisy-chaining up to six Thunderbolt 3 devices, including RAID memory and other storage devices.

USB Ports Connect Keyboards, Thumb Drives and Other USB Peripherals

Two USB-A hub ports and one USB-C port accept USB peripherals, such as flash drives, mice, keyboards, external hard drives and printers. All three support lightning-fast USB 3.2 Gen 2 data transfer rates up to 10 Gbps and are backward compatible with previous USB generations. The USB-C port supports USB charging up to 5V 1.5A. One USB-A port supports BC 1.2 charging speeds up to 5V 1.5A. The other supports charging up to 5V 900mA.

Accesses a Wired Gigabit Ethernet Network

The RJ45 port offers access to a Gigabit Ethernet network when no Wi-Fi is available or when a wired connection offers faster speeds. Connect using a UTP cable (sold separately), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Connects Stereo Audio Equipment for Recording and Playback

This Thunderbolt 3 docking station contains one 3.5 mm mini stereo jack, convenient for connecting speakers, headphones or a microphone to your workstation. You can listen to music or record the latest episode of your podcast.

Allows External Memory Access

The memory card slots support Micro SD and SD cards for transferring data to and from your connected computer or laptop. Both slots may be used at the same time.

Included Thunderbolt 3 Cable Attaches in Either Direction

Unlike traditional USB cables that connect in only one direction, the reversible Thunderbolt 3 male connector plugs into its port in either direction for an instant connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play Thunderbolt 3 dock requires no extra software to download and install. The included external power supply provides up to 20V 3A (60W) to charge and power the connected source device. It comes with four international plug adapters (North America, United Kingdom, Europe, Australia), so you can connect to a wall outlet, UPS, PDU or surge protector all over the world.

Specifications

OVERVIEW	
UPC Code	037332273024
Product Type	Docking Station
Technology	DisplayPort; Thunderbolt
Host Connector	THUNDERBOLT 3 (Type-C MALE)
VIDEO	
Video Input	THUNDERBOLT 3 (Type-C FEMALE)
Video Output	DISPLAYPORT (FEMALE); THUNDERBOLT 3 (Type-C FEMALE)
Number of Monitors Supported	2
Video Ports	DISPLAYPORT (FEMALE); THUNDERBOLT 3 (Type-C FEMALE)
Video Ports Details	Thunderbolt 3; DisplayPort 1.2a; DisplayPort 1.4



Resolutions Supported	Thunderbolt 3: 8K 30Hz (7680 x 4320) DisplayPort: 8K 30Hz (7680 x 4320)
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 3840x2160 (4K); 5120x2880 (5K); 7680x4320 (8K)
Max Supported Video Resolution	7680 x 4320 (When connected to TB3 Host); 4K 60 Hz (When connected to USB-C MFDP Host)
Extended Mode	Yes
Extended Mode Details	Supports dual 4K/60 Hz extended desktop mode via the DisplayPort and Thunderbolt 3 ports
Mirror Mode	Yes
Mirror Mode Details	For Thunderbolt 3 Source: 1x DP (8K 30Hz) + 1x ThunderBolt 3 (4K 30Hz) via USB-C to C or USB-C to DP or USB-C to HDMI cable or adapter For USB-C MFDP Source: 1x DP (4K 60Hz) + 1x ThunderBolt 3 (4K 60Hz) via USB-C to C or USB-C to DP or USB-C to HDMI cable or adapter
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
Chroma Sub Sampling	4:2:2; 4:4:4
Signal Transmission	Unidirectional
AUDIO	
Audio Ports	3.5MM (FEMALE)
Audio Ports Details	Mini stereo jack supports speakers or headphones
Audio Specification	Supports 8/16/22.05/24/32/44.1/48/96/176.4/192/384 KHz
DATA	
Data Ports	(2) THUNDERBOLT 3 (Type-C FEMALE); (2) USB A (FEMALE); USB C (FEMALE)
Data Ports Details	(2) USB-A - USB 3.2 Gen 2 (10 Gbps); (2) USB-C - ThunderBolt 3 (40 Gbps); (1) USB-C - USB 3.2 Gen 2 (10 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
STORAGE	
Card Slots	SD (FEMALE); MICRO SD (FEMALE)
Card Slots Details	SD 4.0 and Micro SD 4.0Both card readers can be used at the same time
INPUT	
Maximum Input Amps	3
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
BATTERY	
Battery Charging (5V/1.5A Port)	Yes



POWER	
Power Source Type	AC Adapter with detachable power cord
Power Source	Unit (Included)
AC Adapter	Input: 100-240V, 50/60 Hz, 2A; Output: 20V / 6A
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 2A
External Power Supply Output Specs (V / A)	20V/6A
External Power Supply Cord Length (ft.)	3.94
External Power Supply Cord Length (m.)	1.2
DC Barrel Plug	OD: 4.5 x 0.6 x 10.5mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/7 Schuko; NEMA 5-15P North America
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	60W
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	RJ45 Port = Green (x1, Power); Amber (x1, Data)
CHARGING	
Number of Charging Ports	1
Total Charging Amps	6
Total Charging Watts	120
Charging Port Type	(2) USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	Includes two USB 3.2 Gen 2 Type-A ports, both of which support 10 Gbps data transfer speeds. One USB-A port supports USB charging up to 5V 1.5A and the other up to 5V 900mA. Includes one USB 3.2 Gen 2 Type-C port which supports USB charging up to 5V 1.5A
Charging Ports	Supports 60W (20V 3A) Power to Host Computer; USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	0.9A; (2) 1.5A
PHYSICAL	
Color	Black; Gray
Material of Construction	PC, ABS, Aluminum
Unit Dimensions (hwd / in.)	0.69 x 5.83 x 3.15
Unit Dimensions (hwd / cm)	1.75 x 14.8 x 8.0
Unit Dimensions (hwd / mm)	17.5 x 80 x 148
Unit Packaging Type	Box



Unit Weight (lbs.)	3.3731
Unit Weight (kg)	1.53
ENVIRONMENTAL	
Operating Temperature Range	32 to 113F (0 to 45C)
Storage Temperature Range	14 to 158F (-10 to 70C)
Operating Humidity Range	10% to 85% RH
Storage Humidity Range	5% to 90% RH
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
EDID Compatible	No
CONNECTIONS	
Number of Ports	10
RJ45 Ports	1
RJ45 Ports Detail	Supports 10/100/1000 Mbps (Gigabit) Ethernet
Dock Connectors	DISPLAYPORT, THUNDERBOLT 3, USB-C CHARGING, RJ45 LAN, MICRO SD, SD, 3.5MM, 2X USB3.0A, USB-C
Side A - Connector 1	(2) THUNDERBOLT 3 (Type-C FEMALE)
Side A - Connector 2	DISPLAYPORT (FEMALE)
Side A - Connector 3	RJ45 (FEMALE)
Side A - Connector 4	RJ45 (FEMALE)
Side B - Connector 1	(2) USB A (FEMALE)
Side B - Connector 2	USB C (FEMALE)
Side B - Connector 3	3.5MM (FEMALE)
Side B - Connector 4	SD (FEMALE)
Side B - Connector 5	MICRO SD (FEMALE)
Side B - Connector 6	DISPLAYPORT (FEMALE)
Side A - Connector 5	USB A (FEMALE)
FEATURES & SPECIFICATIONS	
Data Transfer Rate	(3) 10 Gbps; (2) 40 Gbps
Displayport Specification	1.4
USB Hub Ports	Yes
Number of USB Hub Ports	3
USB Specification	USB 3.2 Gen 2 (Up to 10 Gbps)
Driver Required	No



Recommended Category Cable	Cat5/Cat5e/Cat6 Cables
Suspend Mode Support	No
Remote Wakeup Support	No
SD Card Specification	Micro SD; SD
Thunderbolt Specification	Thunderbolt 3 (up to 40Gbps short or active cables)
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CCC; CE; GS; TUV; WEEE; cUL
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>