

# RX-series: RX300

## Cloud-Ready Thin Client for Windows®

### Compatibility

- **vSpace Pro:** Refer to the [vSpace OS compatibility matrix](#) for the latest supported versions.
- **Verde VDI & Remote Access**
- **Microsoft RDS**

### RX300 Features

- Full-motion HD video playback (1920 x 1200) via HDMI
- Transparent USB redirection
- Built-in 10/100 Ethernet and WiFi (802.11 b/g/n) with Personal and Enterprise 802.1x security
- Integrated VPN support (OpenVPN, OpenConnect, IPSec, FortiClient and PPTP)
- 16GB internal Micro SD card
- 1GB RAM
- Less than 5W power consumption
- Power button and sleep mode for additional power savings
- *NComputing* vCAST Streaming and UXP Turbo protocol support
- RDP with RemoteFX support for improved session performance
- Kensington security port and VESA mount kit included

### Optional Accessories

- **SDA** - Secondary display adapter (USB to VGA, DVI or HDMI)

The RX300 is a cloud-ready thin client built for productivity on the Raspberry Pi 3 platform, providing a rich PC-like experience featuring full-screen, full-motion HD multimedia playback, WiFi and ethernet connectivity, and built-in transparent USB redirection with broad peripheral support.

The RX300 provides a simple-to-deploy, centrally managed, high performance virtual desktop, perfect for use in SMB and education which can be deployed on **vSpace Pro**, **VERDE VDI & Remote Access**, and **Microsoft RDS** systems.

### vCAST Streaming, UXP Turbo and Microsoft RemoteFX

*NComputing* vCAST Streaming reduces server-side CPU usage for streaming media like YouTube as well as local media content without the need for expensive GPUs.

By utilizing network bandwidth instead of the server CPU, vCAST provides for better media streaming and allows for more concurrent users per server.

The new UXP Turbo protocol for **vSpace Pro** Enterprise delivers an enhanced desktop experience with PC-like performance for 3D rendering, browser scrolling, video playback and multimedia-intensive applications running on Windows 10, 11, or Windows Server 2022.

Enabling the RemoteFX feature in Microsoft RDS and VERDE VDI for Remote Desktop connections greatly enhances the user's visual experience. Host systems equipped with supported graphic cards will benefit.

### Central management & express deployment

**vSpace Console**, the integrated device management solution in **vSpace Pro**, allows for easy configuration and updates. Administrators may define a device template with all settings and configurations, then clone and push it to new devices. All can be centrally managed and provisioned by the IT admin, allowing for control of hundreds of RX300 devices with just a few clicks.

**VERDE VDI & Remote Access** and **Microsoft RDS** can configure the RX300 via optional PMC Device Management software. An admin can remotely manage RX300 devices over local and wide-area networks, including locations behind firewalls and NAT-routers through an easy-to-use, web-based user interface. PMC requires a separate license for Microsoft RDS. **vSpace Pro** and **VERDE VDI & Remote Access** users can use PMC by subscribing to AMP.


### Connection License

RX300 comes with a perpetual software connection license for **vSpace Pro**. Microsoft RDS requires multi-user licenses from Microsoft. VERDE VDI & Remote Access requires separate connection licenses.



Server

Thin Clients





## Device Management

### For vSpace Pro

- vSpace Console is included
- [PMC](#) is available for subscribers to [AMP for vSpace Pro](#)

### For VERDE VDI

- [PMC](#) is available for subscribers to [AMP for VERDE](#).

### For Microsoft RDS

- [PMC](#) requires separate licenses.

## RX300 Connections

1. Power in (5.1V micro USB)
2. HDMI video output
3. Speaker jack: 16bit/44kHz/Stereo high quality audio
4. 10/100 Mbps Ethernet RJ45 port
5. 4 High-Speed USB 2.0 ports with full USB redirection support (2 required for mouse and keyboard)
6. Kensington security port
7. Power on/off and sleep mode button disables display output for power savings

HARDWARE	DESCRIPTION
<b>BOX CONTENTS</b>	Each RX300 includes 1 device, 1 power supply, VESA mount kit and a Quick Installation Guide.
<b>SIZE</b>	Width: 76 mm / 3 inches, Depth: 93 mm / 3.7 inches, Height : 30 mm /1.2 inches
<b>WEIGHT</b>	92g / 0.21 lbs. Shipping weight (includes power adapter, packaging, document): 0.31kg / 0.7 lbs
<b>POWER SUPPLY</b>	5.1VDC (2.5A) power supply included
<b>POWER CONSUMPTION</b>	5W max (independent of external USB devices)
<b>LED INDICATORS</b>	Power, network link, and network activity
<b>DISPLAY</b>	HDMI video output supporting resolutions up to 1920 x 1200 with DDC support. Secondary display via optional SDA (USB to VGA, DVI or HDMI)
<b>SOC</b>	Broadcom BCM2837, 1.2GHz 64bit Quad Core Cortex A53 Dual core VideoCore IV, Multimedia Processor
<b>MEMORY</b>	<ul style="list-style-type: none"> <li>• Mass storage: 16 GB internal Micro SD card</li> <li>• RAM: 1GB</li> </ul>
<b>MONITOR POWER-SAVE</b>	Power on/off and sleep mode button to disable display output for power savings
<b>NETWORK AND CONNECTIVITY</b>	<ul style="list-style-type: none"> <li>• 10/100 Ethernet RJ45 port</li> <li>• Wi-Fi (2.4 GHz 802.11 b/g/n)</li> </ul>
<b>AUDIO</b>	16-bit/44kHz/Stereo high quality digital audio with support for USB2.0 audio devices or via 3.5mm stereo audio jacks for headphone
<b>PERIPHERAL SUPPORT</b>	<ul style="list-style-type: none"> <li>4x USB 2.0 high-speed ports (two required for keyboard &amp; mouse)</li> <li>• All USB ports provide full USB redirection, utilizing device drivers from the server.</li> </ul>
<b>OPERATION MODE</b>	Provisioned by IT admin: <ul style="list-style-type: none"> <li>• Thin Client Mode (<a href="#">vSpace Pro</a>, <a href="#">Microsoft RDP</a>, <a href="#">VERDE VDI &amp; Remote Access</a>)</li> </ul>
<b>EMBEDDED OS</b>	RX300 Linux firmware
<b>HOST MACHINE CONFIG</b>	See recommended hardware configuration guide at <a href="http://www.ncomputing.com/support">www.ncomputing.com/support</a>
<b>WARRANTY</b>	1 year hardware warranty included; Optional extended hardware warranty available
<b>MOUNT OPTIONS</b>	VESA mount compatible (included)

SOFTWARE	DESCRIPTION
<b>OPERATING SYSTEMS</b>	Refer to the <a href="#">vSpace operating system compatibility matrix</a> for the latest supported versions.
<b>USER SOFTWARE</b>	NComputing vSpace Pro and VERDE VDI software; built-in vSpace Console device management features to support RX300 thin clients. Optional PMC Device Management software (separate license required) to remotely manage RX300 devices.
<b>LICENSING</b>	RX300 comes with a perpetual software connection license to vSpace Pro desktop virtualization software. PMC Device Management software for remote device management is optional.
<b>VCAST STREAMING</b>	RX300 supports vCAST Streaming for web and media content. vCAST is included in vSpace Pro and VERDE VDI. vCAST on Microsoft RDS requires a license for the NComputing SuperRDP server pack.
<b>DUAL SCREEN DISPLAY</b>	Requires optional NComputing SDA
<b>SUPPORTED PLATFORMS</b>	vSpace Pro (UXP), VERDE VDI (RDP), VERDE Remote Access, (UXP, RDP), Microsoft RDS (RDP)

RX-series products are RoHS compliant and have been EMI certified according to FCC, CE, BIS and KC standards.



**Need more info?**  
We'd love to talk to you about your project. [Click here.](#)