

DATA SHEET

FortiAP™ Series

Available in



Appliance

FortiAP Cloud or FortiOS-managed Access Points



FortiAP(TM) access points are managed centrally by the integrated WLAN controller of any FortiGate® security appliance or through the FortiLAN Cloud provisioning and management portal. With the integration of the wireless controller functionality into the market-leading FortiGate appliance, these APs are perfect for campus and branch deployments. Fortinet’s Security Fabric enables you to easily manage wired and wireless security from a Single-pane-of-glass management console and protects your network from the latest security threats.



Unified management console simplifies operations, ensuring consistency in effective policy enforcement and compliance.



Wireless LAN security done right, from the leader in network security. Integrated Firewall, IPS, Application Control, and Web Filter protect the wireless LAN from the latest security threats.



Protects the network from advanced wireless threats and satisfies PCI DSS compliance.

Product Offerings

802.11ax Wi-Fi 6

FAP-831F 8×8 Indoor tri-radio 11ax AP

FAP-431F
FAP-433F 4×4 Indoor tri-radio 11ax APs

FAP-432F 4×4 Ruggedized indoor/outdoor tri-radio 11ax AP, external antennas

FAP-231F 2×2 Indoor tri-radio 11ax AP, internal antennas

FAP-234F 2×2 Ruggedized indoor/outdoor tri-radio 11ax AP, internal antennas

FAP-23JF 2×2 Wall-mount tri-radio AP, internal antennas


802.11ac (Wave 2) Wi-Fi 5

FAP-221E
FAP-223E 2×2 Indoor dual-radio APs


FAP-C24JE 2×2 Wall-mount dual-radio AP, internal antennas

DEPLOYMENT


FortiAPs allow for a versatile collection of installation topologies with options to fit any enterprise.




Central pair of FortiGates managing a large site




Distributed FortiGates throughout a large campus



Distributed branches via SD-Branch



Centralized FortiGates managing remote teleworkers



FortiLAN Cloud managing standalone FortiAPs



HIGHLIGHTS

FortiAP 831F

This high throughput enterprise class 802.11ax indoor AP provides three radios and 8 spatial streams. This top-of-the line access point supports OFDMA, a 5.0 Gigabit Ethernet port, plus an additional 1 Gbps Ethernet port for PoE diversity. The AP can provide 24/7 scanning across both bands while still providing access on both the 2.4 GHz and 5 GHz bands. The integrated BLE radio can be used for beacons and locationing applications.



 **802.11ax | Tri-Radio 2.4 GHz + 5 GHz + scanning | 13 Internal Antennas**

 **8x8 MU-MIMO | Up to 1,147 Mbps + 4,804 Mbps**

SPECIFICATIONS

FORTIAP 831F	
Hardware	
Hardware Type	Indoor AP
Number of Radios	3 + 1 BLE
Number of Antennas	4 2.4GHz band WiFi + 8 5GHz band WiFi + 1 Dual band Scanning + 1 2.4GHz band BLE
Antenna Type and Peak Gain	PIFA: 4.0 dBi for 2.4 GHz band WiFi antennas 6.0 dBi for 5.0 GHz band WiFi antennas 4.0 dBi for dual band Scanning radio antenna 4.5 dBi for 2.4 GHz band BLE antenna
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850
Radio 1 Capabilities	Frequency Band: 2.4 GHz Channel width: 20/40 MHz Modulation: BPSK, QPSK, QAM64 MIMO chains: 4x4 service
Radio 2 Capabilities	Frequency Band: 5.0 GHz Channel width: 20/40/80/80+80/160MHz Modulation: BPSK, QPSK, QAM64, QAM256, and QAM1024 Mimo chains: 8x8 service in mode 1 or 4x4+4x4 service in mode 2
Radio 3 Capabilities	Frequency band: 2.4/5.0 GHz MIMO chains: 1x1 frequency scanning
Maximum Data Rate	Radio 1: up to 1147.5 Mbps Radio 2: up to 4.804 Gbps in 8x8 MIMO and in 4x4 + 4x4 MIMO modes
Bluetooth Low Energy Radio	Bluetooth scanning and iBeacon advertisement @ 10 dBm max TX power
Interfaces	1x 100/1000/2500/5000 Base-T RJ45 1x 10/100/1000 Base-T RJ45 1x Type 3.0 USB, 1x RS-232 RJ45 Serial Port
Power over Ethernet (PoE)	• 2x 802.3at/bt/30W Passive PoE in (Full function) • 1x 802.3at PoE in (USB3.1 disabled)
Simultaneous SSIDs	Up to 24
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, EAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST
User/Device Authentication	WPA™, WPA2™, and WPA3™ with 802.1x or Preshared key, WEP, Web Captive Portal, MAC blacklist & whitelist
Maximum Tx Power (Conducted)	Radio 1: 2.4 GHz 27 dBm / 500 mW (4 chains combined)* Radio 2: 5 GHz 25.5 dBm / 354 mW (4 chains combined)* Radio 3: NA
Kensington Lock	Yes
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11v, 802.11ac, 802.11ax (Wi-Fi 6), 802.1Q, 802.1X, 802.3ad, 802.3af, 802.3at, 802.3az, 802.3bz
SSID Types Supported	Local-Bridge, Mesh, Tunnel
Per Radio Client Capacity	up to 512 clients per radio (Radio1 and Radio2)
Cellular Co-existence	Yes
LED Off Mode	Yes
Advanced 802.11 Features	
OFDMA	Yes (UL and DL)

FORTIAP-831F	
Spatial Reuse (BSS Coloring)	Yes
UL-MU-MIMO 802.11ax mode	Yes
DL-MU-MIMO	Yes
Enhanced Target Wake Time (TWT)	Yes
ZeroWait DFS /Agile DFS	No
Wireless Monitoring Capabilities	
Rogue Scan Radio Mode	Dedicated
WIPS / WIDS RAdio Modes	Dedicated
Packet Sniffer Mode	Yes
Spectrum Analyzer	Yes
Dimensions	
Length x Width x Height	9.05 × 89.05 × 2.15 inches (230 × 230 × 55 mm)
Weight	2.25 lbs (1.02 kg)
Package (shipping) Weight	4.2 lbs (1.9 kg)
Mounting Options	Ceiling, T-Rail, and Wall
Included Accessories	Mount kit for Ceiling, T-Rail, and Wall
Environment	
Power Supply	SP-FAP400-PA-XX or GPI-130
PSE Functionality	No
Power Consumption (Max)	33 W
PoE Mode	
Single 5G	DC/2at → Full Mode ; Radios will be in (8x8 4x4) & USB Enabled 1at/2af → High Mode ; Radios will be in (8x8 4x4) & USB Disabled 1af → Low Mode ; Radios will be [2x2 2x2], Tx Power 10 dBm & USB Disabled
Dual 5G	DC/2at → Full Mode ; Radios will be in [4x4 4x4 4x4] & USB Enabled 1at/2af → High Mode ; Radios will be in [4x4 4x4 4x4] & USB Disabled 1af → Low Mode ; Radios will be [2x2 2x2 2x2], Tx Power 10 dBm & USB Disabled
Humidity	5–90% Non-Condensing
Operating / Storage Temp.	32–122°F (0–50°C) / -22–158°F (-30–70°C)
Directives	Low Voltage Directive • RoHS
UL2043 Plenum Material	No
Mean Time Betw. Failures	>10 Years
Surge Protection Built In	Yes
Certifications	
Wi-Fi Alliance Certified	Yes
DFS	FCC, IC, CE, Brazil and Taiwan
Warranty	
Limited Lifetime Warranty	Yes




RF RX/TX PERFORMANCE TABLE


FORTIAP 831F								
802.11b	Radio 1		Radio 2		Radio 3			
	2.4 GHz Tx Power per chain (dBm)	Rz Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)	2.4 GHz Tx Power per chain (dBm)	Rz Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)
1 Mbps	21	-98	—	—	21	-96	—	—
11 Mbps	23	-89	—	—	18	-87	—	—
802.11g								
6 Mbps	20	-94	—	—	20	-92	—	—
54 Mbps	22	-75	—	—	18	-73	—	—
802.11n HT20								
MCS0	20	-93	—	—	20	-91	—	—
MCS7	20	-74	—	—	17	-72	—	—
802.11n HT40								
MCS0	17	-92	—	—	19	-90	—	—
MCS7	18	-73	—	—	17	-71	—	—
802.11ax HE20								
MCS0	21	-90	—	—	—	—	—	—
MCS11	17	-71	—	—	—	—	—	—
802.11ax HE40								
MCS0	17	-88	—	—	—	—	—	—
MCS11	17	-68	—	—	—	—	—	—
802.11a								
6 Mbps	—	—	20	-92	—	—	20	-90
54 Mbps	—	—	20	-72	—	—	17.5	-72
802.11n HT20								
MCS0	—	—	20	-91	—	—	20	-90
MCS7	—	—	19	-72	—	—	17.5	-71
802.11n HT40								
MCS0	—	—	20	-88	—	—	19	-88
MCS7	—	—	18	-69	—	—	16.5	-69
802.11ac VHT20								
MCS0	—	—	20	-91	—	—	19	-90
MCS9	—	—	19	-67	—	—	17.5	-67
802.11ac VHT40								
MCS0	—	—	20	-88	—	—	19	-88
MCS9	—	—	18	-62	—	—	16	-62
802.11ac VHT80								
MCS0	—	—	18	-85	—	—	18	-85
MCS9	—	—	17	-59	—	—	16	-58
802.11ax HE20								
MCS0	—	—	20	-90	—	—	—	—
MCS11	—	—	18	-66	—	—	—	—
802.11ac HE40								
MCS0	—	—	20	-87	—	—	—	—
MCS11	—	—	18	-61	—	—	—	—
802.11ac HE80								
MCS0	—	—	18	-94	—	—	—	—
MCS11	—	—	17	-58	—	—	—	—




FAP 831F ANTENNA RADIATION PATTERNS




Radio1 2.4 GHz Horizontal




Radio1 2.4 GHz Vertical




Radio2 5.0 GHz Horizontal




Radio2 5.0 GHz Vertical




Scanning Radio Horizontal



Scanning Radio Vertical



BLE Radio Horizontal



BLE Radio Vertical




HIGHLIGHTS

FortiAP 431F and 433F

These enterprise class 802.11ax indoor APs provide three radios. These top-of-the-line access points provide OFDMA, a 2.5 Gigabit Ethernet port, plus an additional 1 Gbps Ethernet port for PoE diversity. The APs can provide 24/7 scanning across both bands while still providing access on both the 2.4 GHz and 5 GHz bands. The integrated BLE radio can be used for beacons and locationing applications.



 **802.11ax | Tri-Radio 2.4 GHz + 5 GHz + scanning | 5 Internal/External Antennas**

 **4x4 MU-MIMO | Up to 1,147 Mbps + 2,402 Mbps**

SPECIFICATIONS

	FORTIAP 431F	FORTIAP 433F
Hardware		
Hardware Type	Indoor AP	Indoor AP
Number of Radios	3 + 1 BLE	3 + 1 BLE
Number of Antennas	5 Internal + 1 BLE Internal	5 External (RP-SMA) + 1 BLE Internal
Antenna Type and Peak Gain	PIFA: 4 dBi for 2.4 GHz, 5 dBi for 5 GHz	Omni directional rubber duck antenna: 4 dBi for 2.4 GHz, 6 dBi for 5 GHz
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850	
Radio 1 Capabilities	Frequency Band: 2.4 GHz Channel width: 4x4 20/40 MHz Modulation: BPSK, QPSK, QAM64, QAM256, and QAM1024 MIMO chains: 4x4 service	
Radio 2 Capabilities	Frequency Band: 5.0 GHz Channel width: 4x4 20/40/80MHz and 2x2 160MHz contiguous Modulation: BPSK, QPSK, QAM64, QAM256, and QAM1024 Mimo chains: 4x4 service	
Radio 3 Capabilities	Frequency band: 2.4/5.0 GHz MIMO chains: 1x1 frequency scanning	
Maximum Data Rate	Radio 1: up to 1147 Mbps Radio 2: up to 2402 Mbps Radio 3: scan only	Radio 1: up to 1147 Mbps Radio 2: up to 2402 Mbps Radio 3: scan only
Bluetooth Low Energy Radio	Bluetooth scanning and iBeacon advertisement @ 6 dBm max TX power	
Interfaces	1x 100/1000/2500 Base-T RJ45, 1 x 10/100/1000 Base-T RJ45, 1x Type A USB, 1x RS-232 RJ45 Serial Port	
Power over Ethernet (PoE)	<ul style="list-style-type: none"> • 802.3at PoE default • 1 port powered by 802.3at or 2 ports powered by 802.3af - Full System functionality + USB support • 1 port is connected to 802.3af - No USB support, Operate in 2x2 mode with reduced power R1/R2 17dBm(Tx power) 	
Simultaneous SSIDs	Up to 16 (14 if background scanning enabled)	
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, PEAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST	
User/Device Authentication	WPA™, WPA2™, and WPA3™ with 802.1x or Preshared key, WEP, Web Captive Portal, MAC blacklist and allowlist	
Maximum Tx Power (Conducted)	Radio 1: 2.4 GHz 24 dBm / 251 mW (4 chains combined)* Radio 2: 5 GHz 23 dBm / 200 mW (4 chains combined)* Radio 3: NA	
Kensington Lock	Yes	Yes
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11v, 802.11w, 802.11ac, 802.11ax (Wi-Fi 6), 802.11q, 802.11x, 802.3ad, 802.3af, 802.3at, 802.3az, 802.3bz	
SSID Types Supported	Local-Bridge, Mesh, Tunnel	Local-Bridge, Mesh, Tunnel
Per Radio Client Capacity	512 per Radio1 and Radio2	512 per Radio1 and Radio2
Cellular Co-existence	Yes	Yes
Reset Button	Yes	Yes
LED Off Mode	Yes	Yes
Advanced 802.11 Features		
OFDMA	Yes (UL and DL)	Yes (UL and DL)

	FORTIAP-431F	FORTIAP-433F
2.4 GHz OFDMA	Yes	Yes
Spatial Reuse (BSS Coloring)	Yes	Yes
HE-MU-MIMO	Yes	Yes
UL-MU-MIMO 802.11ax mode	Yes	Yes
DL-MU-MIMO	Yes	Yes
Enhanced Target Wake Time (TWT)	Yes	Yes
ZeroWait DFS /Agile DFS	No	No
Wireless Monitoring Capabilities		
Rogue Scan Radio Mode	Background, Dedicated	Background, Dedicated
WIPS / WIDS Radio Modes	Background, Dedicated (recommended)	
Packet Sniffer Mode	Yes	Yes
Spectrum Analyzer	Yes	Yes
Dimensions		
Length x Width x Height	8.27 × 8.27 × 2.22 inches (210 × 210 × 56.5 mm)	
Weight	2.16 lbs (0.98 kg)	2.19 lbs (0.995 kg)
Package (shipping) Weight	3.97 lbs (1.8 kg)	4.4 lbs (2 kg)
Mounting Options	Ceiling, T-Rail, and Wall	Ceiling, T-Rail, and Wall
Included Accessories	Mount kit for Ceiling, T-Rail and Wall	Mount kit for Ceiling, T-Rail and Wall. 5 RP-SMA Male dual-band dipole antenna
Environment		
Power Supply	SP-FAP400-PA-XX or GPI-130	SP-FAP400-PA-XX or GPI-130
Power Consumption (Max)	24.5 W	24.5 W
Humidity	5–90% Non-Condensing	5–90% Non-Condensing
Operating / Storage Temperature	32–113°F (0–45°C) / -31–94°F (-35–70°C)	
Directives	Low Voltage Directive • RoHS	Low Voltage Directive • RoHS
UL2043 Plenum Material	No	No
Mean Time Between Failures	>10 Years	>10 Years
IP Rating	—	—
Surge Protection Built In	Yes	Yes
Hit-less PoE Failover	Yes	Yes
Certifications		
Wi-Fi Alliance Certified	Yes	Yes
DFS	FCC, IC, CE, Japan, Brazil and Taiwan	FCC, IC, CE, Japan, Brazil and Taiwan
Warranty		
Limited Lifetime Warranty	Yes	Yes

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.



RF RX/TX PERFORMANCE TABLE

FORTIAP 431F / 433F								
	Radio 1		Radio 2		Radio 3			
	2.4 GHz Tx Power per chain (dBm)	Rx Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rx Sensitivity (dBm)	2.4 GHz Tx Power per chain (dBm)	Rx Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rx Sensitivity (dBm)
802.11b								
1 Mbps	23	-98	—	—	20	-96	—	—
11 Mbps	23	-89	—	—	18	-87	—	—
802.11g								
6 Mbps	23	-94	—	—	20	-92	—	—
54 Mbps	22	-75	—	—	18	-73	—	—
802.11n HT20								
MCS0	22	-93	—	—	20	-91	—	—
MCS7	20	-74	—	—	17	-72	—	—
802.11n HT40								
MCS0	20	-92	—	—	19	-90	—	—
MCS7	18	-73	—	—	17	-71	—	—
802.11ax HE20								
MCS0	22	-90	—	—	—	—	—	—
MCS11	17	-71	—	—	—	—	—	—
802.11ax HE40								
MCS0	19	-88	—	—	—	—	—	—
MCS11	17	-68	—	—	—	—	—	—
802.11a								
6 Mbps	—	—	20	-92	—	—	20	-90
54 Mbps	—	—	20	-72	—	—	17.5	—
802.11n HT20								
MCS0	—	—	20	-91	—	—	20	-90
MCS7	—	—	19	-72	—	—	17.5	-71
802.11n HT40								
MCS0	—	—	20	-88	—	—	19	-88
MCS7	—	—	18	-69	—	—	16.5	-69
802.11ac VHT20								
MCS0	—	—	20	-91	—	—	19	-90
MCS9	—	—	19	-67	—	—	17.5	-67
802.11ac VHT40								
MCS0	—	—	20	-88	—	—	19	-88
MCS9	—	—	18	-62	—	—	16	-62
802.11ac VHT80								
MCS0	—	—	18	-85	—	—	18	-85
MCS9	—	—	17	-59	—	—	16	-58
802.11ax HE20								
MCS0	—	—	20	-90	—	—	—	—
MCS11	—	—	18	-66	—	—	—	—
802.11ac HE40								
MCS0	—	—	20	-87	—	—	—	—
MCS11	—	—	18	-61	—	—	—	—
802.11ac HE80								
MCS0	—	—	18	-94	—	—	—	—
MCS11	—	—	17	-58	—	—	—	—




ANTENNA RADIATION PATTERNS


FAP-431F




H-Plane Pattern




E-Plane Pattern




FAP-433F



H-Plane Pattern



E-Plane Pattern



HIGHLIGHTS

FortiAP 432F

This enterprise class 802.11ax ruggedized indoor/outdoor AP provides three radios. As a top-of-the-line Wi-Fi 6 access point it provides OFDMA, a 2.5 Gigabit Ethernet port, plus an additional 1 Gbps Ethernet port with PoE out. The AP can provide 24/7 scanning across both bands while still providing access on both the 2.4 GHz and 5 GHz bands. The integrated BLE radio can be used for beacons and locationing applications.



 **802.11ax | Tri-Radio 2.4 GHz + 5 GHz + scanning | 6 External Antennas**

 **4x4 MU-MIMO | Up to 1,147 Mbps + 2,402 Mbps**

SPECIFICATIONS

FORTIAP 432F	
Hardware	
Hardware Type	Ruggedized indoor/outdoor AP
Number of Radios	3 + 1 BLE
Number of Antennas	4 dual band WiFi + 1 dual band scanning + 1 single band 2.4 GHz BLE/ZigBee
Antenna Type and Peak Gain	WiFi and scanning radio dual band antenna: 5.5 dBi in 2.4 GHz and 7.2 dBi in 5 GHz band BLE antenna: 5.0 dBi in 2.4 GHz band
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850
Radio 1 Capabilities	Frequency band: 2.4 GHz Channel width: 20/40MHz Modulation: BPSK, QPSK, 64/256/1024 QAM MIMO Chains: 4x4 Service
Radio 2 Capabilities	Frequency band: 5.0 GHz Channel width: 4x4 20/40/80MHz and 2x2 160 MHz contiguous Modulation: BPSK, QPSK, QAM64, QAM256, and QAM1024 MIMO Chains: 4x4 Service
Radio 3 Capabilities	Frequency bands: 2.4 GHz and 5.0 GHz MIMO Chains: 1x1 Frequency Scanning
Maximum Data Rate	Radio 1: up to 1147 Mbps Radio 2: up to 2402 Mbps Radio 3: Frequency scanning only
Bluetooth Low Energy Radio	Bluetooth scanning and iBeacon advertisement @ 10 dBm max TX power
Interfaces	1x 100/1000/2500 Base-T RJ45, 1x 10/100/1000 Base-T RJ45 (802.3af PoE PSE), 1x RS-232 RJ45 Serial Port
Power over Ethernet (PoE)	<ul style="list-style-type: none"> 802.3bt PoE default (ships with Passive PoE injector) Powered by 802.3at PoE - Operate in 4x4 mode with reduced Tx power Radio1/R2 17dBm This product only supports PSE functionality when it is powered by PoE injector that ships with the product.
Simultaneous SSIDs	Up to 16 (14 if background scanning enabled)
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, PEAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST
User/Device Authentication	WPA™, WPA2™, and WPA3™ with 802.1x or preshared key, WEP, Web Captive Portal, MAC blacklist & allowlist
Maximum Tx Power (Conducted)	Radio 1: 2.4 GHz 30 dBm / 1000 mW (4 chains combined)* Radio 2: 5 GHz 26 dBm / 398 mW (4 chains combined)* Radio 3: N/A
Kensington Lock	Yes
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11v, 802.11w, 802.11ac, 802.11ax (Wi-Fi 6), 802.1Q, 802.1X, 802.3ad, 802.3af, 802.3at, 802.3az, 802.3bt, 802.3bz
SSIDs Supported	Local-Bridge, Tunnel, and Mesh
Per Radio Client Capacity	Up to 512 clients per radio (Radio1 and Radio2)
Cellular Co-existence*	Yes
LED Off Mode	Yes

FORTIAP 432F	
Advanced 802.11 Features	
OFDMA	Yes (UL and DL)
Spatial Reuse (BSS Coloring)	Yes
UL MU-MIMO	Yes
DL-MU-MIMO	Yes
Enhanced Target Wake Time (TWT)	Yes
ZeroWait DFS	No
Wireless Monitoring Capabilities	
Rogue Scan radio modes	Background, Dedicated
WIPS / WIDS radio modes	Background, Dedicated (recommended)
Packet Sniffer Mode	Yes
Spectrum Analyzer	Yes
Dimensions	
Length x Width x Height	8.23 x 8.23 x 2.38 inches (209 x 209 x 60.5 mm)
Weight	5.12 lbs (2.325 kg)
Package (shipping) Weight	12.56.93 lbs (5.7 kg)
Mounting Options	Wall and Pole
Included Accessories	Wall and Pole mounting kit
Environment	
Power Supply	802.3bt PoE, ships with PoE injector (reset functionality)
PSE functionality	Yes (while powered by PoE injector shipped with product)
Power Consumption (Maximum)	25 W without PSE out and 37.9 W with PSE out
Humidity	10 - 90% non condensing
Operating / Storage Temperature	-40–140°F (-40 - 60°C) / -40–176°F (-40–80°C)
Directives	Low Voltage Directive • RoHS
UL2043 Plenum Material	No
Mean Time Between Failures	> 10 Years
IP Rating	IP67
Surge Protection Built In	Yes
Hit-less PoE Failover	N/A
Certifications	
WiFi Alliance Certified	Yes
DFS	FCC, IC, CE, Japan, Brazil and Taiwan
Warranty	
Limited Lifetime Warranty	Yes

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.




RF RX/TX PERFORMANCE TABLE

FORTIAP 432F							
	Radio 1		Radio 2		Radio 3 Scanning		
	2.4 GHz Tx Power per chain (dBm)	Rz Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)	2.4 GHz Tx Power per chain (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)
802.11b							
1 Mbps	24	-99	—	—	20	—	-92
11 Mbps	24	-91	—	—	18	—	-91
802.11g							
6 Mbps	24	-94	—	—	20	—	-92
54 Mbps	23	-78	—	—	18	—	-77
802.11n HT20							
MCS0	24	-94	—	—	20	—	-92
MCS7	23	-75	—	—	17	—	-74
802.11n HT40							
MCS0	23	-92	—	—	19	—	-90
MCS7	22	-73	—	—	17	—	-72
802.11ax HE20							
MCS0	23	-90	—	—	—	—	—
MCS11	21	-71	—	—	—	—	—
802.11ax HE40							
MCS0	21	-91	—	—	—	—	—
MCS11	19	-72	—	—	—	—	—
802.11a							
6 Mbps	—	—	22	-92	—	20	-93
54 Mbps	—	—	22	-76	—	19	-76
802.11n HT20							
MCS0	—	—	22	-93	—	20	-93
MCS7	—	—	21	-74	—	19	-73
802.11n HT40							
MCS0	—	—	22	-91	—	19	-90
MCS7	—	—	21	-72	—	18	-71
802.11ac VHT20							
MCS0	—	—	22	-91	—	19	-93
MCS9	—	—	20	-72	—	18	-69
802.11ac VHT40							
MCS0	—	—	22	-91	—	19	-90
MCS9	—	—	19	-72	—	16	-64
802.11ac VHT80							
MCS0	—	—	20	-86	—	17	-88
MCS9	—	—	17	-62	—	17	-61
802.11ax HE20							
MCS0	—	—	22	-91	—	—	—
MCS11	—	—	19	-72	—	—	—
802.11ac HE40							
MCS0	—	—	22	-91	—	—	—
MCS11	—	—	19	-72	—	—	—
802.11ac HE80							
MCS0	—	—	20	-87	—	—	—
MCS11	—	—	18	-58	—	—	—




ANTENNA RADIATION PATTERNS








FAP-432F



H-Plane Pattern



E-Plane Pattern




HIGHLIGHTS

FortiAP 231F

This enterprise class Wi-Fi 6 indoor AP provides three radios as well as features such as OFDMA and dual 1 Gbps Ethernet ports. The AP can provide 24/7 scanning across both bands while still providing access on both the 2.4 GHz and 5 GHz bands. The integrated BLE radio can be used for beacons and locationing applications.



 **802.11ax | Tri-Radio 5 GHz + 2.4 GHz + scanning | 3 Antennas**

 **2x2 MU-MIMO | Up to 574 Mbps + 1,201 Mbps + scanning**

SPECIFICATIONS

FORTIAP 231F	
Hardware	
Hardware Type	Indoor AP
Number of Radios	3 + 1 BLE
Number of Antennas	3 Dual band Internal Wi-Fi + 1 BLE/ZigBee
Antenna Type and Peak Gain	PIFA antenna Dual band: 4.5dBi for 2.4GHz and 5.5dBi for 5GHz BLE antenna 4.0dBi at 2.4GHz band
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850
Radio 1 Capabilities	Frequency band: 2.4GHz Channel width: 20/40MHz Modulation: BPSK, QPSK, 64/256/1024 QAM MIMO Chains: 2x2 Service
Radio 2 Capabilities	Frequency band: 5.0GHz Channel width: 20/40/80MHz Modulation: BPSK, QPSK, 64/256/1024 QAM MIMO Chains: 2x2 Service
Radio 3 Capabilities	Frequency bands: 2.4GHz and 5.0GHz MIMO Chains: 1x1 Frequency Scanning
Maximum Data Rate	Radio 1: up to 574 Mbps Radio 2: up to 1201 Mbps Radio 3: Frequency scanning only
Bluetooth Low Energy Radio	Bluetooth scanning and iBeacon advertisement @ 10 dBm max TX power
Interfaces	2x 10/100/1000 Base-T RJ45, 1x Type 2.0 USB, 1x RS-232 RJ45 Serial Port
Power over Ethernet (PoE)	• 802.3at PoE default • 1 port powered by 802.3at - full system functionality + USB support • 1 port is connected to 802.3af - no USB support
Simultaneous SSIDs	Up to 16 (14 if background scanning enabled)
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, PEAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST
User/Device Authentication	WPA™, WPA2™, and WPA3™ with 802.1x or Preshared key, WEP, Web Captive Portal, MAC blacklist & allowlist
Maximum Tx Power (Conducted)	Radio 1: 2.4GHz: 23 dBm / 200 mW (2 chains combined)* Radio 2: 5GHz: 22 dBm / 158 mW (2 chains combined)* Radio 3: NA
Kensington Lock	Yes
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11v, 802.11w, 802.11ac, 802.11ax, 802.1Q, 802.1X, 802.3ad, 802.3af, 802.3at, 802.3az
SSID Types Supported	Local-Bridge, Tunnel, and Mesh
Per Radio Client Capacity	Up to 512 clients per radio (Radio1 and Radio2)
Cellular Co-existence*	Yes
Reset Button	Yes

FORTIAP 231F	
LED Off Mode	Yes
Advanced 802.11 Features	
OFDMA	Yes (UL and DL)
Spatial Reuse (BSS Coloring)	Yes
UL MU-MIMO 802.11ax mode	Yes
DL-MU-MIMO	Yes
Enhanced Target Wake Time (TWT)	Yes
ZeroWait DFS/Agile DFS	No
Wireless Monitoring Capabilities	
Rogue Scan radio modes	Background, Dedicated
WIPS / WIDS radio modes	Background, Dedicated (recommended)
Packet Sniffer Mode	Yes
Spectrum Analyzer	Yes
Dimensions	
Length x Width x Height	6.0 x 6.0 x 2.86 inches (153.2 x 153.2 x 53.0 mm)
Weight	1.0 lbs (0.543 kg)
Package (shipping) Weight	2.1lbs (0.95 kg)
Mounting Options	Ceiling, T-Rail, and Wall
Included Accessories	Standard Mount kit for Ceiling, T-Rail, and Wall
Environment	
Power Supply	802.3at PoE GPI-130
Power Consumption (Maximum)	17W
Humidity	5 - 90% non condensing
Operating / Storage Temperature	32–122°F (0 - 50°C) / -22–158°F (-30–70°C)
Directives	Low Voltage Directive • RoHS
UL2043 Plenum Material	No
Mean Time Between Failures	> 10 Years
IP Rating	N/A
Surge Protection Built In	Yes
Hit-less PoE Failover	N/A
Certifications	
WiFi Alliance Certified	Yes
DFS	FCC, IC, CE, Japan, Brazil, Taiwan and Korea
Warranty	
Limited Lifetime Warranty	Yes

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.



RF RX/TX PERFORMANCE TABLE

FORTIAP 231F				
	Radio 1		Radio 2	
	2.4 GHz Tx Power per chain (dBm)	Rx Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rx Sensitivity (dBm)
802.11b				
1 Mbps	21	-99	—	—
11 Mbps	21	-90	—	—
802.11g				
6 Mbps	20	-94	—	—
54 Mbps	20	-77	—	—
802.11n HT20				
MCS0	19	-94	—	—
MCS7	18	-76	—	—
802.11n HT40				
MCS0	19	-92	—	—
MCS7	19	-73	—	—
802.11ax HE20				
MCS0	19	-94	—	—
MCS11	17	-65	—	—
802.11ax HE40				
MCS0	19	-91	—	—
MCS11	16	-63	—	—
802.11a				
6 Mbps	—	—	22	-94
54 Mbps	—	—	21	-77
802.11n HT20				
MCS0	—	—	21	-94
MCS7	—	—	19	-76
802.11n HT40				
MCS0	—	—	21	-91
MCS7	—	—	19	-73
802.11ac VHT20				
MCS0	—	—	21	-94
MCS9	—	—	18	-72
802.11ac VHT40				
MCS0	—	—	21	-91
MCS9	—	—	18	-68
802.11ac VHT80				
MCS0	—	—	19	-88
MCS9	—	—	17	-64
802.11ax HE20				
MCS0	—	—	21	-94
MCS11	—	—	17	-64
802.11ac HE40				
MCS0	—	—	21	-91
MCS11	—	—	17	-62
802.11ac HE80				
MCS0	—	—	19	-88
MCS11	—	—	16	-58




ANTENNA RADIATION PATTERNS


FAP-231F



H-Plane Pattern



E-Plane Pattern



HIGHLIGHTS

FortiAP 234F

This enterprise class Wi-Fi 6 ruggedized indoor/outdoor AP provides three radios with internal antennas as well as features such as OFDMA and dual 1 Gbps Ethernet ports. The AP can provide 24/7 scanning across both bands while still providing access on both the 2.4 GHz and 5 GHz bands. The integrated BLE radio can be used for beacons and locationing applications.



802.11ax | Tri-Radio 5 GHz + 2.4 GHz + scanning | 2 5G antenna + 2 2.4G antenna + 1 dual band antenna + 1 single band 2.4 Ghz BLE/ZigBee



2x2 MU-MIMO | Up to 574 Mbps + 1,201 Mbps + scanning

SPECIFICATIONS

FORTIAP 234F	
Hardware	
Hardware Type	Ruggedized indoor/outdoor AP
Number of Radios	3 + 1 BLE
Number of Antennas	2 dual band WiFi + 1 dual band scanning + 1 single band 2.4 GHz BLE/ZigBee
Antenna Type and Peak Gain	Directional patch antenna Single band antennas: 10 dBi in 2.4 GHz band, 10 dBi in 5.0 GHz band Scanning radio: 3.5 dBi in 2.4 GHz band and 4.5 dBi in 5 GHz band BLE antenna: 3.5 dBi in 2.4 GHz band
Antenna Beam Width	2.4GHz Horizontal BW 70 degree Vertical BW 30 degree 5.0GHz Horizontal BW 78 degree Vertical BW 25 degree
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850
Radio 1 Capabilities	Frequency band: 2.4GHz Channel width: 20/40MHz Modulation: BPSK, QPSK, 64/256/1024 QAM MIMO Chains: 2x2 Service
Radio 2 Capabilities	Frequency band: 5.0GHz Channel width: 20/40/80MHz Modulation: BPSK, QPSK, 64/256/1024 QAM MIMO Chains: 2x2 Service
Radio 3 Capabilities	Frequency bands: 2.4 GHz and 5.0 GHz MIMO Chains: 1x1 Frequency Scanning
Maximum Data Rate	Radio 1: up to 574 Mbps Radio 2: up to 1200 Mbps Radio 3: Frequency scanning only
Bluetooth Low Energy Radio	Bluetooth scanning and iBeacon advertisement @ 10 dBm max TX power
Interfaces	2x 10/100/1000 Base-T RJ45, 1x RS-232 RJ45 Serial Port
Power over Ethernet (PoE)	<ul style="list-style-type: none"> 802.3at PoE default (Ships with Passive PoE injector) 1 port powered by 802.3at or 2 ports powered by 802.3af - Full System functionality 1 port is connected to 802.3af - No USB support, Operate in 2x2 mode with reduced Tx power R1/R2 17dBm
Simultaneous SSIDs	Up to 16 (14 if background scanning enabled)
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, PEAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST
User/Device Authentication	WPA™, WPA2™, and WPA3™ with 802.1x or Preshared key, WEP, Web Captive Portal, MAC blocklist & allowlist
Maximum Tx Power (Conducted)	Radio 1: 2.4 GHz: 27 dBm / 500 mW (2 chains combined)* Radio 2: 5 GHz: 25.5 dBm / 354 mW (2 chains combined)* Radio 3: N/A
Kensington Lock	Yes
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11v, 802.11w, 802.11ac, 802.11ax (Wi-Fi 6), 802.1Q, 802.1X, 802.3ad, 802.3af, 802.3at, 802.3az

FORTIAP 234F	
SSID Types Supported	Local-Bridge, Tunnel, and Mesh
Per Radio Client Capacity	Up to 512 clients per radio (Radio1 and Radio2)
Cellular Co-existence*	Yes
LED Off Mode	Yes
Advanced 802.11 Features	
OFDMA	Yes (UL and DL)
Spatial Reuse (BSS Coloring)	Yes
UL MU-MIMO	Yes
DL-MU-MIMO	Yes
Enhanced Target Wake Time (TWT)	Yes
ZeroWait DFS	No
Wireless Monitoring Capabilities	
Rogue Scan radio modes	Background, Dedicated
WIPS / WIDS radio modes	Background, Dedicated (recommended)
Packet Sniffer Mode	Yes
Spectrum Analyzer	Yes
Dimensions	
Length x Width x Height	12.45 x 8.6 x 1.66 inches (316 x 218 x 42 mm)
Weight	2.88 lbs (1.307 kg)
Package (shipping) Weight	7.93 lbs (3.6 kg)
Mounting Options	Wall and Pole
Included Accessories	Wall and Pole mounting kit
Environment	
Power Supply	802.3at PoE: GPI-130 ; ships with PoE Injector (reset functionality)
PSE functionality	No
Power Consumption (Maximum)	15.5 W
Humidity	10 - 90% non condensing
Operating / Storage Temperature	-40–140°F (-40 - 60°C) / -40–176°F (-40–80°C)
Directives	Low Voltage Directive • RoHS
UL2043 Plenum Material	No
Mean Time Between Failures	> 10 Years
IP Rating	IP67
Surge Protection Built In	Yes
Hit-less PoE Failover	N/A
Certifications	
WiFi Alliance Certified	Yes
DFS	FCC, IC, CE, Japan, Brazil, Taiwan and Korea
Warranty	
Limited Lifetime Warranty	Yes

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.









RF RX/TX PERFORMANCE TABLE

FORTIAP 234F							
	Radio 1		Radio 2		Radio 3 Scanning		
	2.4 GHz Tx Power per chain (dBm)	Rz Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)	2.4 GHz Tx Power per chain (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)
802.11b							
1 Mbps	24	-99	—	—	20	—	-92
11 Mbps	24	-91	—	—	18	—	-91
802.11g							
6 Mbps	24	-95	—	—	20	—	-92
54 Mbps	23	-78	—	—	18	—	-77
802.11n HT20							
MCS0	24	-94	—	—	20	—	-92
MCS7	23	-78	—	—	17	—	-74
802.11n HT40							
MCS0	23	-92	—	—	19	—	-90
MCS7	22	-74	—	—	17	—	-72
802.11ax HE20							
MCS0	23	-90	—	—	—	—	—
MCS11	21	-71	—	—	—	—	—
802.11ax HE40							
MCS0	21	-91	—	—	—	—	—
MCS11	19	-72	—	—	—	—	—
802.11a							
6 Mbps	—	—	21	-93	—	20	-93
54 Mbps	—	—	21	-77	—	19	-76
802.11n HT20							
MCS0	—	—	21	-91	—	20	-93
MCS7	—	—	20	-72	—	19	-73
802.11n HT40							
MCS0	—	—	21	-91	—	19	-90
MCS7	—	—	20	-72	—	18	-71
802.11ac VHT20							
MCS0	—	—	20	-91	—	19	-93
MCS9	—	—	18	-72	—	18	-69
802.11ac VHT40							
MCS0	—	—	19	-87	—	19	-90
MCS9	—	—	17	-64	—	16	-64
802.11ac VHT80							
MCS0	—	—	22	-91	—	17	-88
MCS9	—	—	19	-72	—	17	-61
802.11ax HE20							
MCS0	—	—	22	-91	—	—	—
MCS11	—	—	19	-72	—	—	—
802.11ac HE40							
MCS0	—	—	22	-91	—	—	—
MCS11	—	—	19	-72	—	—	—
802.11ac HE80							
MCS0	—	—	20	-89	—	—	—
MCS11	—	—	18	-59	—	—	—



ANTENNA RADIATION PATTERNS


FAP-234F



HIGHLIGHTS

FortiAP 23JF

This enterprise class Wi-Fi 6 wall plate AP provides three radios with internal antennas as well as features such as OFDMA and is PSE-capable. The AP can provide 24/7 scanning across both bands while still providing access on both the 2.4 GHz and 5 GHz bands. The integrated BLE radio can be used for beacons and locationing applications. Additional features include PoE out for downstream devices and RJ45 passthrough. This access point can be installed in minutes, right over the existing wall plate.

 **802.11ax | Tri-Radio 5 GHz + 2.4 GHz + scanning | 3 Antennas**

 **2x2 MU-MIMO | Up to 574 Mbps + 1,200 Mbps + scanning**



SPECIFICATIONS

FORTIAP 23JF	
Hardware	
Hardware Type	Indoor walljack/desktop AP
Number of Radios	3 + 1 BLE
Number of Antennas	3 dual band internal Wi-Fi + 1 single band 2.4 GHz BLE/ZigBee
Antenna Type and Peak Gain	PCB antenna Dual band: 4.0 dBi in 2.4 GHz band and 4.0 dBi in 5 GHz band BLE antenna: 3.5 dBi in 2.4 GHz band
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850
Radio 1 Capabilities	Frequency band: 2.4 GHz Channel width: 20/40 MHz Modulation: BPSK, QPSK, 64/256/1024 QAM MIMO Chains: 2x2 Service
Radio 2 Capabilities	Frequency band: 5.0 GHz Channel width: 20/40/80 MHz Modulation: BPSK, QPSK, 64/256/1024 QAM MIMO Chains: 2x2 Service
Radio 3 Capabilities	Frequency bands: 2.4 GHz and 5.0 GHz MIMO Chains: 1x1 Frequency Scanning
Maximum Data Rate	Radio 1: up to 574 Mbps Radio 2: up to 1200 Mbps Radio 3: Frequency scanning only
Bluetooth Low Energy Radio	Bluetooth scanning and iBeacon advertisement @ 10 dBm max TX power
Interfaces	4x 10/100/1000 Base-T RJ45 Ports (1x 802.3at PoE(PD), 1x 802.3af PoE (PSE), 2x Non-PoE Ports) 3 RJ-45 Ports (1x Pass-through in, 1x Pass-through out, 1x RS-232 Serial Port)
Power over Ethernet (PoE)	<ul style="list-style-type: none"> 802.3at PoE default (optional DC adaptor) Powered via DC power supply - Full System functionality + USB + PSE (8023af 15.4W) Powered by 802.3af - Only Radio functionality is operational (No USB/PSE supported) Powered by 802.3at - Full System functionality+ PSE(7w)
Simultaneous SSIDs	Up to 16 (14 if background scanning enabled)
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, PEAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST
User/Device Authentication	WPA™, WPA2™, and WPA3™ with 802.1x or preshared key, WEP, Web Captive Portal, MAC blacklist & allowlist
Maximum Tx Power (Conducted)	Radio 1: 2.4 GHz: 25 dBm / 158 mW (2 chains combined)* Radio 2: 5 GHz: 21 dBm / 158 mW (2 chains combined)* Radio 3: N/A
Kensington Lock	Yes
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11v, 802.11w, 802.11ac, 802.11ax (Wi-Fi 6), 802.1Q, 802.1X, 802.3ad, 802.3af, 802.3at, 802.3az
SSID Types Supported	Local-Bridge, Tunnel, and Mesh

FORTIAP 23JF	
Per Radio Client Capacity	Up to 512 clients per radio (Radio1 and Radio2)
Cellular Co-existence*	Yes
LED Off Mode	Yes
Advanced 802.11 Features	
OFDMA	Yes (UL and DL)
Spatial Reuse (BSS Coloring)	Yes
UL MU-MIMO	Yes
DL-MU-MIMO	Yes
Enhanced Target Wake Time (TWT)	Yes
ZeroWait DFS	No
Wireless Monitoring Capabilities	
Rogue Scan radio modes	Background, Dedicated
WIPS / WIDS radio modes	Background, Dedicated (recommended)
Packet Sniffer Mode	Yes
Spectrum Analyzer	Yes
Dimensions	
Length x Width x Height	6.6 × 4.6 × 1.1 inches (168 × 117 × 28 mm)
Weight	0.99 lbs (0.45 kg)
Package (shipping) Weight	1.54 lbs (0.7 kg)
Mounting Options	Wall Plate, Optional Desk Mount FAP-MNT-WJ-20
Included Accessories	Standard Mount kit for Ceiling, T-Rail, and Wall
Environment	
Power Supply	802.3at PoE: GPI-130 Optional DC power adaptor SP-FAP23J-PA-10
PSE functionality	Yes
Power Consumption (Maximum)	17.5W without PSE out and 31W with PSE out
Humidity	10 - 90% non condensing
Operating / Storage Temperature	32–122°F (0 - 50°C) / -22–158°F (-30–70°C)
Directives	Low Voltage Directive • RoHS
UL2043 Plenum Material	No
Mean Time Between Failures	> 10 Years
IP Rating	N/A
Surge Protection Built In	Yes
Hit-less PoE Failover	N/A
Certifications	
WiFi Alliance Certified	Yes
DFS	FCC, IC, CE, Japan, Brazil, Taiwan and Korea
Warranty	
Limited Lifetime Warranty	Yes

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.




RF RX/TX PERFORMANCE TABLE

FORTIAP 23JF							
	Radio 1		Radio 2		Radio 3 Scanning		
	2.4 GHz Tx Power per chain (dBm)	Rz Sensitivity (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)	2.4 GHz Tx Power per chain (dBm)	5 GHz Tx Power per Chain (dBm)	Rz Sensitivity (dBm)
802.11b							
1 Mbps	22	-98	—	—	20	—	-92
11 Mbps	20	-90	—	—	18	—	-91
802.11g							
6 Mbps	22	-93	—	—	20	—	-92
54 Mbps	20	-77	—	—	18	—	-77
802.11n HT20							
MCS0	22	-94	—	—	20	—	-92
MCS7	20	-76	—	—	17	—	-74
802.11n HT40							
MCS0	22	-92	—	—	19	—	-90
MCS7	20	-73	—	—	17	—	-72
802.11ax HE20							
MCS0	22	-90	—	—	—	—	—
MCS11	20	-71	—	—	—	—	—
802.11ax HE40							
MCS0	20	-90	—	—	—	—	—
MCS11	18	-70	—	—	—	—	—
802.11a							
6 Mbps	—	—	18	-93	—	20	-91
54 Mbps	—	—	18	-77	—	19	-75
802.11n HT20							
MCS0	—	—	19	-94	—	20	-90
MCS7	—	—	19	-75	—	19	-72
802.11n HT40							
MCS0	—	—	21	-91	—	19	-90
MCS7	—	—	20	-72	—	18	-71
802.11ac VHT20							
MCS0	—	—	21	-91	—	19	-93
MCS9	—	—	20	-72	—	18	-69
802.11ac VHT40							
MCS0	—	—	20	-91	—	19	-90
MCS9	—	—	18	-72	—	16	-64
802.11ac VHT80							
MCS0	—	—	19	-87	—	17	-88
MCS9	—	—	17	-64	—	17	-61
802.11ax HE20							
MCS0	—	—	20	-91	—	—	—
MCS11	—	—	18	-72	—	—	—
802.11ac HE40							
MCS0	—	—	19	-91	—	—	—
MCS11	—	—	17	-62	—	—	—
802.11ac HE80							
MCS0	—	—	18	-89	—	—	—
MCS11	—	—	16	-60	—	—	—




ANTENNA RADIATION PATTERNS








FAP-23JF



H-Plane Pattern



E-Plane Pattern



HIGHLIGHTS

FortiAP 221E and 223E

The FortiAP 221E and 223E are medium-density 802.11ac Wave 2 access points. These enterprise-class access points are ideal for medium-density environments such as an office or classroom with performance throughput of up to 867 Mbps.



802.11ac Wave 2 | Dual Radio 2.4 and 5 GHz | 4 Internal/External Antennas



2x2 MU-MIMO | Up to 400 + 867 Mbps



SPECIFICATIONS

	FORTIAP 221E	FORTIAP 223E
Hardware		
Hardware Type	Indoor AP	Indoor AP
Number of Radios	2 + 1 BLE	2 + 1 BLE
Number of Antennas	4 Internal + 1 Internal BLE	4 External + 1 Internal BLE
Antenna Type and Peak Gain	Patch: 4 dBi for 2.4 GHz, 5 dBi for 5 GHz	Dipole: 4 dBi for 2.4 GHz, 5 dBi for 5 GHz
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850	
Radio 1 Capabilities	2.4 GHz b/g/n (2x2:2 stream) 20/40 MHz (256 QAM)	2.4 GHz b/g/n (2x2:2 stream) 20/40 MHz (256 QAM)
Radio 2 Capabilities	5 GHz a/n/ac (2x2:2 stream) 20/40/80 MHz (256 QAM)	5 GHz a/n/ac (2x2:2 stream) 20/40/80 MHz (256 QAM)
Maximum Data Rate	Radio 1: up to 400 Mbps Radio 2: up to 867 Mbps	Radio 1: up to 400 Mbps Radio 2: up to 867 Mbps
Bluetooth Low Energy Radio	Bluetooth scanning and iBeacon advertisement @ 4 dBm max TX power	
Interfaces	1x 10/100/1000 Base-T RJ45	1x 10/100/1000 Base-T RJ45
Power over Ethernet (PoE)	IEEE 802.3af	IEEE 802.3af
Simultaneous SSIDs	16 (14 if background scanning enabled)	
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCHAPv2, PEAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST	
User/Device Authentication	WPA™, WPA2™, and WPA3™ with 802.1x or preshared key, WEP, Web Captive Portal, MAC blacklist & allowlist	
Maximum Tx Power	2.4 GHz: 23 dBm / 200 mW (2 chains combined)* 5 GHz: 24 dBm / 251 mW (2 chains combined)*	
Kensington Lock	Yes	Yes
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11v, 802.11w, 802.11ac, 802.11q, 802.1x, 802.3af, 802.3az	
SSID Types Supported	Local-Bridge, Tunnel, Mesh	Local-Bridge, Tunnel, Mesh
Per Radio Client Capacity	Up to 512	Up to 512
Cellular Co-existence	Yes	Yes
Reset Button	Yes	Yes
LED Off Mode	Yes	Yes
Advanced 802.11 Features		
802.11ac Wave 2 MU-MIMO	Yes	Yes
Transmit Beam Forming (TxBF)	Yes	Yes
Low-Density Parity Check (LDPC) Encoding	Yes	Yes
Maximum Likelihood Demodulation (MLD)	Yes	Yes

	FORTIAP 221E	FORTIAP 223E
Maximum Ratio Combining (MRC)	Yes	Yes
A-MPDU and A-MSDU Packet Aggregation	Yes	Yes
MIMO Power Save	Yes	Yes
Short Guard Interval	Yes	Yes
Wireless Monitoring Capabilities		
Rogue Scan Radio Modes	Background, Dedicated	Background, Dedicated
WIPS / WIDS Radio Modes	Background, Dedicated	Background, Dedicated
Packet Sniffer Mode	Yes	Yes
Spectrum Analyzer	Yes	Yes
Dimensions		
Length x Width x Height	6.3 x 6.3 x 1.85 inches (160 x 160 x 47 mm)	
Weight	1.1 lbs (0.5 kg)	1.1 lbs (0.5 kg)
Package (shipping) Weight	4.95 lbs (2.2 kg)	5.3 lbs (2.4 kg)
Mounting Options	Ceiling, T-Rail, and Wall	Ceiling, T-Rail, and Wall
Included Accessories	Mount kits for Ceiling, T-Rail, and Wall	Mount kits for Ceiling, T-Rail, and Wall, 4 dipole antennas
Environment		
Power Supply	SP-FAP200-PA-XX, GPI-115, or GPI-130	
Power Consumption (Max.)	12.36 W	12.36 W
Humidity	5–90% non-condensing	5–90% non-condensing
Operating / Storage Temperature	-4–113°F (-20–45°C) / -40–158°F (-40–70°C)	
Directives	Low Voltage Directive • RoHS	Low Voltage Directive • RoHS
UL2043 Plenum Material	No	No
Mean Time Between Failures	>30 Years	>30 Years
IP Rating	—	—
Surge Protection Built In	—	—
Hit-less PoE Failover	No	No
Certifications		
Wi-Fi Alliance Certified	Yes	Yes
DFS	FCC, IC, CE, Japan, Taiwan, Korea	FCC, IC, CE, Japan, Taiwan, Korea
Warranty		
Limited Lifetime Warranty	Yes	Yes

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.



RF RX/TX PERFORMANCE TABLE

FORTIAP 221E / 223E				
	RADIO 1		RADIO 2	
802.11 a/g	2.4 GHz Tx Power (dBm)	RX Sensitivity (dBm)	5 GHz Tx Power (dBm)	RX Sensitivity (dBm)
6 Mbps	20	-93	21	-91
9 Mbps	20	-91	21	-90
12 Mbps	20	-90	21	-89
18 Mbps	19	-88	21	-86
24 Mbps	19	-85	21	-83
36 Mbps	18	-82	21	-80
48 Mbps	18	-77	19	-76
54 Mbps	17	-75	19	-74
802.11n HT20				
MCS 0/8/16	20	-91	21	-91
MCS 1/9/17	19	-89	21	-88
MCS 2/10/18	19	-86	21	-86
MCS 3/11/19	18	-83	21	-83
MCS 4/12/20	18	-80	21	-79
MCS 5/13/21	17	-75	21	-75
MCS 6/14/22	17	-73	19	-74
MCS 7/15/23	16	-71	19	-72
802.11n HT40				
MCS 0/8/16	19	-89	20	-88
MCS 1/9/17	19	-86	20	-85
MCS 2/10/18	18	-84	20	-82
MCS 3/11/19	18	-81	20	-79
MCS 4/12/20	17	-77	20	-76
MCS 5/13/21	17	-73	20	-72
MCS 6/14/22	16	-71	19	-70
MCS 7/15/23	16	-69	19	-69
802.11ac VHT20				
MCS 0	19	-91	21	-91
MCS 1	19	-89	21	-88
MCS 2	19	-86	21	-86
MCS 3	18	-83	21	-83
MCS 4	18	-80	21	-79
MCS 5	18	-76	21	-75
MCS 6	18	-73	19	-74
MCS 7	18	-71	19	-72
MCS 8	18	-68	18	-69
802.11ac VHT40				
MCS 0	19	-89	20	-88
MCS 1	19	-86	20	-85
MCS 2	19	-84	20	-82
MCS 3	18	-81	20	-79
MCS 4	17	-77	20	-76
MCS 5	17	-73	20	-72
MCS 6	17	-71	19	-70
MCS 7	17	-69	19	-69
MCS 8	17	-68	18	-65
MCS 9	16	-66	17	-64
802.11ac VHT80				
MCS 0	—	—	19	-85
MCS 1	—	—	19	-83
MCS 2	—	—	19	-80
MCS 3	—	—	19	-77
MCS 4	—	—	19	-74
MCS 5	—	—	19	-71
MCS 6	—	—	18	-69




RF RX/TX PERFORMANCE TABLE

FORTIAP 221E / 223E				
802.11ac VHT80	RADIO 1		RADIO 2	
	2.4 GHz Tx Power (dBm)	RX Sensitivity (dBm)	5 GHz Tx Power (dBm)	RX Sensitivity (dBm)
MCS 7	—	—	18	-68
MCS 8	—	—	17	-63
MCS 9	—	—	17	-61




ANTENNA RADIATION PATTERNS




FAP-221E




H-Plane Pattern




E-Plane Pattern






FAP-223E



H-Plane Pattern




E-Plane Pattern



HIGHLIGHTS

FortiAP C24JE

The FAP-C24JE is a performance/price-competitive 2.4 GHz/5 GHz concurrent MU-MIMO wall plate AP with support of PoE IP phone and RJ45 pass-through. This access point can be installed in minutes, right over the existing wall plate.



 **802.11 ac Wave 2 | Dual Radio 2.4 GHz and 5 GHz | 4 Internal Antennas**

 **Up to 300 + 867 Mbps**

SPECIFICATIONS

FORTIAP C24JE	
Hardware	
Hardware Type	Wall Plate AP
Number of Radios	2
Number of Antennas	4 Internal
Antenna Type and Peak Gain	Chip 1.5 dBi for 2.4 GHz, 2 dBi for 5 GHz
Frequency Bands (GHz)*	2.400–2.4835, 5.150–5.250, 5.250–5.350, 5.470–5.725, 5.725–5.850
Radio 1 Capabilities	2.4 GHz b/g/n (2x2:2 stream) 20/40 MHz (64 QAM)
Radio 2 Capabilities	5 GHz a/n/ac (2x2:2 stream) 20/40/80 MHz (256 QAM)
Maximum Data Rate	Radio 1: up to 300 Mbps Radio 2: up to 867 Mbps
Bluetooth Low Energy Radio	—
Interfaces	4x 10/100/1000 Base-T RJ45 Ports (1x 802.3at PoE(PD), 1x 802.3af PoE (PSE), 2x Non-PoE Ports) 3 RJ-45 Ports (1x Pass-through in, 1x Pass-through out, 1x RS-232 Serial Port)
Serial Console Port	1x RJ45 RS232
Power over Ethernet (PoE)	<ul style="list-style-type: none"> • 802.3af (max PSE output of 4W) or • 802.3at (full 802.3af PSE output) • PSE functionality is only supported when powered via PoE/PoE+
Simultaneous SSIDs	Up to 8 (4 per radio)
EAP Type(s)	EAP-TLS, EAP-TTLS/MSCCHAPv2, PEAPv0/EAP-MSCHAPv2, PEAPv1/EAP-GTC, EAP-SIM, EAP-AKA, EAP-FAST
User/Device Authentication	WPA™ and WPA2™ with 802.1x or preshared key, WEP, Web Captive Portal, MAC blacklist & allowlist
Maximum Tx Power	23 dBm / 100mW (2 chains combined)*
Kensington Lock	No
IEEE Standards	802.11a, 802.11b, 802.11d, 802.11e, 802.11g, 802.11h, 802.11i, 802.11j, 802.11k, 802.11n, 802.11r, 802.11w, 802.11v, 802.11ac, 802.11q, 802.11x, 802.3af, 802.3at, 802.3az
SSID Types Supported	Local-Bridge, Tunnel
Per Radio Client Capacity	Up to 64
Cellular Co-existence	No
Reset Button	Yes
LED Off Mode	Yes
Advanced 802.11 Features	
802.11ac MU-MIMO Wave 2	Yes
Transmit Beam Forming (TxBF)	Yes
Low-Density Parity Check (LDPC) Encoding	Yes

FORTIAP C24JE	
Maximum Likelihood Demodulation (MLD)	Yes
Maximum Ratio Combining (MRC)	Yes
A-MPDU and A-MSDU Packet Aggregation	Yes
MIMO Power Save	Yes
Short Guard Interval	Yes
Wireless Monitoring Capabilities	
Rogue Scan Radio Modes	Background, Dedicated
WIPS / WIDS Radio Modes	Background, Dedicated
Packet Sniffer Mode	No
Spectrum Analyzer	No
Dimensions	
Length x Width x Height	6.69 x 4.04 x 1.08 inches 170 x 102.5 x 27.5 mm
Weight	1.3 lbs (0.6 kg)
Package (shipping) Weight	1.6 lbs (0.74 kg)
Mounting Options	Wall Plate, Optional Desk Mount FAP-MNT-WJ-20
Included Accessories	Mounting kit for Wall Plate
Environment	
Power Supply	GPI-115, GPI-130, or SP-FAP400-PA
Power Consumption (Maximum)	Depends on PoE connected
Humidity	5–90% non-condensing
Operating / Storage Temperature	32–104°F (0–40°C) / -4–158°F (-20–70°C)
Directives	Low Voltage Directive • RoHS
UL2043 Plenum Material	No
Mean Time Between Failures	>10 Years
IP Rating	—
Surge Protection Built In	—
Hit-less PoE Failover	No
Certifications	
Wi-Fi Alliance Certified	No
DFS	No
Warranty	
Limited Lifetime Warranty	Yes

* Frequency selection and power may be restricted to abide by regional regulatory compliance laws.



RF RX/TX PERFORMANCE TABLE




FORTIAP C24JE				
802.11 a/g	Radio 1 2.4 GHz		Radio 2 5 GHz	
	Maximum TX Power per Transmit Chain (dBm)	RX Sensitivity (dBm) per Receiver Chain	Maximum TX Power per Transmit Chain (dBm)	RX Sensitivity (dBm) per Receiver Chain
6 Mbps	21	-91	21	-91
9 Mbps	20	-89	20	-89
12 Mbps	20	-87	20	-87
18 Mbps	20	-85	19	-84
24 Mbps	19	-82	19	-80
36 Mbps	19	-76	19	-76
48 Mbps	18	-75	18	-74
54 Mbps	17	-74	18	-73
802.11 HT20				
MSC 0/8/16 (BPSK)	20	-90	19	-91
MSC 1/9/17 (QPSK)	19	-88	18	-88
MSC 2/10/18 (QPSK)	19	-85	18	-84
MSC 3/11/19 (16-QAM)	19	-83	17	-80
MSC 4/12/20 (16-QAM)	19	-76	17	-76
MSC 5/13/21 (64-QAM)	18	-72	17	-73
MSC 6/14/22 (64-QAM)	17	-72	16	-71
MSC 7/15/23 (64-QAM)	16	-71	16	-70
802.11 HT40				
MSC 0/8/16 (BPSK)	20	-89	19	-87
MSC 1/9/17 (QPSK)	19	-87	18	-84
MSC 2/10/18 (QPSK)	19	-84	18	-81
MSC 3/11/19 (16-QAM)	19	-82	18	-78
MSC 4/12/20 (16-QAM)	18	-77	17	-75
MSC 5/13/21 (64-QAM)	18	-72	17	-72
MSC 6/14/22 (64-QAM)	17	-71	17	-70
MSC 7/15/23 (64-QAM)	17	-70	17	-68
MSC 8/16/24 (256-QAM)	16	-69	16	-66
MSC 9/17/25 (256-QAM)	16	-69	16	-64
802.11 HT80				
MSC 0 (BPSK)			19	-85
MSC 1 (QPSK)			18	-82
MSC 2 (QPSK)			18	-80
MSC 3 (16-QAM)			18	-77
MSC 4 (16-QAM)			17	-75
MSC 5 (64-QAM)			17	-74
MSC 6 (64-QAM)			17	-72
MSC 7 (64-QAM)			17	-69
MSC 8 (256-QAM)			16	-65
MSC 9 (256-QAM)			16	-61

Maximum capability of the Hardware provided (Excluding antenna gain)



ANTENNA RADIATION PATTERNS

FAP-C24JE



ORDER INFORMATION

PRODUCT	SKU	DESCRIPTION
FortiAP 831F	FAP-831F	Indoor Wireless AP - Tri radio (1× 802.11 a/b/g/n/ac/ax 4×4 MIMO, 1× 802.11 a/b/g/n/ac/ax 8×8 MIMO and 1× 802.11 a/b/g/n/ac Wave 2 1×1 MU-MIMO), internal antennas, 1× 100/1000/5000 Base-T RJ45, 1× 10/100/1000 Base-T RJ45, BT/BLE, 1x Type A USB, 1x RS-232 RJ45 Serial Port. Ceiling/wall mount kit included. For power order 802.3at PoE injector GPI-130 or AC adapter SP-FAP400-PA.
	FC-10-F831F-247-02-DD	FortiCare Premium Support
	FC-10-P831F-284-02-DD	FortiCare Elite Support
FortiAP 431F	FAP-431F	Indoor Wireless AP - Tri radio (2× 802.11 a/b/g/n/ac/ax, 4×4 MIMO and 1× 802.11 a/b/g/n/ac Wave 2, 1×1 MU-MIMO), internal antennas, 1× 100/1000/2500 Base-T RJ45, 1× 10/100/1000 Base-T RJ45, BT/BLE, 1x Type A USB, 1x RS-232 RJ45 Serial Port. Ceiling/wall mount kit included. For power order 802.3at PoE injector GPI-130 or AC adapter SP-FAP400-PA.
	FC-10-F431F-247-02-DD	FortiCare Premium Support
	FC-10-F431F-284-02-DD	FortiCare Elite Support
FortiAP 433F	FAP-433F	Indoor Wireless AP - Tri radio (2× 802.11 a/b/g/n/ac/ax, 4×4 MIMO and 1× 802.11 a/b/g/n/ac Wave 2, 1×1 MU-MIMO), external antennas included, 1× 100/1000/2500 Base-T RJ45, 1× 10/100/1000 Base-T RJ45, BT/BLE, 1x Type A USB, 1x RS-232 RJ45 Serial Port. Ceiling/wall mount kit included. For power order 802.3at PoE injector GPI-130 or AC adapter SP-FAP400-PA.
	FC-10-F433F-247-02-DD	FortiCare Premium Support
	FC-10-F433F-284-02-DD	FortiCare Elite Support
FortiAP 432F	FAP-432F	Ruggedized indoor/outdoor Wireless FortiAP - Tri radio (1× 802.11b/g/n/ax 4×4 radio, 1 × 802.11a/n/ac/ax 4×4 Radio and 1× 802.11 a/b/g/n/ac Wave 2, 2×2), 1× 100/1000/2500 Base-T RJ45, 1× 10/100/1000 Base-T RJ45, BT/BLE + Zigbee, 1x Type A USB, 1x RS-232 RJ45 Serial Port. External Dual Band N-Type Omnidirectional antennas, Integrated mounting bracket for Antenna included + Wall/Pole Mount mounting kit. Ships with passive PoE injector. For power order 802.3bt.
	FC-10-PF432-247-02-DD	FortiCare Premium Support
	FC-10-PF432-284-02-DD	FortiCare Elite Support
FortiAP 231F	FAP-231F	Indoor Wireless AP - Tri radio (802.11 b/g/n/ax 2×2 MU-MIMO, 802.11 a/n/ac/ax 2×2 MU-MIMO and 1× 802.11 a/b/g/n/ac Wave 2, 1×1), internal antennas, 2× 10/100/1000 RJ45 port, BT/BLE, 1x Type A USB, 1x RS-232 RJ45 Serial Port. Ceiling/wall mount kit included. For power order 802.3at PoE injector GPI-130 or AC adapter SP-FAP250-PA-10.
	FC-10-PF231-247-02-DD	FortiCare Premium Support
	FC-10-PF231-284-02-DD	FortiCare Elite Support
FortiAP 234F	FAP-234F	Ruggedized indoor/outdoor Wireless AP - Tri radio (802.11 b/g/n/ax 2×2 MU-MIMO, 802.11 a/n/ac/ax 2×2 MU-MIMO and 1× 802.11 a/b/g/n/ac Wave 2, 1×1), internal antennas, 2× 10/100/1000 RJ45 port, BT/BLE, 1x Type A USB, 1x RS-232 RJ45 Serial Port. Pole/wall mount kit included. For power order 802.3at PoE injector GPI-130.
	FC-10-P234F-247-02-DD	FortiCare Premium Support
	FC-10-P234F-284-02-DD	FortiCare Elite Support
FortiAP 23JF	FAP-23JF	Wall Plate AP - Tri radio (802.11 b/g/n/ax 2×2 MU-MIMO, 802.11 a/n/ac/ax 2×2 MU-MIMO and 1× 802.11 a/b/g/n/ac Wave 2, 1×1), internal antennas, 4 × 10/100/1000 RJ45 port (1× 802.3at PoE PD, 1× 802.3af PoE PSE, 2x Non-PoE Ports), 2 RJ-45 Ports (1xPass-through in, 1x Pass-through out), BT / BLE, 1x RS-232 RJ45 Serial Port. Wall plate mounting kit included. For power order 802.3at PoE injector GPI-130. Optional Accessory AC power adapter SP-FAP23J-PAX-10; Desktop stand FAP-MNT-WJ-20.
	FC-10-P23JF-247-02-DD	FortiCare Premium Support
	FC-10-P23JF-284-02-DD	FortiCare Elite Support
FortiAP 221E	FAP-221E	Indoor Wireless AP - Dual radio (802.11 b/g/n and 802.11 a/n/ac Wave 2, 2×2 MU-MIMO), internal antennas, 1 × 10/100/1000 RJ45 port, BT / BLE. Ceiling/wall mount kit included. For power order 802.3af PoE injector GPI-115 or AC adapter SP-FAP200-PA.
	FC-10-PE221-247-02-DD	FortiCare Premium Support
	FC-10-PE221-284-02-DD	FortiCare Elite Support
FortiAP 223E	FAP-223E	Indoor Wireless AP - Dual radio (802.11 b/g/n and 802.11 a/n/ac Wave 2, 2×2 MU-MIMO), external antennas included, 1 × 10/100/1000 RJ45 port, BT / BLE. Ceiling/wall mount kit included. For power order 802.3af PoE injector GPI-115 or AC adapter SP-FAP200-PA.
	FC-10-PE223-247-02-DD	FortiCare Premium Support
	FC-10-PE223-284-02-DD	FortiCare Elite Support
FortiAP C24JE	FAP-C24JE	Wall Plate AP - Dual radio (802.11 b/g/n and 802.11 a/n/ac Wave 2, 2×2 MU-MIMO), internal antennas, 4 × 10/100/1000 RJ45 port (1x 802.3at PoE PD, 1× 802.3af PoE PSE, 2x Non-PoE Ports), 2 RJ-45 Ports (1xPass-through in, 1x Pass-through out), 1x RS-232 RJ45 Serial Port. Wall plate mounting kit includedFor power order 802.3af PoE injector GPI-115 (limited features) or 802.3at PoE injector GPI-130. Optional accessory (desktop stand) FAP-MNT-WJ-20.
	FC-10-PC24E-247-02-DD	FortiCare Premium Support
	FC-10-AP024-284-02-DD	FortiCare Elite Support



ORDER INFORMATION

PRODUCT	SKU	DESCRIPTION
Gigabit PoE Injector	GPI-115	1-port Gigabit PoE power injector, 802.3af 15.4 W, 10/100/1000.
	GPI-130	1-port Gigabit PoE power injector, 802.3at up to 30 W.
Power Adapter	SP-FAP400-PA	AC power adapter 12v, 3.0A - 36W for FAP-831F, FAP-431F, FAP-433F, and FAP-C24JE.
	SP-FAP200-PA	AC power adapter 12v, 2.5A - 30W for FAP-221E, and FAP-223E.
	SP-FAP23J-PA-10	AC power adapter 48v, 1.04A - 50W without power cord for FAP-23JF.
	SP-FAP250-PA-10	AC power adapter 12v, 4.0A - 48W with Extended operating temp 0 deg C - 50 deg C with US and EU plugs for FAP-U231F and FAP-231F.
Desktop Stand	FAP-MNT-WJ-20	Desktop stand for FAP/FAP-C/FAP-U wall jack style APs. Converts wall mounting hardware included with unit to desktop mounting - 20 pack.

Notes.

Additional external antenna options available for some models. See antenna datasheet for details.

A country suffix code (-A, -B, -C, -D, -E, -F, -I, -J, -K, -N, -P, -S, -T, -U, -V, -W, or -Y) applies to all AP models based upon country of deployment. Work with your local supplier for the correct model in your regulatory domain.

Access Points mentioned in this datasheet are covered by a Limited Lifetime Hardware Warranty. Terms and conditions can be found in the EULA at <https://www.fortinet.com/content/dam/fortinet/assets/legal/EULA.pdf>



www.fortinet.com

Copyright © 2022 Fortinet, Inc. All rights reserved. Fortinet®, FortiGate®, FortiCare® and FortiGuard®, and certain other marks are registered trademarks of Fortinet, Inc., and other Fortinet names herein may also be registered and/or common law trademarks of Fortinet. All other product or company names may be trademarks of their respective owners. Performance and other metrics contained herein were attained in internal lab tests under ideal conditions, and actual performance and other results may vary. Network variables, different network environments and other conditions may affect performance results. Nothing herein represents any binding commitment by Fortinet, and Fortinet disclaims all warranties, whether express or implied, except to the extent Fortinet enters a binding written contract, signed by Fortinet's General Counsel, with a purchaser that expressly warrants that the identified product will perform according to certain expressly-identified performance metrics and, in such event, only the specific performance metrics expressly identified in such binding written contract shall be binding on Fortinet. For absolute clarity, any such warranty will be limited to performance in the same ideal conditions as in Fortinet's internal lab tests. Fortinet disclaims in full any covenants, representations, and guarantees pursuant hereto, whether express or implied. Fortinet reserves the right to change, modify, transfer, or otherwise revise this publication without notice, and the most current version of the publication shall be applicable.

Fortinet is committed to driving progress and sustainability for all through cybersecurity, with respect for human rights and ethical business practices, making possible a digital world you can always trust. You represent and warrant to Fortinet that you will not use Fortinet's products and services to engage in, or support in any way, violations or abuses of human rights, including those involving illegal censorship, surveillance, detention, or excessive use of force. Users of Fortinet products are required to comply with the Fortinet EULA (<https://www.fortinet.com/content/dam/fortinet/assets/legal/EULA.pdf>) and report any suspected violations of the EULA via the procedures outlined in the Fortinet Whistleblower Policy (https://secure.ethicspoint.com/domain/media/en/gui/19775/Whistleblower_Policy.pdf).