

0.9 cu.ft. Commercial Microwave Oven



Model RCMW25-1000SS

This Royal Sovereign Commercial Microwave is built with a rugged 'grab and go' door handle and a stainless steel interior and exterior for added durability. Manufactured for commercial use, the microwave is ideal for quick service restaurants, convenience stores, snack bars, breakrooms, supermarkets and more.



Stainless Steel



Cooking Power

FEATURES

Manufactured for Commercial Use

- Large 0.9 cu.ft oven capacity with 1000 watts of cooking power
- Stainless steel interior and exterior
- Ceramic bottom without turntable
- Energy efficient bottom load energy feed system
- See-through door and lighted interior
- Built-in fan with automatic cool down feature runs fan automatically when needed, to allow the unit to run at peak performance without overheating

Easy to Use and Clean

- Multi-stage cooking
- 3 Power Levels
- 1 Touch keypad with 20 programmable menu items
- Bright back lit digital display
- Easy to clean stainless steel and ceramic surfaces

Ideal for light and medium usage

- Ideal usage for quick service restaurants, pubs, bars and convenience stores to office breakrooms, cafeteria, teachers lounge and more



0.9 cu.ft. Commercial Microwave Oven

Model RCMW25-1000SS



Multi-Stage
Cooking



Grab & Go
Door Handle



Stainless Steel
Cabinet & Cavity



Programmable Touch
Control Memory Pad

PRODUCT OVERVIEW



① Grab and Go Door Handle

Provides durability and ease-of use

② Spacious, Sealed Ceramic Interior shelf

Provides easy cleaning of interior. Accommodates standard 1/2" size steam table pan 4" Deep or 2 standard 1/4" size steam table pans 4" deep

③ Stainless steel cabinet and cavity

Provides a sleek, durable and easy-to clean unit

④ Versatile Controls

Provides user options including: Multi-stage cooking, 3 power levels, programmable menu items, etc.

SPECIFICATIONS

Attributes

Size: 0.9 cu.ft

Wattage: 1000 Watts

Cabinet Interior and Exterior: Stainless Steel

Controls: Touchpad

Programmable Controls: 20

Multi-Stage Cooking: Multi-stage (2)

Power Levels: 3

Back Lit Digital Display: Yes

Stackable: Yes

Holds: Standard 1/2" Steam Table Pan, 4" deep
or 2 Standard 1/4" Size Steam Table Pans, 4" deep


Child Lock: Yes

Electrical Rating

Plug: 120V/60Hz

Plug Type: NEMA 5-15

Approval: cULus, ETL Sanitization



Dimensions and Weights

Unit Dimensions (w x d x h)

20.5" x 17.1" x 12.3" (52 x 43.5 x 31.2cm)

Unit Weight: 39lbs. (17.7 kg)

Box Dimensions (w x d x h)

23" x 19.2" x 14.9" (58.6 x 48.6 x 37.8cm)

Box Weight: 42.6 lbs. (19.3 kg)

UPC Code

Carton Box: 8490230 61786

Warranty

1 Year /3 Year Magnetron

