


Premier Rolling TV Cart for 37" to 70" Displays, Frosted Glass Base and Shelf, Locking Casters, White

MODEL NUMBER: **DMCS3770SG75W**



Height-adjustable mobile cart with upscale, professional look lets you smoothly roll your 37 to 70 in. display from one room to another.

Features

Move Your Monitor, TV or Interactive Whiteboard Wherever Your Audience Is

This rugged rolling TV stand combines a height-adjustable display mount with the convenience of a mobile cart. Mount your curved- or flat-panel television, digital whiteboard or touchscreen monitor to the all-metal unit, and then roll it safely and smoothly from room to room.

Exquisitely Designed in a Sleek, Modern Style

The durable DMCS3770SG75W is constructed from heavy-duty steel and aluminum with an upscale frosted glass shelf and base. It helps you deliver your message in corporate settings, open-plan offices, modern waiting rooms and medical facilities.

Comes Ready to Roll Wherever You Need to Go

Three-inch swivel casters allow you to roll the DMCS3770SG75W into any office, conference room, huddle space or classroom best suited for cost-efficient resource sharing. Ease of movement allows collaborative workflow to happen in any location and maximizes usage to increase engagement, creativity and productivity. The casters lock into place to keep the stand securely in position while at rest.

Raise and Lower the Screen to Find the Most Comfortable Viewing Angle

The height-adjustable TV floor stand fits most displays, whiteboards and monitors from 37 to 70 inches. Its durable frame withstands the stress of repeated adjustments and supports up to 175 pounds (79.3 kgs.) You can raise or lower the height of the display from 65.7 to 84.6 inches above the floor. You can also rotate the screen to view the image in either landscape or portrait mode.

Conveniently Place Peripherals and Manage Cables

The durable frosted glass shelf and base hold audio/video and other components, such as laptops, projectors, webcams and Blu-ray players. Cables can be routed along the column to keep them hidden and avoid excessive clutter.

VESA-Compliant Mounting Ensures Display Compatibility

VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the

Highlights

- Ideal for rolling your TV or whiteboard into offices, classrooms and conference rooms
- Durable aluminum/steel frame blends into any room décor and supports up to 175 lbs. (79.3 kgs)
- Height adjusts from 65.7 to 84.6 in. to help you find your audience's ideal viewing angle
- Locking 3 in. swivel casters enable smooth rolling and lock to secure the cart at rest
- Elegant glass shelf accommodates laptops, webcams, Blu-ray players, etc. up to 11 lbs. (4.9 kgs)

System Requirements

- Television, monitor, digital whiteboard or interactive display from 37 to 70 in.
- Supports the following VESA patterns: 100 x 100, 200 x 100, 300 x 100, 400 x 100, 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400 and 600 x 400

Package Includes

- DMCS3770SG75W Premier Rolling TV Cart
- Owner's manual

following VESA mounting hole patterns: 100 x 100, 200 x 100, 300 x 100, 400 x 100, 200 x 200, 300 x 200, 300 x 300, 400 x 200, 400 x 300, 400 x 400 and 600 x 400.

Specifications

OVERVIEW	
UPC Code	037332275493
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	White
Material of Construction	Aluminum, Steel
VESA Pattern (mm)	100x100; 200x100; 200x200; 300x200; 300x300; 400x200; 400x300; 600x400
Motion	Fixed
Mounting Location	Floor
Degrees of Motion	Tilt +/-45 Degrees
Minimum Screen Size (in.)	37
Minimum Screen Size (cm)	93.98
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.80
Maximum Weight Capacity (lbs.)	175
Maximum Weight Capacity (kg)	79
Number of Displays	1
Shipping Weight (lbs.)	56.90
Shipping Weight (kg)	25.81
Unit Dimensions (hwd / in.)	84.600 x 31.500 x 19.000
Unit Weight (lbs.)	49.7
Unit Weight (kg)	22.54
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Cord Management	No
Antimicrobial	No
Tools Necessary	Yes
Security Lock	No
Built-in Cable Management	No

Casters	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty