

## PERFORMANCE

### Processor

Intel® Celeron® N5100 (4C / 4T, 1.1 / 2.8GHz, 4MB L3)

### Graphics

Integrated Intel UHD Graphics

### Chipset

Intel SoC Platform

### Memory

8GB Soldered LPDDR4x-2933

### Memory Slots

Memory soldered to systemboard, no slots, dual-channel

### Max Memory

8GB soldered memory, not upgradable

### Storage

64GB eMMC 5.1

### Storage Support

64GB eMMC 5.1 on systemboard

### Storage Slot

eMMC on systemboard, no slots

### Card Reader

MicroSD Card Reader

### Audio Chip

High Definition (HD) Audio, Realtek® 5682I-CGT codec

### Speakers

Stereo speakers, 2W x2

### Camera

HD 720p with Privacy Shutter + World Facing 5.0MP

### Microphone

Mono

### Battery

Integrated 42Wh

### Max Battery Life

Google power load test: 12.1 hr

### Power Adapter

65W USB-C® (2-pin)

## DESIGN

### Display

11.6" HD (1366x768) IPS 250nits Glossy 50% NTSC, Glass, Touch

### Touchscreen

10-point Multi-touch

### Keyboard

Non-backlit, English

### Case Color

Grey

### Surface Treatment

Texture

### Case Material

PC + ABS with Rubber Bumper (Top), PC + ABS (Bottom)

### Pen

Lenovo® USI Pen (Garaged)

### Dimensions (WxDxH)

289.6 x 202.4 x 19.9 mm (11.4 x 7.97 x 0.78 inches)

### Weight

Starting at 1.33 kg (2.93 lbs)

### Others

Buttons: power key, volume key

## SOFTWARE

### Operating System

Chrome OS

### Bundled Software

None

## CONNECTIVITY

### Ethernet

None

### WLAN + Bluetooth®

Intel AX201 11ax, 2x2 + BT5.0

### WWAN

Fibocom L850-GL

### SIM Card

None

### Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.2)
- 1x HDMI® 1.4b
- 1x microSD card reader
- 1x Headphone / microphone combo jack (3.5mm)

### Optional Ports (configured)

1x Nano-SIM card slot (WWAN support models)

## SECURITY & PRIVACY

### Security Chip

Google Security Chip H1

### Fingerprint Reader

None

### Physical Locks

Kensington® Nano Security Slot™

### Other Security

Camera privacy shutter

## SERVICE

### Base Warranty

1-year, Mail-in

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified 8.0
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

TopSeller : Yes

Announce Date : 2022-04-12

EAN / UPC / JAN : 196800798480

End of Support : N/A



## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 65W Standard AC Adapter (USB Type-C)- US/Can/Mex

4X20M26268

This Lenovo 65W Standard AC Adapter (USB Type-C) Power Adapter offers fast, efficient charging at home, in the office, or on the go. This power adapter is compatible with ThinkPad USB-C enabled Notebook and Tablet.



### Lenovo 65W USB-C DC Travel Adapter

40AK0065WW

Power up and stay productive on the road with this DC Travel adapter. Lenovo 65W USB-C DC Travel Adapter is the universal DC adapter, providing 65W power via USB-C for outdoor use.

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

PSREF  
Product Specifications  
Reference