

## OVERVIEW

Upgradeable Switched Outlet Level Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering individual outlet level control and a comprehensive view of outlet level power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. With the Geist Upgradeable hot-swap technology, users may easily update the rPDU technology with the addition of the appropriate Interchangeable Monitoring Device (IMD) as business needs change.

### Benefits

- Remotely reboot outlets to power cycle unresponsive IT equipment or increase runtime of critical equipment upon power failure with outlet-level control.
- Reliable power distribution with local and remote outlet-level power monitoring options offer quick access to critical power usage information down to the device level to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.



## Part #: VP7N6002

**Model Number:** MNU3EGW1-24CF18-6PS15D0A10-S-A

**Category:** Switched

**Sub Category:** Outlet Level Monitoring EC

**Power Configuration:** 60A, 208V DELTA, 17.2kW

**Physical Configuration:** 70in / 1778mm, Vertical

### Product Summary:

rPDU, Switched Outlet Level Monitoring EC, 60A, 208V Delta, 17.2kW, Vertical, (24) Combination C13/C19, 10ft / 3m power cord with 3P+E (IP67), Black Powder Coat.

### Monitoring:

Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.

- Daisy-chain up to 50 devices on a single IP address and reduce deployment time with self-configuration of downstream devices.

#### Plug Form:



3P+E (IP67)

#### Receptacle:



Combination C13/C19  
(Quantity: 24)

#### Chassis Color Options:



To discuss color options, contact your local sales representative.

### Product Specification and Options

#### System Features

<b>Monitoring</b>	Input and Outlet power monitoring with Outlet switching. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
<b>Input Monitoring</b>	Total Unit Monitoring (kWh, W, VA, PF) Phase (AB, BC, CA) Monitoring (kWh, W, VA, PF, V, A) Line (A, B, C) Monitoring (A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Circuit Monitoring</b>	Circuit / Breaker Monitoring (A)  Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
<b>Outlet Monitoring</b>	Outlet Monitoring (kWh, W, VA, PF, V, A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements.
<b>Remote Power Management</b>	Individual Outlet Switching with Optional User Defined Time Delays and Sequential Power-up
<b>Quantity Of Inputs</b>	1
<b>Voltage</b>	200-240V Delta
<b>Current</b>	60A x 3 Phase DELTA
<b>VA per Input (Load Capacity)</b>	17.2kW (208V)
<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	(6) 20A Double Pole Magnetic Breakers (10kAIC Rated)
<b>Switch</b>	Breaker/Switch Combination
<b>Scrolling / Rotatable Digital Display</b>	Yes
<b>Indicators - LED(s)</b>	24
<b>Power Cable Wire Gauge</b>	4/4
<b>Power Cable Length</b>	10ft / 3m
<b>Power Entry Location</b>	Bottom Front
<b>Plug Type</b>	IEC60309 3P + E, 60A, Watertight IP67
<b>Alternating Phase/Circuits</b>	Yes
<b>Receptacle/Socket Type #1</b>	Combination C13/C19

- Quantity on Face	24
- Quantity per Breaker	4
- Quantity per Phase Combination	8
- Circuit Color ID	6 Circuit = Orange, Green, Blue, Light Orange, Light Green, Light Blue
- Style	Banks of 6
- Voltage per Receptacle/Socket	208V
Network Connection	Dual 10/100/1000Mbps Ethernet
Protocols Supported	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
Data Access Formats	CSV datalog, JSON API, JSON datalog
USB Support	Yes
IP Reset Button	Yes
Hard Reboot Button	Yes
Serial Connection	RS232 via RJ45
Remote Sensor RJ Connection Jacks	1 (Supports up to 16 Sensors)
Maximum Operating Temperature	60C / 140F
Heavy Steel - Powder Coat Finish	Black
Configuration	Zero U
7938 Vertical Mounting Bracket Kit	Yes
Toolless Mounting Hardware - Center to Center Spacing	61.25in and 64.75in / 1556mm and 1645mm
Country of Origin	USA, TAA Compliant and Buy American Act COTS Compliant
Product Warranty	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
Certification/Agency Approvals	FCC Part 15 Class A Conformance
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 62368-1
Chassis Dimensions (LxWxD)	70in x 2.25in x 2.6in / 1778mm x 58mm x 66mm
Doghouse (D)	1.4in / 36mm
Shipped Weight	22lbs (9.98kg)