

## OVERVIEW

Upgradeable Outlet Level EC Monitored rPDUs provide reliable power distribution to critical IT equipment while delivering a comprehensive view of outlet level power usage via remote network access. Includes environmental monitoring capabilities to obtain real-time environmental metrics. Upgrade the hot-swappable monitoring device on select units to leverage new technologies and accommodate changing business needs.

### Benefits

- Reliable power distribution with local and remote power monitoring options offer quick access to critical power usage information to evaluate energy usage trends and maximize uptime.
- Reliable power distribution with local and remote outlet-level power monitoring options offer quick access to critical power usage information down to the device level to evaluate energy usage trends and maximize uptime.
- Environmental monitoring capabilities with the addition of optional environmental sensors ensure users have critical infrastructure data at their fingertips to prevent climate-related equipment failure and system downtime.
- Fault-Tolerant Daisy Chaining with RSTP simplifies intelligent rPDU connectivity and ensures data is reported even when a break in the network chain occurs. Supports up to 40 rPDUs.
- Daisy-chain up to 50 devices on a



## Part #: VP6N3002

**Model Number:** MNR3EGW1-36CF18-3TL21A0A10-S-A

**Category:** Monitored

**Sub Category:** Outlet Level EC

**Power Configuration:** 30A, 120/208V WYE, 8.6kW

**Physical Configuration:** 72in / 1829mm, Vertical

### Product Summary:

rPDU, Monitored Outlet Level EC, 30A, 120/208V WYE, 8.6kW, Vertical, (36) Combination C13/C19, 10ft / 3m power cord with L21-30P, Black Powder Coat.

### Monitoring:

Input and Outlet power monitoring. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.


single IP address and reduce deployment time with self-configuration of downstream devices.

**Plug Form:**



L21-30P

**Receptacle:**



Combination C13/C19  
(Quantity: 36)

**Chassis Color Options:**



To discuss color options, contact your local sales representative.

**Product Specification and Options**

**System Features**

<b>Monitoring</b>	Input and Outlet power monitoring. Circuit/Breaker current monitoring. Environmental monitoring via optional remote sensors. Daisy chain Ethernet connectivity. Local high visibility LED display.
<b>Input Monitoring</b>	Total Unit Monitoring (kWh, W, VA, PF) Phase (A, B, C) Monitoring (kWh, W, VA, PF, V, A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements
<b>Circuit Monitoring</b>	Circuit / Breaker Monitoring (A)  Circuit/Breaker Current Measurements Independently Tested and Verified at 2% Accuracy
<b>Outlet Monitoring</b>	Outlet Monitoring (kWh, W, VA, PF, V, A)  Power Measurements Compliant with ANSI C12.1 and IEC 62053-21 at 1% Accuracy Class Requirements.
<b>Quantity Of Inputs</b>	1
<b>Voltage</b>	100-120/200-240V WYE
<b>Current</b>	30A x 3 Phase WYE
<b>VA per Input (Load Capacity)</b>	8.6kW (208V)
<b>Frequency</b>	50/60Hz
<b>Over Current Protection</b>	(3) 20A Double Pole Magnetic Breakers (10kAIC Rated)
<b>Switch</b>	Breaker/Switch Combination
<b>Scrolling / Rotatable Digital Display</b>	Yes
<b>Indicators - LED(s)</b>	36
<b>Power Cable Wire Gauge</b>	10/5
<b>Power Cable Length</b>	10ft / 3m
<b>Power Entry Location</b>	Bottom Front
<b>Plug Type</b>	NEMA L21-30P Twistlock
<b>Alternating Phase/Circuits</b>	Yes
<b>Receptacle/Socket Type #1</b>	Combination C13/C19
<b>- Quantity on Face</b>	36
<b>- Quantity per Breaker and Phase Combination</b>	12

<b>- Circuit Color ID</b>	3 Circuit = Orange, Green, Blue
<b>- Style</b>	Banks of 6
<b>- Voltage per Receptacle/Socket</b>	208V
<b>Network Connection</b>	Dual 10/100/1000Mbps Ethernet
<b>Protocols Supported</b>	DHCP, HTTP, HTTPS, IPv4, IPv6, LDAP, NTP, RADIUS, RSTP, SSH, SMTP, SNMP (v1/v2c/v3), Syslog, TACACS+
<b>Data Access Formats</b>	CSV datalog, JSON API, JSON datalog
<b>USB Support</b>	Yes
<b>IP Reset Button</b>	Yes
<b>Hard Reboot Button</b>	Yes
<b>Serial Connection</b>	RS232 via RJ45
<b>Remote Sensor RJ Connection Jacks</b>	1 (Supports up to 16 Sensors)
<b>Maximum Operating Temperature</b>	60C / 140F
<b>Heavy Steel - Powder Coat Finish</b>	Black
<b>Configuration</b>	Zero U
<b>7938 Vertical Mounting Bracket Kit</b>	Yes
<b>Toolless Mounting Hardware - Center to Center Spacing</b>	61.25in and 64.75in / 1556mm and 1645mm
<b>Country of Origin</b>	USA, TAA Compliant and Buy American Act COTS Compliant
<b>Product Warranty</b>	5-year limited warranty if registered within 120 days of purchase, otherwise warranty defaults to 3 years
<b>Certification/Agency Approvals</b>	FCC Part 15 Class A Conformance
<b>Certification/Agency Approvals</b>	RoHS Compliant
<b>Certification/Agency Approvals</b>	UL & c-UL Listed 62368-1
<b>Chassis Dimensions (LxWxD)</b>	72in x 2in x 2.6in / 1829mm x 51mm x 66mm
<b>Doghouse (D)</b>	1.4in / 36mm
<b>Shipped Weight</b>	22lbs (9.98kg)