

# Product data sheet

Specifications



APC Smart-UPS Modular Ultra On-Line, 15kW, Lithium-ion, Rackmount 9U, 208/240V, Network Management, Extended runtime, W/rail kit

SRYL15K15RMXLT

## Overview

Lead Time Usually in Stock

## Main

Main Input Voltage 208 V

Product Or Component Type Uninterruptible power supply (UPS)

Other Input Voltage 240 V

Main Output Voltage 120 V  
208 V

Other Output Voltage 240 V

Kw Rating 15000 W

Rated Power In Va 15000 VA

Number Of Rack Unit 9U

Battery Type Li-Ion (Lithium Ion)

## Batteries & Runtime

Run Time [View Runtime Graph](#)

Efficiency [View Efficiency Graph](#)

Included Battery Modules 3

Battery Slots Empty 0

Rbc Quantity 3

Battery Design Life 8...10 year(s)

## General

Product Web Sub-Family Network management card

Number Of Power Module 3

Number Preinstalled Power Module 3

Number Of Power Module Free Slots 0

Number Of Power Module Filled Slots 3

Redundant Yes

## Physical

|                           |                          |
|---------------------------|--------------------------|
| <b>Color</b>              | Silver                   |
| <b>Height</b>             | 15.35 in (390 mm)        |
| <b>Width</b>              | 17.32 in (440 mm)        |
| <b>Depth</b>              | 27.56 in (700 mm)        |
| <b>Net Weight</b>         | 243.61 lb(US) (110.5 kg) |
| <b>Mounting Location</b>  | Front<br>Rear<br>Side    |
| <b>Mounting Mode</b>      | Rack-mounted             |
| <b>Two Post Mountable</b> | 1                        |
| <b>Usb Compatible</b>     | Yes                      |
| <b>Mounting Position</b>  | Horizontal               |

## Input

|  |                              |
|--|------------------------------|
| <b>Input Frequency</b>                 | 40 - 70 Hz                   |
| <b>Number Of Input Connectors</b>      | 1 Hard Wire 4-wire (2PH+N+G) |
| <b>Maximum Input Current Per Phase</b> | 75 A                         |
| <b>Load Power Factor</b>               | 0.5 leading to 0.5 lagging   |

## Output

|   |   |
|---|---|
| <b>Max Configurable Power (Watts)</b>   | 15000 W                                 |
| <b>Topology</b>                         | Double Conversion Online                |
| <b>Waveform Type</b>                    | Sine wave                               |
| <b>Overload Operation</b>               | 60 seconds @ 125% and 30 seconds @ 150% |
| <b>Bypass Type</b>                      | Built-in Bypass                         |
| <b>Maximum Configurable Power In Va</b> | 15000 VA                                |

## Conformance

|                               |                        |
|-------------------------------|------------------------|
| <b>Product Certifications</b> | ENERGY STAR V2.0 (USA) |
| <b>Marking</b>                | CULus<br>FCC           |

## Environmental

|  |                                  |
|--|----------------------------------|
| <b>Ambient Air Temperature For Operation</b> | 32...104 °F (0...40 °C)          |
| <b>Operating Altitude</b>                    | 0...9842.52 ft (0...3000 m)      |
| <b>Ambient Air Temperature For Storage</b>   | 5...113 °F (-15...45 °C)         |
| <b>Storage Relative Humidity</b>             | 0...95 %                         |
| <b>Storage Altitude</b>                      | 0.00...49212.60 ft (0...15000 m) |
| <b>Acoustic Level</b>                        | 68 dB                            |

## Communications & Management

|                                       |                                 |
|---------------------------------------|---------------------------------|
| <b>Pre-Installed Smartslot™ Cards</b> | Network management card         |
| <b>Control Panel</b>                  | Touch Screen LCD User Interface |

---

|                           |     |
|---------------------------|-----|
| Emergency Power Off (Epo) | Yes |
|---------------------------|-----|

## Ordering and shipping details

---

|      |              |
|------|--------------|
| Gtin | 731304420132 |
|------|--------------|

## Packing Units

---

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

---

|                              |   |
|------------------------------|---|
| Number Of Units In Package 1 | 1 |
|------------------------------|---|

---

|                  |                    |
|------------------|--------------------|
| Package 1 Height | 38.66 in (98.2 cm) |
|------------------|--------------------|

---

|                 |                  |
|-----------------|------------------|
| Package 1 Width | 23.62 in (60 cm) |
|-----------------|------------------|

---

|                  |                  |
|------------------|------------------|
| Package 1 Length | 22.83 in (58 cm) |
|------------------|------------------|

---

|                  |                          |
|------------------|--------------------------|
| Package 1 Weight | 294.32 lb(US) (133.5 kg) |
|------------------|--------------------------|

## Contractual warranty

---

|          |         |
|----------|---------|
| Warranty | 5 Years |
|----------|---------|

## Sustainability


**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

[Learn more about Green Premium >](#)



RoHS/REACH

## Well-being performance

 **Rohs Exemption Information** [Yes](#)

---

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

---

**Eu Rohs Directive** [Compliant with Exemptions](#)

---

**China Rohs Regulation** [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information.

---