

## PERFORMANCE

### Processor

Intel® Core™ i5-1145G7 (4C / 8T, 2.6 / 4.4GHz, 8MB)

### Graphics

Integrated Intel Iris® Xe Graphics Functions as UHD Graphics

### Chipset

Intel SoC Platform

### Memory

8GB Soldered DDR4-3200

### Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

### Max Memory

Up to 40GB (8GB soldered + 32GB SO-DIMM) DDR4-3200

### Storage

256GB SSD M.2 2242 PCIe® 3.0x4 NVMe®

### Storage Support

One drive, up to 256GB M.2 2242 SSD or 2TB M.2 2280 SSD

### Storage Slot

One M.2 2280 PCIe 3.0 x4 slot

### Card Reader

microSD Card Reader

### Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

### Speakers

Stereo speakers, 2W x2, Dolby® Audio™

### Camera

HD 720p with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 57Wh

### Max Battery Life

MobileMark® 2018: 12 hr  
JEITA 2.0: 16.8 hr

### Power Adapter

65W USB-C® (2-pin)

## DESIGN

### Display

15.6" FHD (1920x1080) IPS 300nits Anti-glare, 45% NTSC

### Keyboard

Backlit, English

### Case Color

Black

### Surface Treatment

Not Anti-microbial

### Case Material

PPS / 50% GF (Top), PC-ABS / Talc15 + Magnesium Alloy (Keyboard Cover), PA / 50% GF (Bottom)

### Dimensions (WxDxH)

365.8 x 248 x 19.1 mm (14.40 x 9.76 x 0.75 inches)

### Weight<sup>[2]</sup>

Starting at 1.82 kg (4.02 lbs)

## SOFTWARE

### Operating System

Windows® 11 DG Windows 10 Pro 64, English

## CONNECTIVITY

### Ethernet

100/1000M (RJ-45)

### WLAN + Bluetooth®

Intel Wi-Fi® 6E AX210, 11ax 2x2 + BT5.1

### Standard Ports

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4a)
- 1x HDMI® 2.0
- 1x microSD card reader
- 1x Headphone / microphone combo jack (3.5mm)

### Optional Ports (configured)

1x Ethernet (RJ-45) + 1x Side Docking Connector

### Docking

Various docking solutions supported via side docking connector (optional) or Thunderbolt.

For more compatible docking solutions, please visit [Docking for ThinkPad® T15 Gen 2](#)

## SECURITY & PRIVACY

### Security Chip

Discrete TPM 2.0

### Fingerprint Reader

Touch Style, Match-on-Chip, on Palm Rest

### Physical Locks

Kensington® Security Slot™, 3 x 7 mm

### Other Security

Camera privacy shutter

## MANAGEABILITY

### System Management

Intel® vPro®

## SERVICE

### Base Warranty

3-year, Courier or Carry-in

## CERTIFICATIONS

### Green Certifications

- EPEAT™ Gold
- ENERGY STAR® 8.0
- TCO Certified
- RoHS compliant

### Mil-Spec Test

MIL-STD-810H military test passed

## MODEL

TopSeller : Yes

Announce Date : 2022-12-10

EAN / UPC / JAN : 196803864854

End of Support : 2027-09-23



intel

To see more note information, please link to [https://psref.lenovo.com/Detail/ThinkPad\\_T15\\_Gen\\_2?M=20W400SUUS](https://psref.lenovo.com/Detail/ThinkPad_T15_Gen_2?M=20W400SUUS)

· Lenovo reserves the right to change specifications or other product information without notice.  
· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.  
· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### ThinkPad USB-C Dock Gen 2

40AS0090US

- Lenovo understands that modern business depends on a wide variety of PC's and even brands to meet their business needs. To make this easier Lenovo USB-C dock is compatible with Lenovo notebooks as well as note...

## Recommended Services

BEST	4Y Lenovo Protect (Premier Support + Accidental Damage Protection + Keep Your Drive + 3Y Sealed Battery + International Upg) (5PS0N73238)
BETTER	3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + Sealed Battery + International Upg) (5PS0N73216)
GOOD	3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery + International Upg) (5PS0N73159)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference