

PERFORMANCE**Processor**

AMD Ryzen™ 7 PRO 6850U (8C / 16T, 2.7 / 4.7GHz, 4MB L2 / 16MB L3)

Graphics

Integrated AMD Radeon™ 680M Graphics

Chipset

AMD SoC Platform

Memory

32GB Soldered LPDDR5-6400

Memory Slots

Memory soldered to systemboard, no slots, dual-channel

Max Memory

32GB soldered memory, not upgradable

Storage

512GB SSD M.2 2280 PCIe® Gen 4x4 Performance NVMe® Opal2

Storage Support

One drive, up to 2TB M.2 2280 SSD

Storage Slot

One M.2 2280 PCIe 4.0 x4 slot

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, Dolby® Audio™

Camera

FHD 1080p + IR with Privacy Shutter

Microphone

2x, Array

Battery

Integrated 52.5Wh

Power Adapter

65W USB-C® Slim (2-pin)

DESIGN**Display**

14" WQUXGA (3840x2400) IPS 500nits Anti-reflection / Anti-smudge, 100% DCI-P3, DisplayHDR™ 400, Dolby Vision™, Touch

Touchscreen

Add on Film Touch

Color Calibration

Factory Color Calibration

Keyboard

Backlit, French

Case Color

Black

Case Material

PC 50% GF + PC 20% CF (Top), PPS (Bottom)

Dimensions (WxDxH)

317.7 x 226.9 x 17.9 mm (12.51 x 8.93 x 0.705 inches)

Weight

Starting at 1.28 kg (2.82 lbs)

SOFTWARE**Operating System**

Windows® 11 Pro 64, French

Bundled Software

None

CONNECTIVITY**Ethernet**

100/1000M (RJ-45)

WLAN + Bluetooth®

Qualcomm® NFA725A Wi-Fi® 6E, 11ax, 2x2 + BT5.1, Soldered

WWAN

WWAN Upgradable to 4G

SIM Card

None

NFC

None

Standard Ports

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x USB-C 3.2 Gen 2 (support data transfer, Power Delivery and DisplayPort™ 1.4)
- 1x HDMI®, up to 4K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Security keyhole

Optional Ports (configured)

- 1x Smart card reader
- 1x Nano-SIM card slot (WWAN support models)

Docking

Various docking solutions supported via USB-C.

For more compatible docking solutions, please visit [Docking for ThinkPad® P14s Gen 3 \(AMD\)](#)**Monitor Cable**

None

SECURITY & PRIVACY**Smart Card Reader**

None

Security Chip

Microsoft® Pluto TPM 2.0

Fingerprint Reader

Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security

Camera privacy shutter

MANAGEABILITY**System Management**

AMD PRO

SERVICE**Base Warranty**

3-year, Courier or Carry-in

Included Upgrade

3Y Sealed Battery Add On (5WS1H31713), 3Y Premier Support Upgrade from 3Y Courier/CCI (5WS1H31725)

ACCESSORIES**Bundled Accessories**

None

CERTIFICATIONS**Green Certifications**

- EPEAT™ Gold
- ENERGY STAR® 8.0
- TCO Certified 9.0
- RoHS compliant

Mil-Spec Test

MIL-STD-810H military test passed

ISV CertificationsPlease visit [ISV certifications for Lenovo® Workstations](#)**MODEL**

TopSeller : Yes Announce Date : 2022-09-13

EAN / UPC / JAN : 196802855341 End of Support : 2029-04-12

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Comprehensive hardware & OEM software support



Single point of contact for simplified end-to-end case management



Technical Account Managers for proactive relationship and escalation management



Priority on service delivery and repair parts



Lenovo Service Connect Portal for customized reporting and product support



Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



Lenovo

PSREF
Product Specifications
Reference